

| | | |
|---|--|--|
|  | <h1 style="margin: 0;">TECHNICAL DATA</h1> | VIKING TO CHEMGUARD PART NUMBER REFERENCE |
|---|--|--|

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-945-4495 Email: techsvcs@vikingcorp.com

| Foam Concentrates | | | | |
|-----------------------------|------------------|-----------------|--------------------|-----------------------|
| Description | Chemguard Model | Container | Viking Part Number | Chemguard Part Number |
| 1% AFFF | C-103 | 5 Gallon Pail | F14969/5 | C103P |
| | | 55 Gallon Drum | F14969/55 | C103D |
| 3% AFFF | C-303 | 5 Gallon Pail | F14970/5 | C303P |
| | | 55 Gallon Drum | F14970/55 | C303D |
| | | 275 Gallon Tote | F14970/275 | C303BD275 |
| 3% AFFF Mil Spec. | C-301 MS | 5 Gallon Pail | F14971/5 | C301P |
| | | 55 Gallon Drum | F14971/55 | C301D |
| | | 275 Gallon Tote | F14971/275 | C301BD275 |
| 3% - 6% AR-AFFF | C-363 | 5 Gallon Pail | F14973/5 | C363P |
| | | 55 Gallon Drum | F14973/55 | C363D |
| 3% AR-AFFF | CUG (Ultraguard) | 5 Gallon Pail | F14972/5 | CUGP |
| | | 55 Gallon Drum | F14972/55 | CUGD |
| | | 275 Gallon Tote | F14972/275 | CUGBD275 |
| 2% High Expansion Foam | C2 | 5 Gallon Pail | F14974/5 | C2P |
| | | 55 Gallon Drum | F14974/55 | C2D |
| | | 275 Gallon Tote | F14974/275 | C2BD275 |
| 2% Xtra High Expansion Foam | CX | 5 Gallon Pail | F14975/5 | CXP |
| | | 55 Gallon Drum | F14975/55 | CXD |
| | | 275 Gallon Tote | F14975/275 | CXBD275 |

| Foam Makers | | |
|--------------------|------------------------|-----------------------|
| Viking Part Number | Chemguard Model Number | Chemguard Part Number |
| F15085 | CGFM1.5L | EF10376-0.6 |
| F15086 | | EF10376-0.8 |
| F15087 | | EF10376-1.0 |
| F15088 | | EF10376-1.5 |
| F15089 | | EF10376-2.0 |
| F15090 | | EF10376-2.5 |
| F15091 | CGFM1.5 | EF10376-3.0 |
| F15092 | | EF10385-4.5 |
| F15093 | | EF10385-6.0 |
| F15094 | | EF10385-6.8 |
| F15095 | | EF10385-8.0 |
| F15096 | | EF10385-10.0 |
| F15097 | CGFM2.5 | EF10385-12.0 |
| F15098 | | EF10392-14.0 |
| F15099 | | EF10392-16.3 |
| F15100 | | EF10392-18.0 |
| F15101 | | EF10392-20.0 |
| F15102 | | EF10392-22.0 |
| F15103 | | EF10392-24.0 |

| Handline Nozzles | |
|--------------------|-----------------------|
| Viking Part Number | Chemguard Part Number |
| F15033 | SB95P |
| F15034 | SB95NPSHP |
| F15035 | CFT |

| Fixed Monitors | |
|----------------|-----------------------|
| Part No. | Chemguard Part Number |
| F15059 | CM-1250M-3 |
| F15060 | CM-1250M-4 |
| F15064 | CM-2000H |



TECHNICAL DATA

VIKING TO CHEMGUARD PART NUMBER REFERENCE

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-945-4495 Email: techsvcs@vikingcorp.com

| Ratio Flow Controllers | | | | | |
|---|-------------------------------|---------|-----------------|------------------------|-----------------------|
| Size | For use with Foam Concentrate | | Viking Part No. | Chemguard Model Number | Chemguard Part Number |
| 2-1/2" (65 mm) Threaded 1" NPT | 1% AFFF | C103 | F15001/A | CPC2.5 | EF10236 |
| | 3% AFFF | C303 | F15001/B | | EF10237 |
| | 3% AFFF MS | C301 MS | F15001/C | | EF11515 |
| | 3% / 6% AR-AFFF @ 3% | C363 | F15001/D | | EF10240 |
| | 3% / 6% AR-AFFF @ 6% | C363 | F15001/E | | EF10241 |
| | 2% High Ex | C2 | F15001/H | | EF10322 |
| | 3% AR-AFFF | CUG | F15001/J | | EF10238 |
| 3" (80 mm) Wafer 1-1/4" NPT | 1% AFFF | C103 | F15007/A | CPC3 | EF10243 |
| | 3% AFFF | C303 | F15007/B | | EF10244 |
| | 3% AFFF MS | C301 MS | F15007/C | | EF11529 |
| | 3% / 6% AR-AFFF @ 3% | C363 | F15007/D | | EF10247 |
| | 3% / 6% AR-AFFF @ 6% | C363 | F15007/E | | EF10248 |
| | 2% High Ex | C2 | F15007/H | | EF10323 |
| | 3% AR-AFFF | CUG | F15007/J | | EF10245 |
| 4" (100 mm) Wafer 1-1/2" NPT | 1% AFFF | C103 | F15013/A | CPC4 | EF10250 |
| | 3% AFFF | C303 | F15013/B | | EF10251 |
| | 3% AFFF MS | C301 MS | F15013/C | | EF11525 |
| | 3% / 6% AR-AFFF @ 3% | C363 | F15013/D | | EF10254 |
| | 3% / 6% AR-AFFF @ 6% | C363 | F15013/E | | EF10255 |
| | 2% High Ex | C2 | F15013/H | | EF10324 |
| | 3% AR-AFFF | CUG | F15013/J | | EF10252 |
| 6" (150 mm) Wafer 2" NPT | 1% AFFF | C103 | F15019/A | CPC6 | EF10257 |
| | 3% AFFF | C303 | F15019/B | | EF10258 |
| | 3% AFFF MS | C301 MS | F15019/C | | EF11530 |
| | 3% / 6% AR-AFFF @ 3% | C363 | F15019/D | | EF |
| | 2% High Ex | C2 | F15019/H | | EF |
| | 3% AR-AFFF | CUG | F15019/J | | EF10259 |
| 8" (200 mm) Wafer 2-1/2" NPT | 1% AFFF | C103 | F15026/A | CPC8 | EF10264 |
| | 3% AFFF | C303 | F15026/B | | EF10265 |
| | 3% AFFF MS | C301 MS | F15026/C | | EF11535 |
| | 3% AR-AFFF | CUG | F15026/J | | EF10266 |



TECHNICAL DATA

VIKING TO CHEMGUARD PART NUMBER REFERENCE

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-945-4495 Email: techsvcs@vikingcorp.com

| ILBP | | | | | |
|------|-------------------------------|---------|-----------------|---------------------|--------------------|
| Size | For use with Foam Concentrate | | Viking Part No. | Chemguard Model No. | Chemguard Part No. |
| 3" | 1% AFFF | C103 | F15012/A | CVILBP3 | EF11559 |
| | 3% AFFF | C303 | F15012/B | | EF11561 |
| | 3% AFFF MS | C301 MS | F15012/C | | EF11560 |
| | 3% / 6% AR-AFFF @ 3% | C363 | F15012/D | | EF11563 |
| | 3% / 6% AR-AFFF @ 6% | C363 | F15012/E | | EF11564 |
| | 2% High Ex | C2 | F15012/H | | EF11565 |
| | 3% AR-AFFF | CUG | F15012/J | | EF11562 |
| 4" | 1% AFFF | C103 | F15018/A | CVILBP4 | EF11566 |
| | 3% AFFF | C303 | F15018/B | | EF11568 |
| | 3% AFFF MS | C301 MS | F15018/C | | EF11567 |
| | 3% / 6% AR-AFFF @ 3% | C363 | F15018/D | | EF11570 |
| | 3% / 6% AR-AFFF @ 6% | C363 | F15018/E | | EF11571 |
| | 2% High Ex | C2 | F15018/H | | EF11572 |
| | 3% AR-AFFF | CUG | F15018/J | | EF11569 |
| 6" | 1% AFFF | C103 | F15025/A | CVILBP6 | EF11573 |
| | 3% AFFF | C303 | F15025/B | | EF11575 |
| | 3% AFFF MS | C301 MS | F15025/C | | EF11574 |
| | 3% AR-AFFF | CUG | F15025/J | | EF11576 |
| 8" | 1% AFFF | C103 | F15032/A | CVILBP8 | EF11577 |
| | 3% AFFF | C303 | F15032/B | | EF11579 |
| | 3% AFFF MS | C301 MS | F15032/C | | EF11578 |
| | 3% AR-AFFF | CUG | F15032/J | | EF11580 |

| Mobile Carts | |
|--------------|-----------------------|
| Part No. | Chemguard Part Number |
| F15332 | CMFC-1 |
| F15333 | CMFC-2 |

| Hose Reel Stations | |
|--------------------|-----------------------|
| Part No. | Chemguard Part Number |
| F15336 | EF-10538 |
| F15337 | EF-10357 |
| F15338 | EF10540-01-01 |
| F15339 | EF10540-01-02 |
| F15340 | EF10540-01-03 |
| F15341 | EF10540-01-04 |
| F15342 | EF10540-02-01 |
| F15343 | EF10540-02-02 |
| F15344 | EF10540-02-03 |
| F15345 | EF10540-02-04 |

THIS PAGE INTENTIONALLY
LEFT BLANK