



## ULSZ.S1456 Audible-signal Appliances

Page Bottom

---

### Audible-signal Appliances

[See General Information for Audible-signal Appliances](#)

**POTTER ELECTRIC SIGNAL CO**

S1456

2081 CRAIG RD  
PO BOX 28480  
ST LOUIS, MO 63146 USA

**Bells, vibrating type**, Models MBL8, -10, provided with Model BBX-1. For outdoor use.

Models EXB-6, -8, -10 with or without one or more of the following suffixes A, C, P, V, followed by 2 or 4, with or without suffix W.

**Bell strobes**, Models MSB-63L, MSB-64S/L with optional mounting plate. Models SB624-75110, SB624-153075, -824-75110, -824-153075, -1024-75110, -1024-153075. For indoor use only.

**Motor driven bells**, Models MSB-63P, MSB-63PV, MSB-64, MSB-64V; Models MBF-6WA, -8WA, -10WA, -10WAL. For indoor or outdoor use; Models MBA-6, MBA-8, MBA-10, PBA-6, PBA-8, PBA-10. For outdoor use when used with Model BBX-4 back box.

Models MBA-6-12, MBA-8-12, MBA-10-12 for indoor or outdoor use.

Model SP-115 Retrofit Plate.

**Horns**, BZ-51-A4. For indoor use only.

Models HW-24, HW-24A, H24W for indoor use only.

Models BZ-52VL4, 52VT, 54VL4, 54VT.

Model ESZ-31 piezo sounder. For indoor use only.

Models HP-11, -11A, -24, -24T. For indoor use only.

Models FS1-1R, -1-1W, -2-1R, -2-1W. For indoor use only.

Models HP-26, HP-25T. For indoor use only.

Models FS-24 and FS-24T. For indoor use only.

Model CM24WH.

**Horn-strobes**, Models FSL1-1R-12, -1-1R-24, -1-1W-12, -1-1W-24, -2-1R-24F, -2-1W-24F, SF2C-24L1575, SHP24, -24-110, -24-153075, -24T, -24T-110, -24T-75110, -24T-153075, SZ5424-110, -5424-153075, -5424T-110, -5424T-153075. For indoor use only.

Models SH24W-153075, SH24W-75110, SH24W-1530, SHW24-153075, SHW24W-75110, SH24C-3075110, SH24C-177, CSH24W, CSH24C, CSH24CH. For indoor use only.

Models SHB24-75, CSHB24. For indoor or outdoor use, with or without Model 5BP-1, 5BX-1 or 4BX-1 accessories.

Model SHB120-75X. CSHB120 For indoor or outdoor use, with or without SBX-1 accessories. `X` maybe a letter indicating lens color.

Models BZ-54SL, HP-12SL, -24SL.

**Chimes**, Models CM24C, CM24W. Private Mode only. For indoor use.

**Chime-Strobes** , Models SCM24C-177, SCM24C-3075110, SCM24W-153075, SCM24W-75110, CSCM24C, CSCM24W, CSCM24CH. Private Mode only. For indoor use.

**Signal appliance accessory** , Model TMP1-3A and TMP1-3B. For indoor use.

Models 4BX-1, 4BX-3 indoor back box; Model 4SP-M trim plate.

Model SBP-1 trim plate.

Last Updated on 2005-03-21

---

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

