

Sprinkler Identification Number (SIN) Directory



210 N. Industrial Park Drive Hastings, MI 49058 U.S.A. Telephone: (269) 945-9501 | Technical Services: (877) 384-5464 | Fax: (269) 818-1680 | E-mail: techsvcs@vikingcorp.com

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK001	F_052814	10192 13007	2.8	40.3	Standard Response Upright, Small Orifice, 15 mm BSP	175 psi
VK001	F_052814	10218 13006	2.8	40.3	Standard Response Upright, Small Orifice, ½" NPT	175 psi
VK002	F_081314	10191	4.2	57	Standard Response Upright, Small Orifice, 15 mm BSP	175 psi
VK002	F_081314	10219	4.2	57	Standard Response Upright, Small Orifice, ½" NPT	175 psi
VK003	F_052914	10189 12992	2.8	40.3	Standard Response Pendent, Small Orifice, 15 mm BSP	175 psi
VK003	F_052914	10221 12994	2.8	40.3	Standard Response Pendent, Small Orifice, ½" NPT	175 psi
VK004	F_081614	10222	4.2	57	Standard Response Pendent, Small Orifice, ½" NPT	175 psi
VK006	F_082214	05574	4.2	57	Standard Response Fusible Link Upright, Small Orifice, ½" NPT	175 psi
VK008	F_082314	05575	4.2	57	Standard Response Fusible Link Pendent, Small Orifice, ½" NPT	175 psi
VK015	F_082114	09997	2.8	40.3	HP Standard Response Horizontal Sidewall, Small Orifice, ½" NPT	250 psi
VK021	F_081514	09995	2.8	40.3	HP Standard Response HP Upright, Small Orifice, ½" NPT	250 psi
VK023	F_081814	09994	2.8	40.3	HP Standard Response HP Pendent, Small Orifice, ½" NPT	250 psi
VK100	F_052014	10138 12986	5.6	80.6	Standard Response Upright, ½" NPT	175 psi
VK100	F_052014	10193 12993	5.6	80.6	Standard Response Upright, 15 mm BSP	175 psi
VK102	F_031414	10139 12987	5.6	80.6	Standard Response Pendent, ½" NPT	175 psi
VK102	F_031414	10173 12989	5.6	80.6	Standard Response Pendent, ½" NPT	175 psi
VK102-D	F_101912	10139A-X	5.6	80.6	Standard Response Domed Concealed Pendent, ½" NPT	175 psi
VK104	F_033514	10171 12988 20230	5.6	80.6	Standard Response Horizontal Sidewall, 15 mm BSP	175 psi
VK104	F_033514	10224 12995 19777	5.6	80.6	Standard Response Horizontal Sidewall, ½" NPT	175 psi
VK106	F_052414	10186 12991	5.6	80.6	Standard Response Vertical Sidewall, 15 mm BSP	175 psi
VK106	F_052414	10226 12996 17496	5.6	80.6	Standard Response Vertical Sidewall, ½" NPT	175 psi
VK108	F_052214	05506 12971	5.6	80.6	Standard Response Fusible Element Upright, 15 mm BSP	175 psi
VK108	F_052214	05557 12973	5.6	80.6	Standard Response Fusible Element Upright, ½" NPT	175 psi
VK110	F_052314	05508 12972	5.6	80.6	Standard Response Fusible Element Pendent, ½" NPT	175 psi
VK112	F_060404	05559 12974	5.6	80.6	Standard Response Fusible Element Horizontal Sidewall, ½" NPT	175 psi
VK116	F_082014	09849	5.6	80.6	HP Standard Response -5 HSW, ½" NPT	250 psi
VK118	F_022414	10172 19384	5.6	80.6	Standard Response Conventional, 15 mm BSP	175 psi
VK118	F_022414	10227 19383	5.6	80.6	Standard Response Conventional, ½" NPT	175 psi
VK120	F_032914	10168 18265	8.0	115.2	Standard Response Conventional, 20 mm BSP	175 psi
VK120	F_032914	10228 18270	8.0	115.2	Standard Response Conventional, ¾" NPT	175 psi
VK122	F_081714	09992	5.6	80.6	HP Standard Response HP Pendent, ½" NPT	250 psi
VK124	F_081414	09993	5.6	80.6	HP Standard Response HP Upright, ½" NPT	250 psi
VK130	F_060691	05012B	5.6	80.6	Standard Response Model N-2 Stainless Steel Upright, ½" NPT	175 psi
VK130	F_060691	06501BZ	5.6	80.6	Standard Response Open Model N-2 Stainless Steel Upright, ½" NPT	175 psi
VK132	F_060691	06483B	5.6	80.6	Standard Response Model N-2 Stainless Steel Pendent, ½" NPT	175 psi
VK132	F_060691	06502BZ	5.6	80.6	Standard Response Open Model N-2 Stainless Steel Pendent, ½" NPT	175 psi
VK145	F_032714	10174 12990 20228	5.6	80.6	Standard Response Upright, 15 mm BSP	175 psi
VK145	F_032714	10233 13001 19778	5.6	80.6	Standard Response Upright, ½" NPT	175 psi
VK150	F_071591	07852U	5.6	80.6	Standard Response Plain Barrel Dry Pendent, 1" NPT	175 psi
VK150	F_071591	07855U	5.6	80.6	Standard Response Plain Barrel Dry Pendent, 25 mm BSP	175 psi
VK151	F_071591	09343	5.6	80.6	Plain Barrel Dry Pendent, 1" NPT	175 psi
VK1510	F_101811	17389	5.6	80.6	Plain Barrel Dry Pendent, 25 mm BSP	175 psi
VK1510	F_101811	17388	5.6	80.6	Plain Barrel Dry Pendent, 1" NPT	175 psi
VK152	F_073091	07858U	5.6	80.6	Standard Response Plain Barrel Dry Horizontal Sidewall, 1" NPT	175 psi
VK152	F_073091	07861U	5.6	80.6	Standard Response Plain Barrel Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK153	F_011194	09125U	5.6	80.6	Standard Response Plain Barrel Dry Vertical Sidewall, 1" NPT	175 psi
VK153	F_011194	08963U	5.6	80.6	Standard Response Plain Barrel Dry Vertical Sidewall, 25 mm BSP	175 psi
VK154	F_071591	07740U	5.6	80.6	Standard Response Adjustable Standard Dry Pendent, 1" NPT	175 psi
VK154	F_071591	07854U	5.6	80.6	Standard Response Adjustable Standard Dry Pendent, 25 mm BSP	175 psi
VK155	F_071591	09341	5.6	80.6	Adjustable Standard Dry Pendent, 1" NPT	175 psi
VK1550	F_101811	17391	5.6	80.6	Adjustable Standard Dry Pendent, 25 mm BSP	175 psi
VK1550	F_101811	17390	5.6	80.6	Adjustable Standard Dry Pendent, 1" NPT	175 psi
VK156	F_073091	07857U	5.6	80.6	Standard Response Adjustable Standard Dry Horizontal Sidewall, 1" NPT	175 psi
VK156	F_073091	07860U	5.6	80.6	Standard Response Adjustable Standard Dry Horizontal Sidewall, 1" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK157	F_011194	09123U	5.6	80.6	Standard Response Adjustable Standard Dry Vertical Sidewall, 1" NPT	175 psi
VK157	F_011194	08961U	5.6	80.6	Standard Response Adjustable Standard Dry Vertical Sidewall, 25 mm BSP	175 psi
VK158	F_071591	06530U	5.6	80.6	Standard Response Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK158	F_071591	07853U	5.6	80.6	Standard Response Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK159	F_071591	09342	5.6	80.6	Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK1590	F_101811	17387	5.6	80.6	Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK1590	F_101811	17386	5.6	80.6	Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK160	F_033192	08050	5.6	80.6	Standard Response Plain Barrel Dry Upright, 1" NPT	175 psi
VK160	F_033192	08079	5.6	80.6	Standard Response Plain Barrel Dry Upright, Std. Orifice, 25 mm BSP	175 psi
VK161	F_011194	09124U	5.6	80.6	Standard Response Adjustable Recessed Dry Vertical Sidewall, 1" NPT	175 psi
VK161	F_011194	08962U	5.6	80.6	Standard Response Adjustable Recessed Dry Vertical Sidewall, 25 mm BSP	175 psi
VK162	F_073091	07856U	5.6	80.6	Standard Response Adjustable Recessed Dry Horizontal Sidewall, 1" NPT	175 psi
VK162	F_073091	07859U	5.6	80.6	Standard Response Adjustable Recessed Dry HSW, 25 mm BSP Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK163	F_090110	12810U	8.0	115.2	Standard Response Adjustable Standard Dry Pendent, 1" NPT	175 psi
VK163	F_090110	12813U	8.0	115.2	Standard Response Adjustable Standard Dry Pendent, 25 mm BSP	175 psi
VK164	F_090110	12811U	8.0	115.2	Standard Response Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK164	F_090110	12814U	8.0	115.2	Standard Response Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK166	F_090110	12741U	8.0	115.2	Standard Response Plain Barrel Dry Pendent, 1" NPT	175 psi
VK166	F_090110	12812U	8.0	115.2	Standard Response Plain Barrel Dry Pendent, 25 mm BSP	175 psi
VK168	F_060796	09798U	5.6	80.6	Standard Response Stainless Steel Plain Barrel Dry Pendent, 1" NPT	175 psi
VK168	F_060796	09799U	5.6	80.6	Standard Response Stainless Steel Plain Barrel Dry Pendent, 25 mm BSP	175 psi
VK169	F_060796	10360U	5.6	80.6	Standard Response Stainless Steel Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK169	F_060796	10377U	5.6	80.6	Standard Response Stainless Steel Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK172	F_031793	08387U	5.6	80.6	Quick Response Plain Barrel Dry Pendent, 1" NPT	175 psi
VK172	F_031793	16455U	5.6	80.6	Quick Response Plain Barrel Dry Pendent, 25 mm BSP	175 psi
VK173	F_010305	13248U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry Pendent, 1" NPT	175 psi
VK173	F_010305	13251U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry Pdt, 25 mm BSP	175 psi
VK174	F_031993	08388U	5.6	80.6	Quick Response Plain Barrel Dry HSW, 1" NPT	175 psi
VK174	F_031993	16456U	5.6	80.6	Quick Response Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK176	F_031793	08383U	5.6	80.6	Quick Response Adjustable Standard Dry Pendent, 1" NPT	175 psi
VK176	F_031793	16457U	5.6	80.6	Quick Response Adjustable Standard Dry Pendent, 25 mm BSP	175 psi
VK177	F_010305	13249U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry Pendent, 1" NPT	175 psi
VK177	F_010305	13252U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry Pendent, 25 mm BSP	175 psi
VK178	F_031993	08384U	5.6	80.6	Quick Response Adjustable Standard Dry Horizontal Sidewall, 1" NPT	175 psi
VK178	F_031993	16458U	5.6	80.6	Quick Response Adjustable Standard Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK180	F_031793	08385U	5.6	80.6	Quick Response Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK180	F_031793	16453U	5.6	80.6	Quick Response Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK181	F_010305	13250U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendent, 1" NPT	175 psi
VK181	F_010305	13253U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendent, 25 mm BSP	175 psi
VK182	F_031993	08386U	5.6	80.6	Quick Response Adjustable Recessed Dry Horizontal Sidewall, 1" NPT	175 psi
VK182	F_031993	16454U	5.6	80.6	Quick Response Adjustable Recessed Dry Horizontal Sidewall, 25 mm BSP	175 psi
VK184	F_031693	08417UA	5.6	80.6	Quick Response Dry Upright, 1" NPT	175 psi
VK186	F_051498	10541U	5.6	80.6	Standard Response/Quick Response Extended Coverage Adjustable Recessed Dry Pendent, 1" NPT or 25 mm BSP	175 psi
VK188	F_051598	10542U	5.6	80.6	Standard Response/Quick Response Extended Coverage Adjustable Recessed Dry Horizontal Sidewall, 1" NPT	175 psi
VK190-D	F_092003	12421UA	5.6	80.6	Standard Response Dry Domed Concealed Pendent, 1" NPT	175 psi
VK190-D	F_092003	12429UA	5.6	80.6	Standard Response Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK192-D	F_081311	12424UA	8.0	115.2	Standard Response Dry Domed Concealed Pendent, 1" NPT	175 psi
VK192-D	F_081311	12432UA	8.0	115.2	Standard Response Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK194-D	F_092103	12422UA	5.6	80.6	Quick Response Dry Domed Concealed Pendent, 1" NPT	175 psi
VK194-D	F_092103	12430UA	5.6	80.6	Quick Response Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK196-D	F_092203	12423UA	5.6	80.6	Standard/QR EC Dry Domed Concealed Pendent, 1" NPT	175 psi
VK196-D	F_092203	12431UA	5.6	80.6	Standard/QR EC Dry Domed Concealed Pendent, 25 mm BSP	175 psi
VK200	F_032814	10141	8.0	115.2	Standard Response Upright, 3/4" NPT	175 psi
VK200	F_032814	10169	8.0	115.2	Standard Response Upright, 20 mm BSP	175 psi
VK200	F_032814	10220	8.0	115.2	Standard Response Upright, 1/2" NPT (retrofit)	175 psi
VK200	F_032814	18266	8.0	115.2	Standard Response Upright, 20 mm BSP	175 psi
VK200	F_032814	20377	8.0	115.2	Standard Response Upright, 20 mm BSP	175 psi
VK200	F_032814	18263	8.0	115.2	Standard Response Upright, 3/4" NPT	175 psi
VK200	F_032814	20381	8.0	115.2	Standard Response Upright, 3/4" NPT	175 psi
VK200	F_032814	18268	8.0	115.2	Standard Response Upright, 1/2" NPT (retrofit)	175 psi
VK202	F_032614	10142	8.0	115.2	Standard Response Pendent, 3/4" NPT	175 psi
VK202	F_032614	10170	8.0	115.2	Standard Response Pendent, 20 mm BSP	175 psi
VK202	F_032614	10223	8.0	115.2	Standard Response Pendent, 1/2" NPT (retrofit)	175 psi
VK202	F_032614	18269	8.0	115.2	Standard Response Pendent, 1/2" NPT (Retrofit)	175 psi
VK202	F_032614	18264	8.0	115.2	Standard Response Pendent, 3/4" NPT	175 psi
VK202	F_032614	18267	8.0	115.2	Standard Response Pendent, 20 mm BSP	175 psi
VK202	F_032614	20380	8.0	115.2	Standard Response Pendent, 3/4" NPT (CCCF)	175 psi
VK202	F_032614	20376	8.0	115.2	Standard Response Pendent, 20 mm BSP (CCCF)	175 psi
VK202-D	F_101912	10142A-X	8.0	115.2	Standard Response Domed Concealed Pendent, 3/4" NPT	175 psi
VK204	F_060414	05514	8.0	115.2	Standard Response Fusible Link Upright, 3/4" NPT	175 psi
VK204	F_060414	05576	8.0	115.2	Standard Response Fusible Link Upright, 1/2" NPT (retrofit)	175 psi
VK204	F_060414	18253	8.0	115.2	Standard Response Fusible Link Upright, 3/4" NPT	175 psi
VK204	F_060414	18255	8.0	115.2	Standard Response Fusible Link Upright, 1/2" NPT (retrofit)	175 psi
VK206	F_060514	05578	8.0	115.2	Standard Response Fusible Link Pendent, 1/2" NPT (retrofit)	175 psi
VK206	F_060514	05516	8.0	115.2	Standard Response Fusible Link Pendent, 3/4" NPT	175 psi
VK206	F_060514	18254	8.0	115.2	Standard Response Fusible Link Pendent, 1/2" NPT (retrofit)	175 psi
VK206	F_060514	18256	8.0	115.2	Standard Response Fusible Link Pendent, 3/4" NPT	175 psi
VK250	F_081511	13173U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrel Dry HSW, 1" NPT	175 psi
VK250	F_081511	13179U	8.0	115.2	Standard Response Ordinary Hazard Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK252	F_081511	13172U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK252	F_081511	13178U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK254	F_081511	13174U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK254	F_081511	13180U	8.0	115.2	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK275	F_081111	13170U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 1" NPT	175 psi
VK275	F_081111	13176U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 25 mm BSP	175 psi
VK277	F_081111	13169U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT	175 psi
VK277	F_081111	13175U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 25 mm BSP	175 psi
VK279	F_081111	13171U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT	175 psi
VK279	F_081111	13177U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 25 mm BSP	175 psi
VK282	F_010505	13254U	8.0	115.2	Quick Response Plain Barrel Dry Pendent Fusible Link, 1" NPT	175 psi
VK282	F_010505	13257U	8.0	115.2	Quick Response Plain Barrel Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK284	F_081211	13239U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, 1" NPT	175 psi
VK284	F_081211	13242U	8.0	115.2	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, 25 mm BSP	175 psi
VK286	F_010505	13255U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, 1" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK286	F_010505	13258U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK288	F_081211	13240U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Standard Dry HSW Fusible Link, 1" NPT	175 psi
VK288	F_081211	13243U	8.0	115.2	Quick Response Adjustable Standard Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK290	F_010505	13256U	8.0	115.2	Quick Response Adjustable Recessed Dry Pendent Fusible Link, 1" NPT	175 psi
VK290	F_010505	13259U	8.0	115.2	Quick Response Adjustable Recessed Dry Pendent Fusible Link, 25 mm BSP	175 psi
VK292	F_081211	13241U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, 1" NPT	175 psi
VK292	F_081211	13244U	8.0	115.2	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, 25 mm BSP	175 psi
VK300	F_052114	06661B 12978	5.6	80.6	Quick Response Upright, 1/2" NPT	175 psi
VK301	F_062414	12279 17535 19779	5.6	80.6	Quick Response Fusible Element Upright, 1/2" NPT	175 psi
VK302	F_033314	06662B 19780 18021 12979	5.6	80.6	Quick Response Pendent, 1/2" NPT	175 psi
VK302-D	F_033614	06662BA-X	5.6	80.6	Standard/Quick Response Domed Concealed Pendent, 1/2" NPT (discontinued part number)	175 psi
VK302-D	F_033614	12979-X	5.6	80.6	Standard/Quick Response Domed Concealed Pendent, 1/2" NPT	
VK303	F_062514	12275 17536 19781	5.6	80.6	Quick Response Fusible Element Pendent, 1/2" NPT	175 psi
VK304	N/A	12982	5.6	80.6	Quick Response Horizontal Sidewall, 1/2" NPT	175 psi
VK305	F_060914	12121 19782 12997	5.6	80.6	Quick Response Horizontal Sidewall, 1/2" NPT	175 psi
VK306	F_060614	06727B 12983	5.6	80.6	Quick Response Vertical Sidewall, 1/2" NPT	175 psi
VK307	F_062714	13947 13948	5.6	80.6	Quick Response Fusible Element Horizontal Sidewall, 1/2" NPT	175 psi
VK308	F_021301	13949 13950	5.6	80.6	Quick Response Fusible Element HSW, 1/2" NPT	175 psi
VK309	F_020407	13951	5.6	80.6	Quick Response Fusible Element VSW, 1/2" NPT	175 psi
VK310	F_022514	06766B 19391	5.6	80.6	Quick Response Conventional, 1/2" NPT	175 psi
VK311	F_022614	13952 19392	5.6	80.6	Quick Response Fusible Element Conventional, 1/2" NPT	175 psi
VK315	F_060714	12281	5.6	80.6	HP Quick Response Upright, 1/2" NPT	250 psi
VK316	F_062814	13953	5.6	80.6	Quick Response Fusible Element Upright, 1/2" NPT	250 psi
VK317	F_060814	12282	5.6	80.6	HP Quick Response Pendent, 1/2" NPT	250 psi
VK318	F_062914	13954	5.6	80.6	HP Quick Response Fusible Element Pendent, 1/2" NPT	250 psi
VK319	F_030103	12285	5.6	80.6	HP -5 Quick Response Horizontal Sidewall, 1/2" NPT	250 psi
VK320	F_020307	13955	5.6	80.6	Quick Response Fusible Element HSW, 1/2" NPT	175 psi
VK325	F_061414	06717B 12980	2.8	40.3	Quick Response Upright, Small Orifice, 1/2" NPT	175 psi
VK326	F_063014	13956 13957	2.8	40.3	Quick Response Fusible Element Upright, Small Orifice, 1/2" NPT	175 psi
VK3271	F_061614	06931B	4.2	57	Quick Response Upright, Small Orifice, 10 mm BSP	175 psi
VK327	F_061514	06719B	4.2	57	Quick Response Upright, Small Orifice, 1/2" NPT	175 psi
VK328	F_071114	13958	4.2	57	Quick Response Upright, Small Orifice, 1/2" NPT	175 psi
VK329	F_061714	06718B 12981	2.8	40.3	Quick Response Pendent, Small Orifice, 1/2" NPT	175 psi
VK330	F_071014	13959 13960	2.8	40.3	Quick Response Fusible Element Pendent, Small Orifice, 1/2" NPT	175 psi
VK3311	F_061914	06932B	4.2	57	Quick Response Pendent, Small Orifice, 10 mm BSP	175 psi
VK331	F_061814	06720B	4.2	57	Quick Response Pendent, Small Orifice, 1/2" NPT	175 psi
VK332	F_071214	13961	4.2	57	Quick Response Fusible Element Pendent, Small Orifice, 1/2" NPT	175 psi
VK333	F_062014	10035	2.8	40.3	Quick Response Horizontal Sidewall, Small Orifice, 1/2" NPT	175 psi
VK334	F_071314	13962	2.8	40.3	Quick Response Fusible Element Horizontal Sidewall, Small Orifice, 1/2" NPT	175 psi
VK335	F_011012	08983	4.2	57	Quick Response Horizontal Sidewall, Small Orifice, 10 mm BSP	175 psi
VK337	F_050300	08985	4.2	57	Quick Response Vertical Sidewall, Small Orifice, 10 mm BSP	175 psi
VK338	F_073107	14692	5.6	80.6	Quick Response Stainless Steel Upright, 1/2" NPT	175 psi
VK339	F_073107	14693	5.6	80.6	Quick Response Stainless Steel Pendent, 1/2" NPT	175 psi
VK340	F_062114	12286	2.8	40.3	HP Quick Response Upright, Small Orifice, 1/2" NPT	250 psi
VK341	F_071414	13963	2.8	40.3	Quick Response Upright, Small Orifice, 1/2" NPT	250 psi
VK342	F_062214	12290	2.8	40.3	HP Quick Response Pendent, Small Orifice, 1/2" NPT	250 psi
VK343	F_071514	13964	2.8	40.3	HP Quick Response Fusible Element Pendent, Small Orifice, 1/2" NPT	250 psi
VK344	F_080688	12287	2.8	40.3	HP Quick Response Horizontal Sidewall, Small Orifice, 1/2" NPT	250 psi
VK345	F_033114	07060 12984 19783	5.6	80.6	Quick Response Upright, 15 mm BSP	175 psi
VK346	F_071614	13965	2.8	40.3	HP Quick Response Fusible Element Horizontal Sidewall, Small Orifice, 1/2" NPT	250 psi
VK350	F_033014	06665B	8.0	115.2	Quick Response Upright, 3/4" NPT	175 psi
VK350	F_033014	14817	8.0	115.2	Quick Response Upright, 20 mm BSP	175 psi
VK350	F_033014	06764B	8.0	115.2	Quick Response Upright, 1/2" NPT	175 psi
VK351	F_071714	13976 18275	8.0	115.2	Quick Response Fusible Element Upright, 3/4" NPT	175 psi
VK351	F_071714	13966 18272	8.0	115.2	Quick Response Fusible Element Upright, 1/2" NPT (Retrofit)	175 psi
VK352	F_033414	06666B 18258 20383	8.0	115.2	Quick Response Pendent, 3/4" NPT	175 psi
VK352	F_033414	06765B 18260	8.0	115.2	Quick Response Pendent, 1/2" NPT (Retrofit)	175 psi
VK352-D	N/A	06666BA-X	8.0	115.2	Standard/Quick Response Domed Concealed Pendent, 3/4" NPT (discontinued part number)	175 psi
VK352-D	F_102112	18258	8.0	115.2	Standard/Quick Response Domed Concealed Pendent, 3/4" NPT (discontinued part number)	175 psi
VK352	N/A	12104	8.0	115.2	Quick Response Pendent, 3/4" NPT (discontinued part number)	175 psi
VK353	F_071814	13975 18274	8.0	115.2	Quick Response Fusible Element Pendent, 3/4" NPT	175 psi
VK353	F_071814	13967 18273	8.0	115.2	Quick Response Fusible Element Pendent, 1/2" NPT (Retrofit)	175 psi
VK353-D	N/A	13975A-X	8.0	115.2	Quick Response Concealed Fusible Element Pendent, 3/4" NPT (discontinued part number)	175 psi
VK353-D	F_102212	18274A-X	8.0	115.2	Quick Response Concealed Fusible Element Pendent, 3/4" NPT	175 psi
VK354	F_033214	06768B 18261	8.0	115.2	Quick Response Conventional, 3/4" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK355	F_071914	13979 18276	8.0	115.2	Quick Response Fusible Element Conventional, 3/4" NPT	175 psi
VK360	F_092508	15591	8.0	115.2	Quick Response Horizontal Sidewall, 3/4" NPT	175 psi
VK375	N/A	08338	11.2	161.3	Quick Response ELO Upright, Extra-Large Orifice, 3/4 NPT (discontinued product)	175 psi
VK377	F_030993	08337 17489	11.2	161.3	Quick Response ELO Pendant, (Special Application), 3/4" NPT	175 psi
VK400	F_081788	06697B	5.6	80.6	Standard Response Model H Fusible Link Flush Pendant, Std. Orifice, 1/2" NPT	175 psi
VK402	F_081888	06702B	5.6	80.6	Quick Response Model H-1 Fusible Link Flush Pendant, 1/2" NPT	175 psi
VK404	N/A	09783A	5.6	80.6	Standard Response/Quick Response Model B-2 Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	175 psi
VK405	N/A	09782A	5.6	80.6	HP Standard Response/Quick Response Model B-2 Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	250 psi
VK408	N/A	11262A	5.6	80.6	Quick Response Concealed Horizontal Sidewall Sprinkler, Std. Orifice, 1/2" NPT (discontinued product)	175 psi
VK410	F_100998	10554	5.6	80.6	Quick Response Model HQR-2 Fusible Link Flush Pendant,	175 psi
VK412	F_101098	10579	5.6	80.6	Quick Response Model HQR-2 Fusible Link Flush Horizontal Sidewall, 1/2" NPT	175 psi
VK413	F_081888	11487	5.6	80.6	Quick Response Model H Fusible Link Flush Pendant, 1/2" NPT	175 psi
VK420	F_062395	09458	3.8	54.8	Residential Model H-3 Fusible Link Flush Pendant, 1/2" NPT	175 psi
VK430	F_082095	09530	4.3	62.0	Residential -4 Pendant, 1/2" NPT	175 psi
VK446	N/A	10037	5.6	80.6	Quick Response Light Hazard Horizontal Sidewall Sprinkler, 15 mm BSP (discontinued product)	175 psi
VK450	N/A	12357	4.2	57	Residential Horizontal Sidewall Sprinkler VK450 (K4.2) (discontinued product)	175 psi
VK454	N/A	12292	5.6	80.6	HP Quick Response Model B-2 Fusible Link Concealed Pendant, 1/2" NPT (discontinued product)	250 psi
VK457	F_072607	14694A	4.9	70.6	Residential Fusible Element Concealed Pendant, 1/2" NPT	175 psi
VK4570	F_100710	16872AC	4.9	70.6	Residential Fusible Element Concealed Lead Free Pendant, 1/2" NPT	175 psi
VK458	F_042005	13230	7.4	106.7	Residential Pendant, 3/4" NPT	175 psi
VK458-D	F_092305	13230ABX	7.4	106.7	Residential Domed Concealed Pendant, 3/4" NPT	175 psi
VK460	F_110205	13933	5.8	83.6	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK461	F_091506	13831A	2.8	40.3	Standard/Quick Response Concealed Pendant, Small Orifice, 1/2" NPT	175 psi
VK461	F_010408	14927	2.8	40.3	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK461	F_010408	14928	2.8	40.3	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK462	F_103005	13503A 19785A	5.6	80.6	Quick Response Concealed Pendant, 1/2" NPT	175 psi
VK462	F_062908	15480A	5.6	80.6	Quick Response Concealed Pendant MRI, 1/2" NPT	175 psi
VK462	F_010408	14918	5.6	80.6	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK462	F_010408	14919	5.6	80.6	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK462	F_022409	13642-/CR	5.6	80.6	Cleanroom Sprinkler (Cover Assembly)	175 psi
VK463	F_103005	13667A	5.6	80.6	HP Quick Response Concealed Pendant, 1/2" NPT	250 psi
VK464	F_021606	13614A	8.0	115.2	Quick Response Concealed Pendant, 3/4" NPT	175 psi
VK464	F_062908	15481A	8.0	115.2	Quick Response Concealed Pendant MRI, 3/4" NPT	175 psi
VK465	F_032107	14262A	4.2	57	Quick Response Concealed Pendant, Small Orifice, 1/2" NPT	175 psi
VK465	F_010408	14929	4.2	57	Adjustable Concealed Sprinkler Assembly, 1" NPT Male Connection	175 psi
VK465	F_010408	14930	4.2	57	Adjustable Concealed Sprinkler Assembly, 1" NPT Female Connection	175 psi
VK466	F_091406	13781	5.2	74.9	Residential Pendant, 1/2" NPT	175 psi
VK466-D	F_091606	13781A-X	5.2	74.9	Residential Concealed Pendant, 1/2" NPT	175 psi
VK468	F_012706	13637	4.9	70.6	Residential Pendant, 1/2" NPT	175 psi
VK467	F_090413	19154	4.9	70.6	Residential Upright, 1/2" NPT	175 psi
VK4670	F_061314	19442	4.9	70.6	Residential Lead Free Upright, 1/2" NPT	175 psi
VK4680	F_101010	16876	4.9	70.6	Residential Lead Free Pendant, 1/2" NPT	175 psi
VK468-D	F_020206	13637A-X	4.9	70.6	Residential Concealed Pendant, 1/2" NPT	175 psi
VK469	F_120508	15764A	11.2	161.3	Quick Response ELO Concealed Pendant, Extra Large Orifice, 3/4" NPT	175 psi
VK470	F_061011	17147	3.0	43.2	Residential Pendant, 1/2" NPT	175 psi
VK4700	F_100611	17492	3.0	43.2	Residential Lead FreePendant, 1/2" NPT	175 psi
VK472	F_121409	16130	5.8	83.6	Residential Pendant, 1/2" NPT	175 psi
VK474	F_012109	15790AC	5.8	83.6	Residential Concealed Pendant, 1/2" NPT	175 psi
VK476	F_120608	15630MC/-	4.9	70.6	Residential Flush Pendant, 1/2" NPT	175 psi
VK478	F_042612	19995	5.6	80.6	Quick Response Flush Pendant, 1/2" NPT	175 psi
VK478	F_042612	20112	5.6	80.6	Quick Response Flush Pendant, 15 mm BSP	175 psi
VK479	F_012915	19707	3.0	43.2	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK480	F_121609	16116AC	4.0	57.7	Residential Concealed Horizontal Sidewall, 1/2" NPT	175 psi
VK4800	F_100810	16880AC	4.0	57.7	Residential Lead Free Concealed Horizontal Sidewall, 1/2" NPT	175 psi
VK481	F_020312	17555A	5.6	80.6	Quick Response Concealed Horizontal Sidewall, 1/2" NPT	175psi
VK482	F_081512	18385	5.6	80.6	Quick Response Flush Concealed Dry Pendant, 1" NPT	175psi
VK484	F_050310	16240	4.2	57	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK4840	F_100510	16881	4.2	57	Residential Lead Free Horizontal Sidewall, 1/2" NPT	175 psi
VK486	F_082411	17315	4.0	57.7	Residential Horizontal Sidewall, 1/2" NPT	175 psi
VK488	F_073012	18325	3.0	43.2	Freedom Residential Concealed Pendant, 1/2" NPT	175 psi
VK4880	F_061214	18326	3.0	43.2	Freedom Residential Lead Free Concealed Pendant, 1/2" NPT	175 psi
VK490	F_032116	20409	5.8	83.6	Freedom Residential Concealed Pendant, 1/2" NPT	175 psi
VK492	F_101615	20034	5.6	80.6	Standard Response Concealed Pendant, 1/2" NPT	175 psi
VK494	F_012116	20759	4.9	70.6	Residential Concealed Pendant, 1/2" NPT	175 psi
VK500	F_060198	10284	14.0	-	Model S-1 ESFR Pendant, 3/4" NPT	175 psi
VK500	F_060198	11350 19855	-	202	Model S-1 ESFR Pendant, 20 mm NPT	175 psi
VK501	N/A	14909	14.0	202	ESFR Dry Pendant, 2" Grooved Connection (discontinued product)	175 psi
VK501	N/A	14910	14.0	202	ESFR Dry Pendant, 1-1/2" NPT Threaded Connection (discontinued product)	175 psi
VK501	N/A	14911	14.0	202	ESFR Dry Pendant, 1-1/2" BSP Threaded Connection (discontinued product)	175 psi
VK502	F_042012	18702 18706 18710 18176 19908 19909 19910 19895	14.0	202	ESFR Dry Pendant, 2" Grooved Connection	175psi
VK502	F_042012	18703 18707 18711 18177	14.0	202	ESFR Dry Pendant, 1-1/2" NPT Threaded Connection	175psi
VK502	F_042012	18704 18708 18712 18178 19901	14.0	202	ESFR Dry Pendant, 1-1/2" BSP Threaded Connection	175psi
VK503	F_120106	14073	16.8	242	ESFR Pendant, 3/4" NPT	175 psi
VK503	F_120106	14818 19856 20372	16.8	242	ESFR Pendant, 20 mm BSP	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK504	F_062613	19015 19905 19907 19911 19913 19229 19912 19225	16.8	242	ESFR Dry Pendent, 1-1/2" Grooved Connection	175 psi
VK504	F_062613	19016 19234 19226 19230	16.8	242	ESFR Dry Pendent, 1-1/2" NPT Threaded Connection	175 psi
VK504	F_062613	19017 19235 19231 19227 19225	16.8	242	ESFR Dry Pendent, 1-1/2" BSP Threaded Connection	175 psi
VK506	F_081612	18493 18494	22.4	320	ESFR Pendent, 1" NPT, 25mm BSP	175 psi
VK510	F_100102	12080 19857 15221	25.2	363.3	ESFR Pendent, 1" NPT (Part No. 15221 discontinued)	175 psi
VK510	F_100102	12200 20373 14958	25.2	363.3	ESFR Pendent, 25 mm BSP (Part No. 14958 discontinued)	175 psi
VK514	F_010715	19591 19592	28.0	404	Specific Application ESFR Pendent, 1" NPT, 25 mm BSP	175 psi
VK520	F_060298	10625 19786	14.0	202	Model A-4 ESFR Upright, 3/4" NPT	175 psi
VK530	F_010692	09679	11.2	161.3	Standard Response ELO Upright (Special Application), 3/4" NPT	175 psi
VK530	F_010692	14819	11.2	161.3	Standard Response ELO Upright (Special Application), 20 mm BSP	175 psi
VK531	F_120699	10633	11.2	161.3	Quick Response ELO Upright (Special Application), 3/4" NPT	175 psi
VK5311	F_120699	19304 19305	11.2	161.3	Quick Response ELO Upright (Special Application), 1/2" NPT	175 psi
VK532	F_053114	08687	11.2	161.3	Standard/Quick Response EC LH/OH ELO Upright, 3/4" NPT	175 psi
VK533	F_021807	13978	11.2	161.3	Quick Response ELO Fusible Element Upright (Special Application), 3/4" NPT	175 psi
VK534	F_051393	08340	11.2	161.3	Standard and QR ECOH ELO Pendent, 3/4" NPT	175 psi
VK535	F_072014	14139	11.2	161.3	Standard and QR ECOH ELO Fusible Element Upright, 3/4" NPT	175 psi
VK536	F_072213	07961	11.2	161.3	Standard Response ELO Upr (Special Application) and Pdt, 3/4" NPT	175 psi
VK536	F_072213	14820	11.2	161.3	Standard Response ELO Upr (Special Application) and Pdt, 20 mm BSP	175 psi
VK537	F_021907	14611	11.2	161.3	Standard and QR ECOH ELO Fusible Element Pendent, 3/4" NPT	175 psi
VK538	F_050511	17115A	11.2	161.3	EC/QREC OH Concealed Pendent, Extra-Large Orifice, 3/4" NPT	175 psi
VK540	F_090595	13167	11.2	161.3	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, 3/4" NPT	175 psi
VK540	F_090595	13166	11.2	161.3	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, 1/2" NPT	175 psi
VK544	F_040815	19830 19831	11.2	161.3	Standard Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK545	F_040815	19835 19836	11.2	161.3	Standard Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK546	F_040815	19840 19841	11.2	161.3	Standard Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK547	F_040915	19828 19829	11.2	161.3	Quick Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK548	F_040915	19833 19834	11.2	161.3	Quick Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK549	F_040915	19838 19839	11.2	161.3	Quick Response Dry Pendent ELO, 1-1/4" NPT, 32 mm BSP	175 psi
VK550	F_012498	10138--U 12986--U	5.6	80.6	Standard Response Upright Intermediate Level, 1/2" NPT	175 psi
VK551	F_012498	12279--U	5.6	80.6	Quick Response Fusible Element Upright Intermediate Level, 1/2" NPT	175 psi
VK552	F_012498	05557--U 12973--U	5.6	80.6	Standard Response Fusible Link Upright Intermediate Level, 1/2" NPT	175 psi
VK556	F_012498	06661B--U 12978--U	5.6	80.6	Quick Response Upright Intermediate Level, 1/2" NPT	175 psi
VK558	F_012498	12281--U	5.6	80.6	HP Quick Response Upright Intermediate Level, 1/2" NPT	250 psi
VK560	F_012498	10141--U	8.0	115.2	Standard Response Upright Intermediate Level, 3/4" NPT	175 psi
VK560	F_012498	10220--U	8.0	115.2	Standard Response Upright Intermediate Level, 1/2" NPT	175 psi
VK562	F_012498	05514--U	8.0	115.2	Standard Response Fusible Link Upright Intermediate Level, 3/4" NPT	175 psi
VK566	F_012498	06665B--U	8.0	115.2	Quick Response Upright Intermediate Level, 3/4" NPT	175 psi
VK567	F_012498	13976--U	8.0	115.2	Quick Response Upright Intermediate Level, 3/4" NPT	175 psi
VK570	F_010104	13840	14.0	202	Extended Coverage Ordinary Hazard Upright, 3/4" NPT	175 psi
VK572	F_072313	13722	14.0	202	Extended Coverage Ordinary Hazard Pendent, 3/4" NPT	175 psi
VK580	F_041904	12739	16.8	242.2	Standard Response Upright, 3/4" NPT	175 psi
VK592	F_033108	14243A	19.6	282.6	Standard Response Pendent, 1" NPT	175 psi
VK592	F_033108	15468	19.6	282.6	Standard Response Pendent, 25 mm BSP	175 psi
VK595	F_121610	16859	25.2	363.3	EC Upright (Storage-Density/Area), 1" NPT	175 psi
VK595	F_121610	16885	25.2	363.3	EC Upright (Storage-Density/Area), 25 mm BSP	175 psi
VK598	F_090414	19522A 19764A	25.2	363.3	Standard Response Upright, 1" NPT, 25 mm BSP	175 psi
VK600	F_080988	06778B	5.6	80.6	Standard Response/Quick Response Extended Coverage Pendent, 1/2" NPT	175 psi
VK601	F_072114	13969	5.6	80.6	Quick Response EC Fusible Element Pendent, 1/2" NPT	175 psi
VK602	F_102412	07077B 18262	8.0	115.2	Standard Response/Quick Response Extended Coverage Pendent, 3/4" NPT	175 psi
VK603	F_102512	14140 18277	8.0	115.2	Quick Response Extended Coverage Pendent, 3/4" NPT	175 psi
VK604	F_062314	10335	5.6	80.6	Standard Response/Quick Response -5 Extended Coverage Pendent, 1/2" NPT	175 psi
VK605	F_072414	12120	5.6	80.6	-5 HSW (with EC, QREC, and Specific Application Listings), 1/2" NPT	175 psi
VK606	F_102612	13005 18271	8.0	115.2	Standard Response/Quick Response Extended Coverage Horizontal Sidewall, 3/4" NPT	175 psi
VK607	F_072214	13970	5.6	80.6	Standard Response/Quick Response Extended Coverage Fusible Element Pendent, 1/2" NPT	175 psi
VK608	F_052793	08339	11.2	161.3	Standard Response/Quick Response Extended Coverage Light Hazard Extra-Large Orifice Pendent, 3/4" NPT	175 psi
VK609	F_072314	13971	5.6	80.6	Standard Response/Quick Response Extended Coverage Fusible Element Horizontal Sidewall, 1/2" NPT	175 psi
VK610	F_022098	12294	5.6	80.6	HP Standard Response/Quick Response -5 Extended Coverage Pendent, 1/2" NPT	250 psi
VK611	F_020807	13972	5.6	80.6	HP Standard Response/Quick Response Extended Coverage Fusible Element Pendent, 1/2" NPT	250 psi
VK612	F_030203	12295	5.6	80.6	HP Standard Response/Quick Response -5 EC HSW, 1/2" NPT	250 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK613	F_020907	13973	5.6	80.6	HP Standard Response/Quick Response Extended Coverage Fusible Element Horizontal Sidewall, 1/2" NPT	250 psi
VK614-D	F_061603	06778BA-X	5.6	80.6	Standard Response/Quick Response Extended Coverage Domed Concealed Pendent, 1/2" NPT	175 psi
VK616-D	F_061603	07077BA-X	8.0	115.2	Standard Response/Quick Response Extended Coverage	175 psi
VK617	F_021207	14141	11.2	161.3	Standard Response/Quick Response Extended Coverage Light Hazard Extra-Large Orifice Fusible Element Pendent, 3/4" NPT	175 psi
VK618-D	F_061503	08339A-X	11.2	161.3	Standard Response/Quick Response Extended Coverage Domed Concealed Light Hazard Extra-Large Orifice Pendent, 3/4" NPT	175 psi
VK630	F_102905	13500	8.0	115.2	Quick Response Extended Coverage Horizontal Sidewall, 3/4" NPT	175 psi
VK630-D	F_102805	13500A-X	8.0	115.2	Quick Response EC Domed Concealed HSW, 3/4" NPT	175 psi
VK632	F_080107	14613A	5.6	80.6	Quick Response EC Concealed Pendent, 1/2" NPT	175 psi
VK634	F_080107	14535A	8.0	115.2	Quick Response EC Concealed Pendent, 3/4" NPT	175 psi
VK636	F_121009	16102A	11.2	161.3	Quick Response EC LH Concealed Pendent, Extra-Large Orifice, 3/4" NPT	175 psi
VK638	F_081911	17375	8.0	115.2	Quick Response EC Horizontal Sidewall, 3/4" NPT	175psi
VK638	F_082211	17375	8.0	115.2	Quick Response EC Concealed Horizontal Sidewall, 3/4" NPT	175psi
VK680	F_050611	17114AC	8.0	115.2	Quick Response EC Concealed HSW, 3/4" NPT	175 psi
VK681	F_042915	19626	8.0	115.2	V-BB Specific Application Attic Sprinkler, 3/4" NPT (4:12 < 7:12)	175 psi
VK682	F_042915	19798	8.0	115.2	V-BB Specific Application Attic Sprinkler, 3/4" NPT (7:12 < 10:12)	175 psi
VK683	F_042915	19751	8.0	115.2	V-BB Specific Application Attic Sprinkler, 3/4" NPT (10:12 ≤ 12:12)	175 psi
VK684	F_042915	19627	5.6	80.6	V-BB Specific Application Attic Sprinkler, 1/2" NPT (4:12 < 7:12)	175 psi
VK685	F_042915	19801	5.6	80.6	V-BB Specific Application Attic Sprinkler, 1/2" NPT (7:12 < 10:12)	175 psi
VK686	F_042915	19754	5.6	80.6	V-BB Specific Application Attic Sprinkler, 1/2" NPT (10:12 ≤ 12:12)	175 psi
VK693	F_043015	19578	5.6	80.6	V-SD Specific Application Attic Sprinkler, 1/2" NPT (4:12 < 7:12)	175 psi
VK694	F_043015	19799	5.6	80.6	V-SD Specific Application Attic Sprinkler, 1/2" NPT (7:12 < 10:12)	175 psi
VK695	F_043015	19759	5.6	80.6	V-SD Specific Application Attic Sprinkler, 1/2" NPT (10:12 ≤ 12:12)	175 psi
VK696	F_042815	19538	4.2	57	Attic Upright Specific Application Attic Sprinkler, 1/2" NPT (4:12 to 12:12)	175 psi
VK740	F_030789	05133AAJ or AJJ	1.2	17.3	30° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK741	F_030789	05133AAK or AJK	1.2	17.3	60° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK742	F_030789	05133AAL or AJL	1.2	17.3	90° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK743	F_030789	05133AAM or AJM	1.4	20.2	120° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK744	F_030789	05133AAN or AJN	1.4	20.2	140° Model A-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK750	F_030789	05134AAJ or AJJ	2.0	28.8	30° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK751	F_030789	05134AAK or AJK	2.0	28.8	60° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK752	F_030789	05134AAL or AJL	2.0	28.8	90° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK753	F_030789	05134AAM or AJM	2.2	31.7	120° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK754	F_030789	05134AAN or AJN	2.2	31.7	140° Model A-2X Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK760	F_030789	05135AAJ or AJJ	2.8	40.3	30° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK761	F_030789	05135AAK or AJK	2.8	40.3	60° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK762	F_030789	05135AAL or AJL	2.8	40.3	90° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK763	F_030789	05135AAM or AJM	3.3	47.6	120° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK764	F_030789	05135AAN or AJN	3.3	47.6	140° Model B-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK770	F_030789	05136AAJ or AJJ	3.4	49	30° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK771	F_030789	05136AAK or AJK	3.4	49	60° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK772	F_030789	05136AAL or AJL	3.8	54.8	90° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK773	F_030789	05136AAM or AJM	3.9	56.2	120° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK774	F_030789	05136AAN or AJN	3.9	56.2	140° Model C-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK780	F_030789	05137AAJ or AJJ	4.7	67.8	30° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK781	F_030789	05137AAK or AJK	4.7	67.8	60° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK782	F_030789	05137AAL or AJL	5.0	72.1	90° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK783	F_030789	05137AAM or AJM	5.2	75.0	120° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK784	F_030789	05137AAN or AJN	5.2	75.0	140° Model D-2 Spray Nozzle, 1/2" NPT, Brass or Nickel	N/A
VK790	F_051800	01320B	1.5	21.6	Model C-1 Window Sprinkler, 1/4" Orifice, 1/2" NPT	N/A
VK791	F_051800	01321B	2.1	30.3	Model C-1 Window Sprinkler, 5/16" Orifice, 1/2" NPT	N/A
VK792	F_051800	01322B	3.0	43.2	Model C-1 Window Sprinkler, 3/8" Orifice, 1/2" NPT	N/A
VK793	F_051800	01323B	4.3	62	Model C-1 Window Sprinkler, 7/16" Orifice, 1/2" NPT	N/A
VK794	F_051800	01324B	5.8	83.6	Model C-1 Window Sprinkler, 1/2" Orifice, 1/2" NPT	N/A
VK795	F_051800	01325B	7.3	105.2	Model C-1 Window Sprinkler, 5/8" Orifice, 3/4" NPT	N/A
VK796	F_051800	01326B	8.1	117.3	Model C-1 Window Sprinkler, 3/4" Orifice, 3/4" NPT	N/A
VK800	F_051091	07848	-	-	HP Fixed Temperature Release, 1/2" NPT	250 psi
VK810	F_062104	12867	7.2	103.8	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	F_062104	12868	5.6	80.6	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	F_062104	12869	4.1	59.1	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	F_062104	12870	3.2	46.3	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	F_062104	12871	2.3	33.2	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	F_062104	12872	1.8	25.9	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK810	F_062104	12873	1.2	17.3	65° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12874	7.2	103.8	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12875	5.6	80.6	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12876	4.1	59.1	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12877	3.2	46.3	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12878	2.3	33.2	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12879	1.8	25.9	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK811	F_062104	12880	1.2	17.3	80° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12881	7.2	103.8	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12882	5.6	80.6	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12883	4.1	59.1	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12884	3.2	46.3	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12885	2.3	33.2	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12886	1.8	25.9	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK812	F_062104	12887	1.2	17.3	95° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12888	7.2	103.8	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12889	5.6	80.6	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12890	4.1	59.1	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12891	3.2	46.3	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12892	2.3	33.2	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12893	1.8	25.9	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK813	F_062104	12894	1.2	17.3	110° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12895	7.2	103.8	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12896	5.6	80.6	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12897	4.1	59.1	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12898	3.2	46.3	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12899	2.3	33.2	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12900	1.8	25.9	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK814	F_062104	12901	1.2	17.3	125° Model E Spray Nozzle, 1/2" NPT	175 psi
VK815	F_062104	12902	7.2	103.8	140° Model E Spray Nozzle, 1/2" NPT	175 psi

SIN*	Technical Data Page(s)	Sprinkler Base Part Number	Nominal K-Factor		Sprinkler Model and Type	Maximum Pressure Rating
			U.S.	metric		
VK815	F_062104	12903	5.6	80.6	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12904	4.1	59.1	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12905	3.2	46.3	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12906	2.3	33.2	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12907	1.8	25.9	140° Model E Spray Nozzle, ½" NPT	175 psi
VK815	F_062104	12908	1.2	17.3	140° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12909	7.2	103.8	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12910	5.6	80.6	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12911	4.1	59.1	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12912	3.2	46.3	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12913	2.3	33.2	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12914	1.8	25.9	160° Model E Spray Nozzle, ½" NPT	175 psi
VK816	F_062104	12915	1.2	17.3	160° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12916	7.2	103.8	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12917	5.6	80.6	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12918	4.1	59.1	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12919	3.2	46.3	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12920	2.3	33.2	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12921	1.8	25.9	180° Model E Spray Nozzle, ½" NPT	175 psi
VK817	F_062104	12922	1.2	17.3	180° Model E Spray Nozzle, ½" NPT	175 psi
VK824	F_051606	13633	.82	12.0	Model EM Spray Nozzle	175 psi
VK825	F_051606	13872	.48	7.0	Model EM Spray Nozzle	175 psi
VK900	F_110503	12493	4.2	57	Coin™ QR Upright (Specific Application), ½" NPT	175 psi
VK901	F_021607	12676AE	4.2	57	Coin™ QR Fusible Element Upright (Specific Application), ½" NPT	175 psi
VK920	N/A	15111	5.6	80.6	Flat Spray QR Pendent Sprinkler, 1/2" NPT (discontinued product)	175 psi
VK922	N/A	15112	8.0	115.2	Flat Spray QR Pendent Sprinkler, 3/4" NPT (discontinued product)	175 psi
VK950	F_081216	20757	5.6	80.6	Coin™ QR Upright (Specific Application), ½" NPT	175 psi

* The Sprinkler Identification Number (SIN) is stamped on the sprinklers.