

# **SASH SERIES**

# SPRINKLER ALARM SELECT-A-STROBE/HORN®/SIGN COMBINATION



**UL Listed Strobe Horn** 

**Dimensions:** 10-3/4" h x 9" w x 4-1/2" d

Voltages Available: SASH-24 (12/24 VDC)

SASH-120 (120 VAC)

**Environment:** Indoor or Outdoor use

Weatherproof backbox is included with

both models


**Termination:** Separate terminals for horn and strobe

Finish: Red with white lettering


Stock number: 1000755 SASH-24 Stock number: 1000760 SASH-120

The SASH series is a multitone sstrobe/horn combination designed for use as an audio visual indication for automatic sprinkler systems. It can be installed in conjunction with or in place of water motor gongs.


## **Wiring Information**



### SASH-24



#### SASH-120



DWG# 1216-2

Potter Electric Signal Company, LLC • St. Louis, MO • Cust Service: 866-572-3005 • Tech Support: 866-956-0988 • Canada 888-882-1833 • www.pottersignal.com