



For Listings/Approval Details and Limitations, visit our website at www.anvilintl.com or contact an Anvil® Sales Representative.

SK-1 GROOVED CAP

Nominal Size	O.D.	End to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./Kg
1 25	1.315 33.4	1¼ 25	0.3 0.1
1¼ 32	1.660 42.2	1 25	0.4 0.2
1½ 40	1.900 48.3	1 25	0.5 0.2
2 50	2.375 60.3	1 25	0.7 0.3
2½ 65	2.875 73.0	1 25	1.0 0.4
3 80	3.500 88.9	1 25	1.5 0.7
4 100	4.500 114.3	1½ 27	2.7 1.2
5 125	5.563 141.3	1½ 27	4.4 2.0
6 150	6.625 168.3	1½ 27	6.6 3.0
8 200	8.625 219.1	1¾ 30	11.3 5.1
10* 250	10.750 273.1	1¼ 32	21.0 9.5
12* 300	12.750 323.9	1¼ 32	35.5 16.1

*Supplied as Style K-1 only.

MATERIAL SPECIFICATIONS

CAST FITTINGS:

Ductile Iron conforming to ASTM-A536

COATINGS:

- Rust inhibiting paint Color: ORANGE (standard) or
- Hot Dipped Zinc Galvanized conforming to ASTM A-153 (optional)
- Other available options: Example: RAL3000 or RAL9000 Series

PROJECT INFORMATION

APPROVAL STAMP

Project:	<input type="checkbox"/> Approved
Address:	<input type="checkbox"/> Approved as noted
Contractor:	<input type="checkbox"/> Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	