



Viking Sprinklers Now Available with Electroless Nickel Teflon® Coating for Corrosion Resistance

VIKING - STANDARD COVERAGE SPRINKLERS (w/ ENT Coating)		
SIN	K	Description
Standard Response, Upright		
VK100	5.6	Micromatic®, Upright, Glass Bulb, ½" NPT (p/n 12986JN_)
VK200	8.0	Micromatic®, Upright, Glass Bulb, ¾" NPT (p/n 18263JN_)
Standard Response, Pendant		
VK102	5.6	Micromatic®, Pendant, Glass Bulb, ½" NPT (p/n 12987JN_)
VK202	8.0	Micromatic®, Pendant, Glass Bulb, ¾" NPT (p/n 18264JN_)
Standard Response, Domed Concealed Pendant		
VK102-D	5.6	Domed Cnclد Pendant, Glass Bulb, ½" NPT (p/n 12987JN_X)
VK202-D	8.0	Domed Cnclد Pendant, Glass Bulb, ¾" NPT (p/n 18264JN_X)
Quick Response, Upright		
VK300	5.6	Microfast®, Upright, Glass Bulb, ½" NPT (p/n 12978JN_)
VK350	8.0	Microfast®, Upright, Glass Bulb, ¾" NPT (p/n 18257JN_)
Quick Response, Pendant		
VK302	5.6	Microfast®, Pendant, Glass Bulb, ½" NPT (p/n 12979JN_)
VK352	8.0	Microfast®, Pendant, Glass Bulb, ¾" NPT (p/n 18258JN_)
Quick Response, Horizontal Sidewall		
VK305	5.6	Microfast®, Horizontal Sidewall, Glass Bulb, ½" NPT (p/n 12997JN_)
Quick Response, Flat Concealed Pendant		
VK462	5.6	Mirage®, Flat Concealed Pendant, Glass Bulb, ½" NPT (p/n 13503JN_)
Quick Response, Domed Concealed Pendant		
VK302-D	5.6	Microfast®, Domed Cnclد Pendant, G Bulb, ½" NPT (p/n 12979JN_X)
VK352-D	8.0	Microfast®, Domed Cnclد Pendant, G Bulb, ¾" NPT (p/n 18258JN_X)
HIGH PRESSURE, Standard Response		
VK116	5.6	Micromatic®-HP, Horiz Sidewall, Glass Bulb, ½" NPT (p/n 09849JN_)
HIGH PRESSURE, Quick Response		
VK319	5.6	Micromatic®-HP, Horiz Sidewall, Glass Bulb, ½" NPT (p/n 12285JN_)

VIKING - EXTENDED COVERAGE SPRINKLERS (w/ ENT Coating)		
SIN	K	Description
Extended Coverage, Upright		
VK532	11.2	EC-ELO, Upright, Glass Bulb, ¾" NPT (p/n 08687JN_) - LH/OH
VK570	14.0	EC-ELO, Upright, Glass Bulb, ¾" NPT (p/n 13840JN_) - LH/OH
Extended Coverage, Pendant		
VK534	11.2	EC-ELO, Pendant, Glass Bulb, ¾" NPT (p/n 08340JN_) - LH/OH
VK608	11.2	EC-ELO, Pendant, Glass Bulb, ¾" NPT (p/n 08339JN_) - LH
VK572	14.0	EC-ELO, Pendant, Glass Bulb, ¾" NPT (p/n 13722JN_) - OH
Extended Coverage, Horizontal Sidewall		
VK630	8.0	EC, Horizontal Sidewall, Glass Bulb, ¾" NPT (p/n 13500JN_) - LH
Extended Coverage, Domed Concealed, Sidewall		
VK630-D	8.0	EC, Domed Cnclد HSW, Glass Bulb, ¾" NPT (p/n 13500JN_X) - LH

VIKING - ELO/STORAGE SPRINKLERS (w/ ENT Coating)		
SIN	K	Description
Extra Large Orifice (ELO), Upright		
VK530	11.2	Standard Response, Upright, Glass Bulb, ¾" NPT (p/n 09679JN_)
VK531	11.2	Quick Response, Upright, Glass Bulb, ¾" NPT (p/n 10633JN_)
Extra Large Orifice (ELO), Pendant		
VK536	11.2	Standard Response, Pendant, Glass Bulb, ¾" NPT (p/n 07961JN_)
VK377	11.2	Quick Response, Pendant, Glass Bulb, ¾" NPT (p/n 08337JN_)

VIKING - DRY BARREL SPRINKLERS (w/ ENT Coating)		
SIN	K	Description
Standard Response, Pendant (Dry Sprinkler)		
VK150	5.6	Pendant, Glass Bulb, Plain Barrel, 1" NPT (p/n 07852UJN_)
VK154	5.6	Pendant, Glass Bulb, Standard Adj, 1" NPT (p/n 07740UJN_)
VK158	5.6	Pendant, Glass Bulb, Recessed Adj, 1" NPT (p/n 06530UJN_)
VK166	8.0	Pendant, Glass Bulb, Plain Barrel, 1" NPT (p/n 12741UJN_)
VK163	8.0	Pendant, Glass Bulb, Standard Adj, 1" NPT (p/n 12810UJN_)
VK164	8.0	Pendant, Glass Bulb, Recessed Adj, 1" NPT (p/n 12811UJN_)
Standard Response, Horizontal Sidewall (Dry Sprinkler)		
VK152	5.6	HSW, Glass Bulb, Plain Barrel, 1" NPT (p/n 07858UJN_)
VK156	5.6	HSW, Glass Bulb, Standard Adj, 1" NPT (p/n 07857UJN_)
VK162	5.6	HSW, Glass Bulb, Recessed Adj, 1" NPT (p/n 07856UJN_)
VK250	8.0	HSW, Glass Bulb, Plain Barrel, 1" NPT (p/n 13173UJN_) - OH
VK254	8.0	HSW, Glass Bulb, Recessed Adj, 1" NPT (p/n 13174UJN_) - OH
Quick Response, Horizontal Sidewall (Dry Sprinkler)		
VK277	8.0	HSW, Glass Bulb, Standard Adj, 1" NPT (p/n 13169UJN_) - OH

VIKING - RESIDENTIAL SPRINKLERS (w/ ENT Coating)		
SIN	K	Description
Pendant		
VK470	3.0	Freedom®, Pendant, Glass Bulb, ½" NPT (p/n 17147JN_)
VK430	4.3	Freedom®, Pendant, Glass Bulb, ½" NPT (p/n 09530JN_)
VK468	4.9	Freedom®, Pendant, Glass Bulb, ½" NPT (p/n 13637JN_)
VK466	5.2	Freedom®, Pendant, Glass Bulb, ½" NPT (p/n 13781JN_)
VK472	5.8	Freedom®, Pendant, Glass Bulb, ½" NPT (p/n 16130JN_)
VK458	7.4	Freedom®, Pendant, Glass Bulb, ¾" NPT (p/n 13230JN_)
Domed Concealed, Pendant		
VK468-D	4.9	Freedom®, Domed Cnclد Pendant, Glass Bulb, ½" NPT (p/n 13637JN_X)
VK466-D	5.2	Freedom®, Domed Cnclد Pendant, Glass Bulb, ½" NPT (p/n 13781JN_X)
VK458-D	7.4	Freedom®, Domed Cnclد Pendant, Glass Bulb, ¾" NPT (p/n 13230JN_X)
Horizontal Sidewall		
VK486	4.0	Freedom®, Horizontal Sidewall, Glass Bulb, ½" NPT (p/n 17315JN_)
VK484	4.2	Freedom®, Horizontal Sidewall, Glass Bulb, ½" NPT (p/n 16240JN_)
VK460	5.8	Freedom®, Horizontal Sidewall, Glass Bulb, ½" NPT (p/n 13933JN_)
Flat Plate Concealed, Pendant		
VK457	4.9	Freedom®, Flat Cnclد Pendant, Fusible Link, ½" NPT (p/n 14694JN_)
VK474	5.8	Freedom®, Flat Cnclد Pendant, Fusible Link, ½" NPT (p/n 15790JN_)
Flat Plate Concealed, Horizontal Sidewall		
VK480	4.0	Freedom®, Flat Cnclد HSW, Fusible Link, ½" NPT (p/n 16116JN_)

Additional Information:

- ▶ To order, add suffix "JN" to the base part number, then add temperature suffix.
- ▶ Suffix "JN" is used for the "Electroless Nickel Teflon" finish.
- ▶ Refer to each sprinkler's page of the Viking List Price Book for additional information, including part numbers and list prices.
- ▶ Viking's Electroless Nickel Teflon® (ENT) finish has been investigated for installations in corrosive environments and is cULus Listed and FM Approved as corrosion resistant as indicated in the appropriate sprinkler technical data pages, and technical bulletin F_112712, which is available on Viking's web site (www.vikinggroupinc.com)

** Teflon is a registered trademark of Dupont*