

# Red Rubber Flange Accessory Packs

Class 125 & Class 250

**UNITED  
BRAND**

## Red Rubber Ring and Full Face

Flange Size	1/8" Full Face Red Rubber	1/8" Ring Type Red Rubber
1"	FRP-010-*	RRP-010-*
1-1/4"	FRP-012-*	RRP-012-*
1-1/2"	FRP-015-*	RRP-015-*
2"	FRP-020-*	RRP-020-*
2-1/2"	FRP-025-*	RRP-025-*
3"	FRP-030-*	RRP-030-*
4"	FRP-040-*	RRP-040-*
5"	FRP-050-*	RRP-050-*
6"	FRP-060-*	RRP-060-*
8"	FRP-080-*	RRP-080-*
10"	FRP-100-*	RRP-100-*
12"	FRP-120-*	RRP-120-*
14"	FRP-140-*	RRP-140-*
16"	FRP-160-*	RRP-160-*
18"	FRP-180-*	RRP-180-*
20"	FRP-200-*	RRP-200-*
24"	FRP-240-*	RRP-240-*
30"	FRP-300-*	RRP-260-*
36"	FRP-360-*	RRP-280-*
42"	FRP-420-*	RRP-300-*
48"	FRP-480-*	RRP-340-*



**Red Rubber Flange Gaskets - Full Face and Ring Type to fit ANSI B16.1-Class 125 Flanges.**

**Reference Standard:** ANSI B16.1 - Flange Dimensions - Class 125

**Material Standard:** Red Rubber - ASTM D1330, Grade II, SBR/Durometer 75+/-5 Shore A/Red Color

### Heavy Hex Head Bolts and Nuts

**Reference Standard:** Heavy hex head steel bolts to ANSI B18.2.1 with heavy hex steel nuts to ANSI B18.2.2. Bolts to be threaded to ANSI B1.1 unified inch screw threads, Class 2A external & Class 2B internal.

**Material Standard:** to conform to ASTM A307 specification for carbon steel externally threaded standard fasteners, Grade B. Zinc plated - ASTM B633, Stainless Steel 304 & 316 Bolts - AASTM F593 Stainless Steel 302 & 316 Nuts - ASTM F594

\*Add suffix:

"Z" for Zinc Plated.

"304" for 304 Stainless Steel

"316" for 316 Stainless Steel

"250" for Zinc Class 250 Flange Accessories



**NAPAC, Inc.**

229 Southbridge Street, Worcester, MA 01608 U.S.A.

Tel: (800) 807-2215 • Fax: (800) 807-2214 • [www.napacinc.com](http://www.napacinc.com)

0113