



Residential | VK467 Freedom® Residential Upright Sprinkler

The First and Only Residential Upright Sprinkler

Viking's new Freedom® Model VK467 is the industry's only available residential sprinkler in an upright configuration. Perfectly suited for loft-style residential applications where the system's piping network is exposed, the VK467 has a K factor of 4.9 (71) and is approved for up to a 16 x 16 ft. (4.9m x 4.9m) area of coverage.

- UL Listed for installation in any type of residential occupancy.
- Easier installation, more efficient hydraulic design, and a lower cost sprinkler system overall.
- Can provide the residential design advantage in an NFPA 13 application.
- Can be installed below beams of up to 14 in (35cm) in depth and is available in 155°F (68°C) and 175°F (79°C) temperature ratings.
- The VK467 can be installed on steel sprinkler piping without offsets.
- Available in several standard finishes, including Viking's new ENT coating for corrosion resistant applications.

Contact your local Viking SupplyNet team for pricing today!

Model Number: VK467

Base Part Number: 19154

Listings/Approvals: cULus, NYC

K Factor: 4.9 (71)

Approved Coverage: 16 x 16 ft.
(4.9 x 4.9m)

Connection: Threaded: 1/2" NPT

Temperature: 155° F (68°C)
175° F (79°C)

Operating Element: Glass Bulb

Finish: Brass/Chrome/White or
Black Polyester/
ENT Coating

Item Price Group: V15.6

Occupancy/Hazard: Residential

Technical Datasheet: Sprinkler 158a

The Viking Corporation

210 N Industrial Park Drive, Hastings, Michigan 49058

Telephone: (800) 968-9501

Email: products@vikingcorp.com

www.vikinggroupinc.com

Trusted above all.™

