

**Quick Response
Standard Coverage
Fusible Link
Light/Ordinary Hazard
Concealed Sidewall**



SIN: VK481
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 17555A

Finish	Temp	Part #	IPG	List Price
Standard Brass	165°F	17555AC	V127	\$102.77
Standard Brass	220°F	17555AF	V127	\$102.77
Heavy Duty Spk Wrench		16208W/R	V207	\$137.03
Head Cabinet Wrench		16267	V207	\$28.09

Cover plate sold separately (see below)

VK481 Cover Plate¹

Diameter = 3-5/16 inches



Finish	Temp	Part #	IPG	List Price
White	135°F	16207MA/W	V213	\$38.31
White	165°F	16207MC/W	V213	\$38.31
Cover Plate Installation Tool		14867	V205	\$12.37

**Horizon® Flush (Model H-1)²
Quick Response
Standard Coverage
Fusible Link**



SIN: VK402⁴
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 06702B

Finish	Temp	Part #	IPG	List Price
Chrome	165°F	06702BFC	V128	\$76.48
Painted White	165°F	06702BMC/W	V128	\$77.83
Heavy Duty Spk Wrench		08336W/B	V207	\$137.03
Light Duty Spk Wrench		10366W/B	V207	\$32.40

**NEW! Flush Pendent³
Quick Response
Standard Coverage
Fusible Link**



SIN: VK478⁴
K Factor: 5.6 (81)
Thread Size: 1/2 inch NPT
Base Part #: 19995

Finish	Temp	Part #	IPG	List Price
Painted White	165°F	19995MC/W	V128	\$69.10
Painted White	205°F	19995ME/W	V128	\$69.10
RAL9010/Pure White	165°F	19995MC/RAL9010	V128	\$76.78
RAL9010/Pure White	205°F	19995MC/RAL9010	V128	\$76.78
Heavy Duty Spk Wrench		15209W/R	V207	\$137.03

(1) Cover plates sold separately. Covers are also available in custom colors at an additional charge (see pg. F-8)

(2) Ceiling rings for Horizon Model H-1 flush pendent sprinklers (VK402) are sold separately.

(3) Ceiling rings for new Model VK478 flush pendent sprinklers are INCLUDED with the sprinkler.

(4) See page H-8 for ceiling rings for both the Horizon Model H-1 (VK402) and the new Model VK478 flush pendent sprinkler.