

Sprinkler Index and Reference Guide

<u>Model / SIN</u>	<u>Price Book Page Number</u>	<u>Technical Data Form Number</u>	<u>Base Part Number</u>	<u>K Factor</u>	<u>Product Description</u>
VK001	A1		13006	4.2	Standard Response Model M Upright, Small Orifice, 1/2" NPT
VK002	A2		10219	4.2	Standard Response Model M Upright, Small Orifice, 1/2" NPT
VK003	A1		12994	2.8	Standard Response Model M Pendent, Small Orifice, 1/2" NPT
VK004	A2		10222	4.2	Standard Response Model M Pendent, Small Orifice, 1/2" NPT
VK006	A10		05574	4.2	Standard Response Model M Fusible Link Upright, Small Orifice, 1/2" NPT
VK008	A10		05575	4.2	Standard Response Model M Fusible Link Pendent, Small Orifice, 1/2" NPT
VK015	A14		09997	2.8	HP Standard Response Model M Horizontal Sidewall, Small Orifice, 1/2" NPT
VK021	A12		09995	2.8	HP Standard Response Model M HP Upright, Small Orifice, 1/2" NPT
VK023	A12		09994	2.8	HP Standard Response Model M HP Pendent, Small Orifice, 1/2" NPT
VK100	A3, A15, E2		12986	5.6	Standard Response Model M Upright, Standard Orifice, 1/2" NPT
VK102	A8, A15		12987	5.6	Standard Response Model M Pendent, Standard Orifice, 1/2" NPT
VK102-D	A8		12987A-X	5.6	Standard Response Domed Concealed Pendent, Standard Orifice, 1/2" NPT
VK104	A7		12995	5.6	Standard Response Model M Horizontal Sidewall, Standard Orifice, 1/2" NPT
VK106	A7		12996	5.6	Standard Response Model M Vertical Sidewall, Standard Orifice, 1/2" NPT
VK108	A10, E2		12973	5.6	Standard Response Model M Fusible Element Upright, Standard Orifice, 1/2" NPT
VK110	A10, E2		12972	5.6	Standard Response Model M Fusible Element Pendent, Standard Orifice, 1/2" NPT
VK112	A11, E2		12974	5.6	Standard Response Model M Fusible Element Horizontal Sidewall, Standard Orifice, 1/2" NPT
VK116	A14		09849	5.6	HP Standard Response Model M-5 HSW, Standard Orifice, 1/2" NPT
VK118	A6		19383	5.6	Standard Response Model M Conventional, Standard Orifice, 1/2" NPT
VK120	A6		10228	8.0	Standard Response Model M Conventional, Large Orifice, 3/4" NPT
VK122	A13, A16		09992	5.6	HP Standard Response Model M HP Pendent, Standard Orifice, 1/2" NPT
VK124	A14		09993	5.6	HP Standard Response Model M HP Upright, Standard Orifice, 1/2" NPT
VK130	A16		05012B	5.6	Standard Response Model N-2 Stainless Steel Upright, Standard Orifice, 1/2" NPT
VK132	A16		06483B	5.6	Standard Response Model N-2 Stainless Steel Pendent, Standard Orifice, 1/2" NPT
VK134	E3		09224	5.6	Special Response Pendent, Standard Orifice, 1/2" NPT
VK136			09225	5.6	Special Response Conventional, Standard Orifice, 1/2" NPT
VK138	E3		09226	5.6	Special Response Upright, Standard Orifice, 1/2" NPT
VK150	G2		07852	5.6	Standard Response Model M Plain Barrel Dry Pendent, Standard Orifice, 1" NPT
VK152	G3		07858	5.6	Standard Response Model M Plain Barrel Dry Horizontal Sidewall, Standard Orifice, 1" NPT
VK153	G6		09125	5.6	Standard Response Model M Plain Barrel Dry Vertical Sidewall, Standard Orifice, 1" NPT
VK154	G2		07740	5.6	Standard Response Model M Adjustable Standard Dry Pendent, Standard Orifice, 1" NPT
VK156	G3		07857	5.6	Standard Response Model M Adjustable Std Dry Horizontal Sidewall, Standard Orifice, 1" NPT
VK157	G6		09123	5.6	Standard Response Model M Adjustable Std Dry Vertical Sidewall, Standard Orifice, 1" NPT
VK158	G2		06530	5.6	Standard Response Model M Adjustable Recessed Dry Pendent, Standard Orifice, 1" NPT
VK160	G1		08050	5.6	Standard Response Model M Plain Barrel Dry Upright, Standard Orifice, 1" NPT
VK161	G6		09124	5.6	Standard Response Model M Adjustable Recessed Dry Vertical Sidewall, Std Orifice, 1" NPT
VK162	G3		07856	5.6	Standard Response Model M Adjustable Recessed Dry Horizontal Sidewall, Std Orifice, 1" NPT
VK163	G4		12810	8.0	Standard Response Model M Adjustable Standard Dry Pendent, Large Orifice, 1" NPT
VK164	G4		12811	8.0	Standard Response Model M Adjustable Recessed Dry Pendent, Large Orifice, 1" NPT
VK166	G4		12741	8.0	Standard Response Model M Plain Barrel Dry Pendent, Large Orifice, 1" NPT
VK168	G7		09798	5.6	Standard Response Model M Stainless Steel Plain Barrel Dry Pendent, Std Orifice, 1" NPT
VK169	G7		10360	5.6	Standard Response Model M Stainless Steel Adj Recessed Dry Pendent, Std Orifice, 1" NPT
VK172	G9		08387	5.6	Quick Response Model M Plain Barrel Dry Pendent, Standard Orifice, 1" NPT
VK173	G11		13248	8.0	Quick Response Ordinary Hazard Plain Barrel Dry Pendent, Large Orifice, 1" NPT
VK174	G10		08388	5.6	Quick Response Model M Plain Barrel Dry HSW, Standard Orifice, 1" NPT
VK176	G9		08383	5.6	Quick Response Model M Adjustable Standard Dry Pendent, Standard Orifice, 1" NPT

Sprinkler Index and Reference Guide

<u>Model / SIN</u>	<u>Price Book Page Number</u>	<u>Technical Data Form Number</u>	<u>Base Part Number</u>	<u>K Factor</u>	<u>Product Description</u>
VK177	G11		13249	8.0	Quick Response Ordinary Hazard Adjustable Standard Dry Pendant, Large Orifice, 1" NPT
VK178	G10		08384 and 11494	5.6	Quick Response Model M Adjustable Standard Dry Horizontal Sidewall, Std Orifice, 1" NPT
VK180	G9		08385	5.6	Quick Response Model M Adjustable Recessed Dry Pendant, Standard Orifice, 1" NPT
VK181	G11		13250	8.0	Quick Response Ordinary Hazard Adjustable Recessed Dry Pendant, Large Orifice, 1" NPT
VK182	G10		08386	5.6	Quick Response Model M Adjustable Recessed Dry Horizontal Sidewall, Std Orifice, 1" NPT
VK184	G1		08417A	5.6	Quick Response Model M Dry Upright, Standard Orifice, 1" NPT
VK188	G15		10542	5.6	Standard Response/Quick Response Extended Coverage Model M Adjustable Recessed Dry Horizontal Sidewall, Standard Orifice, 1" NPT
VK190	G8		12421A	5.6	Standard Response Dry Concealed Pendant, Standard Orifice, 1" NPT
VK192	G8		12424A	8.0	Standard Response Dry Concealed Pendant, Large Orifice, 1" NPT
VK194	G16		12422A	5.6	Quick Response Dry Concealed Pendant, Standard Orifice, 1" NPT
VK196	G16		12423A	5.6	Standard/QR EC Dry Concealed Pendant, Standard Orifice, 1" NPT
VK200	A4, A5, A15		18263	8.0	Standard Response Model M Upright, Large Orifice, 3/4" NPT
VK202	A4-5, A15		18264	8.0	Standard Response Model M Pendant, Large Orifice, 3/4" NPT
VK202-D	A8		18264A-X	8.0	Standard Response Domed Concealed Pendant, Large Orifice, 3/4" NPT
VK204	A11		18255	8.0	Standard Response Model M Fusible Link Upright, Large Orifice, 3/4" NPT
VK206	A11		18256	8.0	Standard Response Model M Fusible Link Pendant, Large Orifice, 3/4" NPT
VK250	G5		13173	8.0	Standard Response Ordinary Hazard Plain Barrel Dry HSW, Large Orifice, 1" NPT
VK252	G5		13172	8.0	Standard Response Ordinary Hazard Adjustable Standard Dry HSW, Large Orifice, 1" NPT
VK254	G2		13174	8.0	Standard Response Ordinary Hazard Adjustable Recessed Dry HSW, Large Orifice, 1" NPT
VK275	G12		13170	8.0	Quick Response Ordinary Hazard Plain Barrel Dry HSW, 1" NPT
VK277	G12		13169	8.0	Quick Response Ordinary Hazard Adjustable Standard Dry HSW, 1" NPT
VK279	G12		13171	8.0	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW, 1" NPT
VK282	G13		13254	8.0	Quick Response Plain Barrel Dry Pendant Fusible Link, Large Orifice, 1" NPT
VK284	G14		13239	8.0	Quick Response Ordinary Hazard Plain Barrel Dry HSW Fusible Link, Large Orifice, 1" NPT
VK286	G13		13255	8.0	Quick Response Adjustable Standard Dry Pendant Fusible Link, Large Orifice, 1" NPT
VK288	G14		13240	8.0	Quick Response Ordinary Hazard Adjustable Std Dry HSW Fusible Link, Large Orifice, 1" NPT
VK290	G13		13256	8.0	Quick Response Adjustable Recessed Dry Pendant Fusible Link, Large Orifice, 1" NPT
VK292	G14		13241	8.0	Quick Response Ordinary Hazard Adjustable Recessed Dry HSW Fusible Link, Large Orifice, 1" NPT
VK300	B3, E2		12978	5.6	Quick Response Model M Upright, Standard Orifice, 1/2" NPT
VK301	B14		17535	5.6	Quick Response Fusible Element Upright, Standard Orifice, 1/2" NPT
VK302	B3, E2,		12979	5.6	Quick Response Model M Pendant, Standard Orifice, 1/2" NPT
VK302	B9		12979BA-X	5.6	Quick Response Concealed Pendant, Standard Orifice, 1/2" NPT
VK303	B14,		17536	5.6	Quick Response Fusible Element Pendant, Standard Orifice, 1/2" NPT
VK305	B8, E2		12997	5.6	Model M-5 Quick Response Horizontal Sidewall, 1/2" NPT
VK306	B8		12983	5.6	Quick Response Model M Vertical Sidewall, Standard Orifice, 1/2" NPT
VK310	B6		19391	5.6	Quick Response Model M Conventional, Standard Orifice, 1/2" NPT
VK315	B20		12281	5.6	HP Quick Response Model M Upright, Standard Orifice, 1/2" NPT
VK317	B20		12282	5.6	HP Quick Response Model M Pendant, Standard Orifice, 1/2" NPT
VK319	B21		12285	5.6	HP Model M-5 Quick Response Horizontal Sidewall, 1/2" NPT
VK325	B1, E2		12980	2.8	Quick Response Model M Upright, Small Orifice, 1/2" NPT
VK327	B2		06719B	4.2	Quick Response Model M Upright, Small Orifice, 1/2" NPT
VK329	B1, E2		12981	2.8	Quick Response Model M Pendant, Small Orifice, 1/2" NPT
VK331	B2		06720B	4.2	Quick Response Model M Pendant, Small Orifice, 1/2" NPT
VK333	B7		10035	2.8	Quick Response Model M Horizontal Sidewall, Small Orifice, 1/2" NPT
VK338	B20		14692	5.6	Quick Response Stainless Steel Upright 1/2" NPT
VK339	B20		14693	5.6	Quick Response Stainless Steel Pendant 1/2" NPT
VK340	B19		12286	2.8	HP Quick Response Model M Upright, Small Orifice, 1/2" NPT
VK342	B19		12290	2.8	HP Quick Response Model M Pendant, Small Orifice, 1/2" NPT
VK344	B21		12287	2.8	HP Quick Response Model M Horizontal Sidewall, Small Orifice, 1/2" NPT
VK350	B4		18257	8.0	Quick Response Model M Upright, Large Orifice, 3/4" NPT
VK352	B9		18258	8.0	Quick Response Model M Pendant . Domed Concealed Pendant, Large Orifice, 3/4" NPT
VK354	B6		18261	8.0	Quick Response Model M Conventional, Large Orifice, 3/4" NPT
VK360	B8		15591	8.0	Quick Response Horizontal Sidewall, Glass Bulb, 3/4" NPT
VK377	D4		08337	11.2	Quick Response Model M ELO Pendant, Extra-Large Orifice, 3/4" NPT
VK400	A8		06697B	5.6	Standard Response Model H Fusible Link Flush Pendant, Std. Orifice, 1/2" NPT

Sprinkler Index and Reference Guide

Model / SIN	Price Book Page Number	Technical Data Form Number	Base Part Number	K Factor	Product Description
VK402	B9		06702B	5.6	Quick Response Model H-1 Fusible Link Flush Pendent, Standard Orifice, 1/2" NPT
VK408	B13		11262A	5.6	Quick Response Concealed Horizontal Sidewall Sprinkler, Std. Orifice, 1/2" NPT
VK410	E1		10554	5.6	Quick Response Model HQR-2 Fusible Link Flush Pendent,
VK412	E1		10579	5.6	Quick Response Model HQR-2 Fusible Link Flush Horizontal Sidewall, Std Orifice, 1/2" NPT
VK420	F6		09458	3.8	Residential Model H-3 Fusible Link Flush Pendent, 1/2" NPT
VK430	F1, F7		09530	4.3	Residential Model M-4 Pendent, 1/2" NPT
VK435	F1		13203	3.1	Residential Pendent, 1/2" NPT
VK450	F3, F7		12357	4.2	Residential Horizontal Sidewall, 1/2" NPT
VK457	F4		14694AC	4.9	Residential Fusible Link Concealed Pendent, 1/2" NPT
VK458	F1		13230	7.4	Residential Pendent / Domed Concealed Pendent, 3/4" NPT
VK461	A9, B10, B12		13831A	2.8	Mirage® Quick Response Concealed Pendent, Small Orifice, 1/2" NPT
VK462	A9, B10, B12		13503A	5.6	Mirage® Quick Response Concealed Pendent, Standard Orifice, 1/2" NPT
VK463	B10		13667A	5.6	Mirage®HP QR Concealed Pendent, Standard Orifice, 1/2" NPT
VK464	B10		13614A	8.0	Mirage® Quick Response Concealed Pendent, Large Orifice, 3/4" NPT
VK465	B10		14262A	4.2	Mirage® Quick Response Concealed Pendent, Standard Orifice, 1/2" NPT
VK466	F1, F7		13781	5.2	Freedom® residential pendent sprinkler, 1/2" NPT
VK467	F5		19154	4.9	Freedom® residential upright sprinkler VK467, 1/2" NPT
VK468	F1, F7		13637	4.9	Freedom® residential pendent sprinkler, 1/2" NPT
VK469	B10		15764A	11.2	Quick Response Concealed Pendent Sprinkler, 3/4" NPT
VK470	F1		17147	3.0	Freedom® residential pendent sprinkler, 1/2" NPT
VK472	F1		16130	5.8	Residential Glass Bulb Pendent, 1/2" NPT
VK474	F4		15790AC	5.8	Residential Concealed Pendent, 1/2" NPT
VK476	F6		15630	4.9	Residential Flush Pendent, 1/2" NPT
VK480	F5		16116AC	4.0	Residential Flat Plate Concealed Horizontal Sidewall, 1/2" NPT
VK481	B13		17555	5.6	QR Concealed Horizontal Sidewall Sprinkler - Light and Ordinary Hazard
VK482	G17		18385	5.6	QR Recessed Flush Dry Sprinkler 1" NPT
VK484	F3		16240	4.2	Residential Horizontal Sidewall, 1/2" NPT
VK486	F3		17315	4.0	Residential Horizontal Sidewall, 1/2" NPT
VK488	F4		18325AC	3.0	Freedom® residential pendent sprinkler, 1/2" NPT
VK500	D1		10284	14.0	Model S-1 ESFR Pendent, 3/4" NPT
VK502	D2		18176	14.0	ESFR Dry Barrel Pendent, 1-1/2" or 2" NPT
VK503	D1		14073	16.8	K17 ESFR Pendent, 3/4" NPT
VK504	D2		19015	16.8	ESFR Dry Barrel Pendent, 1-1/2" or 1-1/2" NPT
VK506	D1		18493	22.4	K22 ESFR Pendent, 1" NPT
VK510	D1		12080	25.2	K25 ESFR Pendent, 1" NPT
VK514	D1		19591	28.0	K28 Specific Application ESFR Pendent, 1" NPT
VK520	D1		10625	14.0	Model A-4 ESFR Upright, 3/4" NPT
VK530	D3		09679	11.2	Standard Response Model M ELO Upright (Special App.), 3/4" NPT
VK531	D3		10633	11.2	Model M Quick Response ELO Upright (Special App), 3/4" NPT
VK532	C2		08687	11.2	Standard Response ECOH Model M ELO Upright, 3/4" NPT
VK534	C2		08340	11.2	Standard and QR ECOH Model M ELO Pendent, 3/4" NPT
VK536	D4		07961	11.2	Standard Response Model M ELO Upright (Special Application) and Pendent, 3/4" NPT
VK538	C7		17115A	11.2	Mirage ELO Concealed Pendent Sprinkler, 3/4" NPT (Ord Hazard)
VK540	D2		13166/7	11.2	Model A-2 Standard Response High Challenge® Upright Large Drop, ELO, 3,4" NPT, 1/2" NPT
VK550	D5		12986--U	5.6	Standard Response Model M Upright Intermediate Level, Standard Orifice, 1/2" NPT
VK551	D5, D7		12279--U	5.6	Quick Response Fusible Element Upright Intermediate Level, Standard Orifice, 1/2" NPT
VK552	D5		12973--U	5.6	Standard Response Model M Fusible Link Upright Intermediate Level, Std Orifice, 1/2" NPT
VK556	D5		12978B--U	5.6	Quick Response Model M Upright Intermediate Level, Standard Orifice, 1/2" NPT
VK558	D5		12281--U	5.6	HP Quick Response Model M Upright Intermediate Level, Standard Orifice, 1/2" NPT
VK560	D5		18263--U	8.0	Standard Response Model M Upright Intermediate Level, Large Orifice, 3/4" NPT
VK560	D5		12986--U	8.0	Standard Response Model M Upright Intermediate Level, Large Orifice, 1/2" NPT
VK562	D5		18253--U	8.0	Standard Response Model M Fusible Link Upright Intermediate Level, Large Orifice, 3/4" NPT
VK566	D5		18257B--U	8.0	Quick Response Model M Upright Intermediate Level, Large Orifice, 3/4" NPT
VK570	C3		13840	14.0	Extended Coverage Ordinary Hazard Upright, 3/4" NPT
VK572	C3		13722	14.0	Extended Coverage Ordinary Hazard Pendent, 3/4" NPT
VK580	D3		12739A	16.8	Standard Response Upright, 3/4" NPT
VK592	D2		14243A	19.6	Control Mode Specific App, Standard Response, Fusible Link, Pendent, 1" NPT
VK595	D3		16859A	25.2	Extended Coverage, Area/Density Storage, Upright, 1" NPT

Sprinkler Index and Reference Guide

Model / SIN	Price Book Page Number	Technical Data Form Number	Base Part Number	K Factor	Product Description
VK600	C1		06778B	5.6	Standard Response/Quick Response Model M Ext Coverage Pendant, Std Orifice, 1/2" NPT
VK602	C1		18262	8.0	Standard Response/Quick Response Model M Extended Coverage Pendant, Large Orifice, 3/4" NPT
VK604	C1		10335	5.6	Standard Response/Quick Response Model M-5 ExtCoverage Pendant, Std Orifice, 1/2" NPT
VK605	C4		12120	5.6	Model M-5 HSW (with EC, QREC, and Specific Application Listings), 1/2" NPT
VK606	C4		18271	8.0	Standard Response/Quick Response Model M Extended Coverage Horizontal Sidewall, Large Orifice, 3/4" NPT
VK608	C2		08339	11.2	Standard Response/Quick Response Model M Extended Coverage Light Hazard Extra-Large Orifice Pendant, 3/4" NPT
VK610	C1		12294	5.6	HP Standard Response/Quick Response Model M-5 Extended Coverage Pendant, Standard Orifice, 1/2" NPT
VK612	C4		12295	5.6	HP Standard Response/Quick Response Model M-5 EC HSW, 1/2" NPT
VK614	C6		06778B	5.6	Standard Response/Quick Response Extended Coverage Pendant/Domed Concealed Pendant, Standard Orifice, 1/2" NPT
VK616	C6		07077B	8.0	Standard Response/Quick Response Extended Coverage Pendant/Domed Concealed Pendant, Standard Orifice, 3/4" NPT
VK618	C6		08339_	11.2	Standard Response/Quick Response Extended Coverage Pendant/Domed Concealed Pendant, Standard Orifice, 3/4" NPT
VK630	C5		13500	8.0	Quick Response Extended Coverage Concealed HSW, Large Orifice, 3/4" NPT
VK632	C7		14613A	5.6	Quick Response Extended Coverage, Fusible Link, Standard Orifice, Concealed Pendant, 1/2" NPT (Light Hazard)
VK634	C7		14535A	8.0	Quick Response Extended Coverage Fusible Link, Large Orifice, Concealed Pendant, 3/4" NPT (Light Hazard)
VK636	C7		16102A	11.2	Quick Response ELO Extended Coverage Fusible Link, Concealed Pendant, 3/4" NPT (Light Hazard)
VK638	C5		17375	8.0	Quick Response Extended Coverage HSW (Wide Throw / Corridor Spk)
VK680	C7		17114AC	8.0	Quick Response Extended Coverage HSW (Flat Plate Concealed)
VK700	11-12		16948	5.6	60° Model M Spray Nozzle, 1/2" Orifice, 1/2" NPT
VK701	11-12		16949	5.6	90° Model M Spray Nozzle, 1/2" Orifice, 1/2" NPT
VK702	11-12		16950	5.6	120° Model M Spray Nozzle, 1/2" Orifice, 1/2" NPT
VK703	11-12		16951	5.6	150° Model M Spray Nozzle, 1/2" Orifice, 1/2" NPT
VK705	11-12		16952	4.2	60° Model M Spray Nozzle, 7/16" Orifice, 1/2" NPT
VK706	11-12		16953	4.2	90° Model M Spray Nozzle, 7/16" Orifice, 1/2" NPT
VK707	11-12		16954	4.2	120° Model M Spray Nozzle, 7/16" Orifice, 1/2" NPT
VK708	11-12		16955	4.2	150° Model M Spray Nozzle, 7/16" Orifice, 1/2" NPT
VK710	11-12		16956	2.8	60° Model M Spray Nozzle, 3/8" Orifice, 1/2" NPT
VK711	11-12		16957	2.8	90° Model M Spray Nozzle, 3/8" Orifice, 1/2" NPT
VK712	11-12		16958	2.8	120° Model M Spray Nozzle, 3/8" Orifice, 1/2" NPT
VK713	11-12		16959	2.8	150° Model M Spray Nozzle, 3/8" Orifice, 1/2" NPT
VK715	11-12		16960	1.9	60° Model M Spray Nozzle, 5/16" Orifice, 1/2" NPT
VK716	11-12		16961	1.9	90° Model M Spray Nozzle, 5/16" Orifice, 1/2" NPT
VK717	11-12		16962	1.9	120° Model M Spray Nozzle, 5/16" Orifice, 1/2" NPT
VK718	11-12		16963	1.9	150° Model M Spray Nozzle, 5/16" Orifice, 1/2" NPT
VK720	11-12		16964	1.4	60° Model M Spray Nozzle, 1/4" Orifice, 1/2" NPT
VK721	11-12		16965	1.4	90° Model M Spray Nozzle, 1/4" Orifice, 1/2" NPT
VK722	11-12		16966	1.4	120° Model M Spray Nozzle, 1/4" Orifice, 1/2" NPT
VK723	11-12		16967	1.4	150° Model M Spray Nozzle, 1/4" Orifice, 1/2" NPT
VK740	11-12		05133AAJ	1.2	30° Model A-2 Spray Nozzle, 1/2" NPT, Brass
VK741	11-12		05133AAK	1.2	60° Model A-2 Spray Nozzle, 1/2" NPT, Brass
VK742	11-12		05133AAL	1.2	90° Model A-2 Spray Nozzle, 1/2" NPT, Brass
VK743	11-12		05133AAM	1.4	120° Model A-2 Spray Nozzle, 1/2" NPT, Brass
VK744	11-12		05133AAN	1.4	140° Model A-2 Spray Nozzle, 1/2" NPT, Brass
VK745	11-12		05133AJJ	1.2	30° Model A-2 Spray Nozzle, 1/2" NPT, Nickel
VK746	11-12		05133AJK	1.2	60° Model A-2 Spray Nozzle, 1/2" NPT, Nickel
VK747	11-12		05133AJL	1.2	90° Model A-2 Spray Nozzle, 1/2" NPT, Nickel
VK748	11-12		05133AJM	1.4	120° Model A-2 Spray Nozzle, 1/2" NPT, Nickel
VK749	11-12		05133AJN	1.4	140° Model A-2 Spray Nozzle, 1/2" NPT, Nickel
VK750	11-12		05134AAJ	2.0	30° Model A-2X Spray Nozzle, 1/2" NPT, Brass
VK751	11-12		05134AAK	2.0	60° Model A-2X Spray Nozzle, 1/2" NPT, Brass
VK752	11-12		05134AAL	2.0	90° Model A-2X Spray Nozzle, 1/2" NPT, Brass
VK753	11-12		05134AAM	2.2	120° Model A-2X Spray Nozzle, 1/2" NPT, Brass
VK754	11-12		05134AAN	2.2	140° Model A-2X Spray Nozzle, 1/2" NPT, Brass
VK755	11-12		05134AJJ	2.0	30° Model A-2X Spray Nozzle, 1/2" NPT, Nickel
VK756	11-12		05134AJK	2.0	60° Model A-2X Spray Nozzle, 1/2" NPT, Nickel
VK757	11-12		05134AJL	2.0	90° Model A-2X Spray Nozzle, 1/2" NPT, Nickel
VK758	11-12		05134AJM	2.2	120° Model A-2X Spray Nozzle, 1/2" NPT, Nickel
VK759	11-12		05134AJN	2.2	140° Model A-2X Spray Nozzle, 1/2" NPT, Nickel
VK760	11-12		05135AAJ	2.8	30° Model B-2 Spray Nozzle, 1/2" NPT, Brass
VK761	11-12		05135AAK	2.8	60° Model B-2 Spray Nozzle, 1/2" NPT, Brass

Sprinkler Index and Reference Guide

Model / SIN	Price Book Page Number	Technical Data Form Number	Base Part Number	K Factor	Product Description
VK762	11-12		05135AAL	2.8	90° Model B-2 Spray Nozzle, 1/2" NPT, Brass
VK763	11-12		05135AAM	3.3	120° Model B-2 Spray Nozzle, 1/2" NPT, Brass
VK764	11-12		05135AAN	3.3	140° Model B-2 Spray Nozzle, 1/2" NPT, Brass
VK765	11-12		05135AJJ	2.8	30° Model B-2 Spray Nozzle, 1/2" NPT, Nickel
VK766	11-12		05135AJK	2.8	60° Model B-2 Spray Nozzle, 1/2" NPT, Nickel
VK767	11-12		05135AJL	2.8	90° Model B-2 Spray Nozzle, 1/2" NPT, Nickel
VK768	11-12		05135AJM	3.3	120° Model B-2 Spray Nozzle, 1/2" NPT, Nickel
VK769	11-12		05135AJN	3.3	140° Model B-2 Spray Nozzle, 1/2" NPT, Nickel
VK770	11-12		19505AJ	3.4	30° Model C-2 Spray Nozzle, 1/2" NPT, Brass
VK771	11-12		19505AK	3.4	60° Model C-2 Spray Nozzle, 1/2" NPT, Brass
VK772	11-12		19505AL	3.8	90° Model C-2 Spray Nozzle, 1/2" NPT, Brass
VK772	11-12		19505AM	3.8	90° Model C-2 Spray Nozzle, 1/2" NPT, Brass
VK773	11-12		19505AN	3.9	120° Model C-2 Spray Nozzle, 1/2" NPT, Brass
VK770	11-12		19505JJ	3.4	30° Model C-2 Spray Nozzle, 1/2" NPT, Nickel
VK771	11-12		19505JK	3.4	60° Model C-2 Spray Nozzle, 1/2" NPT, Nickel
VK772	11-12		19505JL	3.8	90° Model C-2 Spray Nozzle, 1/2" NPT, Nickel
VK773	11-12		19505JM	3.9	120° Model C-2 Spray Nozzle, 1/2" NPT, Nickel
VK774	11-12		19505JN	3.9	140° Model C-2 Spray Nozzle, 1/2" NPT, Nickel
VK780	11-12		19506AJ	4.7	30° Model D-2 Spray Nozzle, 1/2" NPT, Brass
VK781	11-12		19506AK	4.7	60° Model D-2 Spray Nozzle, 1/2" NPT, Brass
VK782	11-12		19506AL	5.0	90° Model D-2 Spray Nozzle, 1/2" NPT, Brass
VK783	11-12		19506AM	5.2	120° Model D-2 Spray Nozzle, 1/2" NPT, Brass
VK784	11-12		19506AN	5.2	140° Model D-2 Spray Nozzle, 1/2" NPT, Brass
VK780	11-12		19506JJ	4.7	30° Model D-2 Spray Nozzle, 1/2" NPT, Nickel
VK781	11-12		19506JK	4.7	60° Model D-2 Spray Nozzle, 1/2" NPT, Nickel
VK782	11-12		19506JL	5.0	90° Model D-2 Spray Nozzle, 1/2" NPT, Nickel
VK783	11-12		19506JM	5.2	120° Model D-2 Spray Nozzle, 1/2" NPT, Nickel
VK784	11-12		19506JN	5.2	140° Model D-2 Spray Nozzle, 1/2" NPT, Nickel
VK790	11		01320B	1.5	Model C-1 Window Sprinkler, 1/4" Orifice, 1/2" NPT
VK791	11		01321B	2.1	Model C-1 Window Sprinkler, 5/16" Orifice, 1/2" NPT
VK792	11		01322B	3.0	Model C-1 Window Sprinkler, 3/8" Orifice, 1/2" NPT
VK793	11		01323B	4.3	Model C-1 Window Sprinkler, 7/16" Orifice, 1/2" NPT
VK794	11		01324B	5.8	Model C-1 Window Sprinkler, 1/2" Orifice, 1/2" NPT
VK795	11		01325B	7.3	Model C-1 Window Sprinkler, 5/8" Orifice, 3/4" NPT
VK796	11		01326B	8.1	Model C-1 Window Sprinkler, 3/4" Orifice, 3/4" NPT
VK800	N8		07848	-	Model M HP Fixed Temperature Release, Standard Orifice, 1/2" NPT
VK810	11-12		12867	7.2	65° Model E Spray Nozzle, 1/2" NPT
VK810	11-12		12868	5.6	65° Model E Spray Nozzle, 1/2" NPT
VK810	11-12		12869	4.1	65° Model E Spray Nozzle, 1/2" NPT
VK810	11-12		12870	3.2	65° Model E Spray Nozzle, 1/2" NPT
VK810	11-12		12871	2.3	65° Model E Spray Nozzle, 1/2" NPT
VK810	11-12		12872	1.8	65° Model E Spray Nozzle, 1/2" NPT
VK810	11-12		12873	1.2	65° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12874	7.2	80° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12875	5.6	80° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12876	4.1	80° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12877	3.2	80° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12878	2.3	80° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12879	1.8	80° Model E Spray Nozzle, 1/2" NPT
VK811	11-12		12880	1.2	80° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12881	7.2	95° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12882	5.6	95° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12883	4.1	95° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12884	3.2	95° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12885	2.3	95° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12886	1.8	95° Model E Spray Nozzle, 1/2" NPT
VK812	11-12		12887	1.2	95° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12888	7.2	110° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12889	5.6	110° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12890	4.1	110° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12891	3.2	110° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12892	2.3	110° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12893	1.8	110° Model E Spray Nozzle, 1/2" NPT
VK813	11-12		12894	1.2	110° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12895	7.2	125° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12896	5.6	125° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12897	4.1	125° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12898	3.2	125° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12899	2.3	125° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12900	1.8	125° Model E Spray Nozzle, 1/2" NPT
VK814	11-12		12901	1.2	125° Model E Spray Nozzle, 1/2" NPT
VK815	11-12		12902	7.2	140° Model E Spray Nozzle, 1/2" NPT
VK815	11-12		12903	5.6	140° Model E Spray Nozzle, 1/2" NPT
VK815	11-12		12904	4.1	140° Model E Spray Nozzle, 1/2" NPT

Sprinkler Index and Reference Guide

<u>Model / SIN</u>	<u>Price Book Page Number</u>	<u>Technical Data Form Number</u>	<u>Base Part Number</u>	<u>K Factor</u>	<u>Product Description</u>
VK815	11-12		12905	3.2	140° Model E Spray Nozzle, 1/2" NPT
VK815	11-12		12906	2.3	140° Model E Spray Nozzle, 1/2" NPT
VK815	11-12		12907	1.8	140° Model E Spray Nozzle, 1/2" NPT
VK815	11-12		12908	1.2	140° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12909	7.2	160° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12910	5.6	160° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12911	4.1	160° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12912	3.2	160° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12913	2.3	160° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12914	1.8	160° Model E Spray Nozzle, 1/2" NPT
VK816	11-12		12915	1.2	160° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12916	7.2	180° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12917	5.6	180° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12918	4.1	180° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12919	3.2	180° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12920	2.3	180° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12921	1.8	180° Model E Spray Nozzle, 1/2" NPT
VK817	11-12		12922	1.2	180° Model E Spray Nozzle, 1/2" NPT
VK900	E1		12493	4.2	COIN® QR Upright (Specific Application), Glass Bulb, 1/2" NPT
VK901	E1		12676	4.2	COIN® QR Upright (Specific Application), Fusible Link, 1/2" NPT