

SHIPPING WEIGHTS

Description	Quantity Per Carton	Pounds Per Carton	Kilograms Per Carton
Accelerator, D-2	1	7	4
Accelerator, E-1	1	8	4
Accelerator/Anti-Flood Package	1	11	5
Accelerator	1	8	4
Anti-Flood Device, Model B-1	1	3	1
Anti-Flood Device, Model B-2	1	7	4
Air Maintenance Device	1	4	1
Air Maintenance Device with Trim	1	7	3
Dehydrator Package	1	9	4
Emergency Release	1	4	2
Escutcheons, Flat	200	9	4
Escutcheons, Recessed	200	18	8
Escutcheons, Recessed E-2	200	18	8
Gate Nozzle 26"	1	130	59
Gate Nozzle 20"	1	106	48
Maintenance Air Compressor	1	43	20
VFR-400 Release Control Panel			
Batteries, 7 amp hours	1	6	3
Batteries, 12 amp hours	2	18	8
Batteries, 18 amp hours	1	13	6
VFR-400 Panel (110VAC)	1	27	12
Pneumatic Actuator, Model H-1	250	750	315
Pressure Operator Relief Valve	10	50	19
Prime Shut Off Valve	1	3	1
Retarding Chamber, C-1	10	260	103
Release Line Air Supply Assembly	1	4	2
Spray Nozzles			
A2, A2X, B2	50	49	22
C2, D2	50	60	27
Model M	50	11	5
Model E	50	49	22
Sprinklers			
COIN - Combustible Interstitial Space	50	9	4
Dry Concealed Sprinkler, 8"	10	31	14
Dry Concealed Sprinkler, 12"	10	38	17
Dry Concealed Sprinkler, 24"	10	66	30
Dry Sprinkler, 8"	10	31	14
Dry Sprinkler, 12"	10	38	17
Dry Sprinkler, 24"	10	66	30
ESFR Pendent, 14K	50	21	10
ESFR Pendent, 25K	50	24	11
ESFR Upright, 14K	50	21	10
ESFR Upright, 17K	50	13	6
Extra Large Orifice	50	15	5
Freedom® Residential Pendent	50	9	4
Freedom® Residential Concealed Pendent (for Domed)	50	11	7
Freedom® Residential Concealed Pendent (for Flat Plate)	50	23	11
Freedom® Residential Domed Cover	50	3	2
Freedom® Residential Flat Plate Cover	50	4	2
Fusible Link	200	39	18
Guard D-1	100	13	6
High Challenge, 1/2" NPT	50	29	13
High Challenge, 3/4" NPT	50	30	14
Horizon Flush	50	20	9
Horizon Mirage Concealed Pendent Sprinkler	50	23	11
Horizon Mirage Cover (Std and Large)	50	4	2
Institutional HSW	50	23	11
Institutional Escutcheon/Lockring Pkg	50	23	11
Microfast Horizontal Sidewall	50	10	5
Microfast Quick Response Ext. Coverage Pendent	50	9	4
Micromatic\Microfast, 1/2" NPT	200	36	16
Micromatic\Microfast, 3/4" NPT	200	45	20
Sprinkler with Preassembled Shield	100	24	11
Sprinkler with Preassembled Guard	100	36	16
WaterShield E-1	200	32	14
Window Sprinklers	10	5	2
Thermostatic Release	6	28	13

Description	Quantity Per Carton	Pounds Per Carton	Kilograms Per Carton
Valves			
Alarm Valve / Easy Riser Valve			
2½" and 3" G/G	1	20	9
3" F/F	1	35	16
3" F/G	1	27	12
4" F/F	1	45	20
4" F/G	1	37	17
4" G/G	1	27	12
6" F/F	1	75	34
6" F/G	1	62	28
6" G/G	1	51	23
8" F/F	1	140	64
8" F/G	1	120	54
8" G/G	1	106	48
Alarm Valve Trim, Vertical, Model J-1			
3"	1	24	11
4"	1	45	14
6"	1	32	15
8"	1	24	15
Deluge Valve			
1½" Threaded, Angle Style	1	13	6
2" Threaded, Angle Style	1	34	15
3" F/F, Angle Style	1	73	33
3" F/G, Angle Style	1	65	30
4" F/F, Angle Style	1	122	55
4" F/G, Angle Style	1	111	50
6" F/F, Angle Style	1	242	110
6" F/G, Angle Style	1	234	106
1½" Threaded, Straight Through	1	38	17
2" Threaded and 2" G/G, Straight Through	1	37	17
2½" Threaded and 2½" G/G, Straight Through	1	67	31
3" F/F, Straight Through	1	82	37
3" F/G, Straight Through	1	75	34
3" G/G, Straight Through	1	64	29
4" F/F, Straight Through	1	146	66
4" F/G, Straight Through	1	136	62
4" G/G, Straight Through	1	127	58
6" F/F, Straight Through	1	271	123
6" F/G, Straight Through	1	261	118
6" G/G, Straight Through	1	245	111
8" F/F, Straight Through	1	466	211
8" G/G, Straight Through	1	403	183
Deluge Valve Trim, Galvanized, Angle Style			
1½"	1	37	17
2" and 3"	1	32	15
4", 6" and 8"	1	38	17
Deluge Valve Trim, Galvanized, Straight Through			
2½" and 3"	1	36	16
4" and 6"	1	32	15
8"	1	45	20
Dry Valve, F-1			
3" F/F	1	129	59
3" F/G	1	125	57
4" F/F	1	143	65
4" F/G	1	132	60
6" F/F	1	197	89
6" F/G	1	188	85
Dry Valve Conventional Trim			
3"	1	26	14
4" and 6"	1	31	15
Flow Control Valve			
1½" Threaded, Angle Style	1	12	5
2" Threaded, Angle Style	1	34	15
3" F/F, Angle Style	1	72	33
3" F/G, Angle Style	1	66	30
4" F/F, Angle Style	1	123	56
4" F/G, Angle Style	1	112	50
6" F/F, Angle Style	1	251	114
6" F/G, Angle Style	1	236	107

Description	Quantity Per Carton	Pounds Per Carton	Kilograms Per Carton
Flow Control Valve			
1½" G/G, Straight Through	1	37	17
3" F/F and F/G Straight Through	1	251	114
3" G/G Straight Through	1	79	36
4" F/F and F/G, Straight Through	1	152	68
4" G/G, Straight Through	1	251	114
6" F/F, Straight Through	1	287	130
6" F/G, Straight Through	1	272	123
6" G/G, Straight Through	1	251	114
8" F/F, Straight Through	1	413	187
8" G/G, Straight Through	1	411	186
Flow Control Valve Trim, Galvanized, Angle Style			
1½" and 2"	1	18	8
3"	1	21	10
4"	1	18	8
6"	1	39	18
Flow Control Valve Trim, Galvanized, Straight Through			
4"	1	32	15
6"	1	38	17
8"	1	63	28
In-Line Check Valve			
1½"	1	4	2
2"	1	6	3
SureFire®			
Single Interlock, Galvanized, Angle Style			
1½" through 6"	1	607	276
Double Interlock, Galvanized, Angle Style			
1½"	1	48	22
2"	1	31	14
3"	1	30	14
4"	1	30	14
6"	1	26	12
Swing Check Valve			
2½" G/G	1	16	7
3" G/G	1	20	9
4" F/F	1	45	20
4" G/G	1	27	12
6" F/F	1	75	34
6" G/G	1	51	23
8" F/F	1	140	64
8" G/G	1	106	48
TrimPac®			
Single Interlock Electric Release	1	34	15
Single Interlock Pneumatic Release	1	73	33
Double Interlock Electric/Pneumatic	1	76	34
Double Interlock Electric/Pneumatic	1	34	15
Deluge Electric Release	1	34	15
Deluge Pneumatic Release	1	34	15
Waterflow Indicator			
1½"	1	2	1
2" and 2½"	1	4	2
3" through 5"	1	5	2
6"	1	6	3
8"	1	7	3
Water Motor Alarm	1	11	5