



Youngstown Tube

Schedule 10 Sprinkler Pipe

Youngstown Tube manufactures Schedule 10 pipe in sizes 1 ¼" thru 6" using only high quality **domestic** steel. This ensures a uniform superior product for roll grooving, welding or plain end uses. Youngstown Tube's schedule 10 pipe is produced under ASTM A795 Type E, Grade A, NH standards. Every piece is Eddy-Current tested and conforms to internal SPC testing and recording.

Youngstown Tube Schedule 10 steel sprinkler pipe is coated with a black enamel coating, continuous color coded *white* stencil, and **stored indoors** ready for immediate shipment.

Approvals

- **UL Listed**
- **CUL Listed**
- **FM Approved**

Youngstown Tube schedule 10 pipe meets the rigorous testing and certification processes of Underwriters Laboratory and Factory Mutual for steel sprinkler pipe with working pressures of 300 psi or less. It also meets the requirements of NFPA 13 and can be used in wet, dry, deluge and preaction systems.

Schedule 10 *

Pipe Size	Pipe OD	Nominal Wall	Weight per Foot	Standard Length	Pieces per Bundle	Feet per Bundle	Weight per Bundle	UL Threaded CRR
1 ¼	1.660	.109	1.81	21	61	1,281	2,319	8.5
1 ½	1.900	.109	2.08	21	44	924	1,921	6.8
2	2.375	.109	2.64	21	37	777	2,051	5.5
2 ½	2.875	.120	3.53	21	37	777	2,742	4.1
3	3.500	.120	4.33	21	24	504	2,182	3.0
4	4.500	.120	5.61	21	19	399	2,238	1.8
6	6.625	.134	9.29	21	10	210	1,951	1.16
8**	8.625	.188	18.49	21	7	147	2,424	1.81

* Schedule 10 pipe can not be threaded or cut-grooved.

** 8" schedule 10 is manufactured from a different domestic supplier.

Youngstown Tube Company
 401 Andrews Avenue
 Youngstown, Ohio 44505
 1-866-The-Tube
www.youngstowntube.com