

Schedule 40 Sprinkler Pipe

Youngstown Tube manufactures Schedule 40 pipe in sizes 1" thru 2" using only high quality **domestic** steel coils. This ensures a uniform superior product for threading, roll grooving, welding or plain end uses. Youngstown Tube's schedule 40 pipe is produced under ASTM A135/A795 Type E, Grade A, NH standards. Every piece is Eddy-Current tested and conforms to internal SPC testing and recording.

Youngstown Tube Schedule 40 steel sprinkler pipe is coated with a waterbased black enamel coating, YTC Guard[®] antimicrobial coating and a continuous color coded **red** stencil, and **stored indoors** ready for immediate shipment.

Approvals

- **UL Listed**
- **CUL Listed**
- **FM Approved**

Youngstown Tube schedule 40 pipe meets the rigorous testing and certification processes of Underwriters Laboratory and Factory Mutual for steel sprinkler pipe with working pressures of 300 psi or less. It also meets the requirements of NFPA 13 and can be used in wet, dry, deluge and preaction systems.

Schedule 40

Pipe Size	Pipe OD	Pipe ID	Nominal Wall	Weight per Foot	Standard Length	Pieces per Bundle	Feet per Bundle	Weight per Bundle	UL Threaded CRR
1	1.315	1.049	.133	1.68	21	61	1,281	2,152	1.00
1 ¼	1.660	1.380	.140	2.27	21	61	1,281	2,907	1.00
1 ½	1.900	1.610	.145	2.72	21	44	924	2,511	1.00
2	2.375	2.067	.154	3.65	21	37	777	2,836	1.00

Youngstown Tube Company
 401 Andrews Avenue
 Youngstown, Ohio 44505
 1-866-The-Tube
www.youngstowntube.com

[Youngstown Tube Company Home Page](#)

[Back](#)