



Viking Sprinklers Available with Electroless Nickel Teflon® Coating for Corrosion Resistance

VIKING - STANDARD COVERAGE SPRINKLERS (w/ ENT Coating)

SIN	K	Description
Standard Response, Upright		
VK100	5.6	Micromatic®, Upright, Glass Bulb, ½" NPT (p/n 12986_)
VK200	8.0	Micromatic®, Upright, Glass Bulb, ¾" NPT (p/n 10141_)
Standard Response, Pendant		
VK102	5.6	Micromatic®, Pendant, Glass Bulb, ½" NPT (p/n 10139_)
VK202	8.0	Micromatic®, Pendant, Glass Bulb, ¾" NPT (p/n 10142_)
Standard Response, Domed Cnclد Pendant		
VK102-D	5.6	Domed Cnclد Pendant, Glass Bulb, ½" NPT (p/n 10139A_X)
VK202-D	8.0	Domed Cnclد Pendant, Glass Bulb, ¾" NPT (p/n 10142A_X)
Quick Response, Upright		
VK300	5.6	Microfast®, Upright, Glass Bulb, ½" NPT (p/n 12978_)
VK350	8.0	Microfast®, Upright, Glass Bulb, ¾" NPT (p/n 06665B_)
Quick Response, Pendant		
VK302	5.6	Microfast®, Pendant, Glass Bulb, ½" NPT (p/n 06662B_)
VK352	8.0	Microfast®, Pendant, Glass Bulb, ¾" NPT (p/n 06666B_)
Quick Response, Domed Cnclد Pendant		
VK302-D	5.6	Microfast®, Domed Cnclد Pendant, G Bulb, ½" NPT (p/n 06662BA_X)
VK352-D	8.0	Microfast®, Domed Cnclد Pendant, G Bulb, ¾" NPT (p/n 06666BA_X)
HIGH PRESSURE, Standard Response		
VK116	5.6	Micromatic®-HP, HSW, Glass Bulb, ½" NPT (p/n 09849_)

VIKING - EXTENDED COVERAGE SPRINKLERS (w/ ENT Coating)

SIN	K	Description
EC, Upright		
VK532	11.2	EC-ELO, Upright, Glass Bulb, ¾" NPT (p/n 08687_) - LH/OH
VK570	14.0	EC-ELO, Upright, Glass Bulb, ¾" NPT (p/n 13840_) - LH/OH
EC, Pendant		
VK534	11.2	EC-ELO, Pendant, Glass Bulb, ¾" NPT (p/n 08340_) - LH/OH
VK608	11.2	EC-ELO, Pendant, Glass Bulb, ¾" NPT (p/n 08339_) - LH
VK572	14.0	EC-ELO, Pendant, Glass Bulb, ¾" NPT (p/n 13722_) - OH
EC, Horizontal Sidewall		
VK630	8.0	EC, HSW, Glass Bulb, ¾" NPT (p/n 13500_) - LH
EC, Domed Concealed, Sidewall		
VK630-D	8.0	EC, Domed Cnclد HSW, Glass Bulb, ¾" NPT (p/n 13500A_X) - LH

VIKING - DRY BARREL SPRINKLERS (w/ ENT Coating)

SIN	K	Description
Standard Response, Pendant (Dry Sprinkler)		
VK150	5.6	Pendent, Glass Bulb, Plain Barrel, 1" NPT (p/n 07852U_)
VK154	5.6	Pendent, Glass Bulb, Standard Adj, 1" NPT (p/n 07740U_)
VK158	5.6	Pendent, Glass Bulb, Recessed Adj, 1" NPT (p/n 06530U_)
VK166	8.0	Pendent, Glass Bulb, Plain Barrel, 1" NPT (p/n 12741_)
VK163	8.0	Pendent, Glass Bulb, Standard Adj, 1" NPT (p/n 12810_)
VK164	8.0	Pendent, Glass Bulb, Recessed Adj, 1" NPT (p/n 12811_)
Standard Response, Sidewall (Dry Sprinkler)		
VK152	5.6	HSW, Glass Bulb, Plain Barrel, 1" NPT (p/n 07858U_)
VK156	5.6	HSW, Glass Bulb, Standard Adj, 1" NPT (p/n 07857U_)
VK162	5.6	HSW, Glass Bulb, Recessed Adj, 1" NPT (p/n 07856U_)
VK250	8.0	HSW, Glass Bulb, Plain Barrel, 1" NPT (p/n 13173_) - OH
VK254	8.0	HSW, Glass Bulb, Recessed Adj, 1" NPT (p/n 13174_) - OH
Quick Response, Horizontal Sidewall (Dry Sprinkler)		
VK277	8.0	HSW, Glass Bulb, Standard Adj, 1" NPT (p/n 13169_) - OH

VIKING - ELO/STORAGE SPRINKLERS (w/ ENT Coating)

SIN	K	Description
ELO, Upright		
VK530	11.2	Standard Response, Upright, Glass Bulb, ¾" NPT (p/n 09679_)
VK531	11.2	Quick Response, Upright, Glass Bulb, ¾" NPT (p/n 10633_)
ELO, Pendant		
VK536	11.2	Standard Response, Pendant, Glass Bulb, ¾" NPT (p/n 07961_)
VK377	11.2	Quick Response, Pendant, Glass Bulb, ¾" NPT (p/n 08337_)

VIKING - RESIDENTIAL SPRINKLERS (w/ ENT Coating)

SIN	K	Description
Pendent		
VK470	3.0	Freedom®, Pendent, Glass Bulb, ½" NPT (p/n 17147_)
VK430	4.3	Freedom®, Pendent, Glass Bulb, ½" NPT (p/n 09530_)
VK468	4.9	Freedom®, Pendent, Glass Bulb, ½" NPT (p/n 13637_)
VK466	5.2	Freedom®, Pendent, Glass Bulb, ½" NPT (p/n 13781_)
VK472	5.8	Freedom®, Pendent, Glass Bulb, ½" NPT (p/n 16130_)
VK458	7.4	Freedom®, Pendent, Glass Bulb, ¾" NPT (p/n 13230_)
Domed Cnclد, Pendant		
VK468-D	4.9	Freedom®, Domed Cnclد Pendant, Glass Bulb, ½" NPT (p/n 13637A_X)
VK466-D	5.2	Freedom®, Domed Cnclد Pendant, Glass Bulb, ½" NPT (p/n 13781A_X)
VK458-D	7.4	Freedom®, Domed Cnclد Pendant, Glass Bulb, ¾" NPT (p/n 13230A_X)
Horizontal Sidewall		
VK486	4.0	Freedom®, HSW, Glass Bulb, ½" NPT (p/n 17315_)
VK484	4.2	Freedom®, HSW, Glass Bulb, ½" NPT (p/n 16240_)
VK460	5.8	Freedom®, HSW, Glass Bulb, ½" NPT (p/n 13933_)
Flat Plate Cnclد, Pendant		
VK457	4.9	Freedom®, Flat Cnclد Pendant, Fusible Link, ½" NPT (p/n 14694AC)
VK474	5.8	Freedom®, Flat Cnclد Pendant, Fusible Link, ½" NPT (p/n 15790AC)
Flat Plate Cnclد, Horizontal Sidewall		
VK480	4.0	Freedom®, Flat Cnclد HSW, Fusible Link, ½" NPT (p/n 16116AC)

Additional Information:		
► To order, add temperature and finish suffix to base part number		
► Suffix "JN" is used for Electroless Nickel Teflon finish		
► Refer to the appropriate page of the Viking List Price Book for additional information, including part numbers and list prices		
► Viking's Electroless Nickel PTFE (ENT) finish has been investigated for installation in corrosive atmospheres and is cULus Listed and FM Approved as corrosion resistant as indicated in the appropriate sprinkler technical data pages, and technical bulletin F_112712, which is available on Viking's web site (www.vikinggroupinc.com)		

* Teflon is a registered trademark of Dupont