



## cULus Listed Residential Upright Sprinkler

Viking's VK467 is the industry's only available residential sprinkler in an upright configuration. Perfectly suited for loft-style residential applications where the system's piping network is exposed, the VK467 has a K-Factor of 4.9 (71) and is approved for up to a 16 x 16 ft. (4.9m x 4.9m) area of coverage.

### Features and advantages of Viking's VK467:

- UL Listed for installation in any type of residential occupancy
- Easier installation, more efficient hydraulic design, and a lower cost sprinkler system overall
- Can provide the residential design advantage in an NFPA 13 application
- Can be installed below beams of up to 14" (35 cm) in depth and is available in 155°F (68°C) and 175°F (79°C) temperature ratings
- The VK467 can be installed on steel sprinkler piping without offsets
- Available in several standard finishes, including and Electroless Nickel PTFE (ENT) coating for corrosion resistant applications

For more information, please contact your Viking sales representative or visit our website at [vikinggroupinc.com](http://vikinggroupinc.com).

### TECHNICAL SPECIFICATIONS

<b>Model Number:</b>	VK467
<b>Base Part Number:</b>	19154
<b>Listings/Approvals:</b>	cULus, NYC
<b>K-factor:</b>	4.9 (71)
<b>Approved Coverage</b>	16 x 16 ft. (4.9 x 4.9m)
<b>Connection:</b>	Threaded: 1/2" NPT
<b>Temperatures:</b>	155°F (68C) 175°F (79°C)
<b>Operating Element:</b>	Glass Bulb
<b>Finish:</b>	Brass, Chrome, Black or White Polyester ENT Coating
<b>Occupancy/Hazard:</b>	Residential
<b>Technical Datasheet:</b>	F_090413
<b>Item Price Group:</b>	V184

### DIGITAL TOOLS



Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting [webtools.vikingcorp.com/sprinklerselector](http://webtools.vikingcorp.com/sprinklerselector).

