



Residential concealed pendent VK495 addresses water supply concerns

The cULus Listed VK495, a K3.7 residential concealed pendent sprinkler, offers sprinkler contractors advantages at 14 x 14 ft coverage areas, addressing water supply concerns and presenting an ideal solution for homeowners. The VK495 rounds out Viking's robust residential concealed sprinkler line, which offers a solution for every challenge in residential occupations.

Features and advantages of Viking's K3.7 residential concealed pendent sprinkler:

- Optimized at a 14 x 14 ft coverage area, making it an ideal solution for areas where water supply issues may be present
- cULus Listed for residential applications and available in a corrosion resistant Electroless Nickel PTFE (ENT) coating for areas where corrosion is a concern
- Protective cap prevents damage during installation and ceiling finishing as well as paint overspray from coating critical internal parts
- Available in Ordinary 155°F (68°C) and Intermediate 200°F (93°C) temperature ratings with a 1/2" NPT threaded connection
- Maximum working pressure of 175 psi (12 bar)

For more information, please contact your Viking SupplyNet sales representative or visit our website at vikinggroupinc.com.

TECHNICAL SPECIFICATIONS

Model Number:	VK495
Base Part Number:	25639
Listings/Approvals:	cULus
K-factor:	K3.7 (53.3)
Connection:	1/2" NPT (15 mm)
Temperatures:	155°F (68°C) 200°F (93°C)
Operating Element:	Glass bulb
Finish:	Brass, Electroless Nickel PTFE (ENT)
Item Price Group:	V183.1
Occupancy/Hazard:	Residential
Technical Datasheet:	F_041623

DIGITAL TOOLS



Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting webtools.vikingcorp.com/sprinklerselector.

MKT-0020

General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.

