



VLTR7.EX1130 Accessories for Special Systems Certified for Canada

[Page Bottom](#)

Accessories for Special Systems Certified for Canada

[See General Information for Accessories for Special Systems Certified for Canada](#)

VIKING CORP

EX1130

210 N INDUSTRIAL PARK RD
HASTINGS, MI 49058 USA

Valve tripping equipment and accessories for "Viking" water supply control valves.

Thermostatic (combined rate-of-rise and fixed temperature): Thermostatic releases, Models C-1, C-2, releasing air or water under pressure from the pilot line. Maximum smooth ceiling spacing 15.2 by 15.2 M. For Model C-1. Model C-2 with spacing of 12.2 by 12.2 M.

Pneumatic actuators, Models H-1, R-1 for use with Viking special system water control valves as indicated in the individual Listings and manufacturer's installation instructions for each type valve.

Prime shutoff valves, Models A-1, A-2 for use with Viking special system water control valves as indicated in the individual Listings and manufacturer's installation instructions for each type valve.

For wet pilot line having water under pressure, Viking Model C-1 pressure-operated relief valve, for use with Viking special system water control valves as indicated in the installation instructions for each type valve and when thermostatically operated tripping mechanism is employed. Maximum operating service pressure 1725 kPa (250 psig).

Pressure operated relief valves, Models D-1 and D-2 for use with Viking special system water control valves as indicated in the individual Listings and manufacturer's installation instructions for each type of valve. Maximum operating service pressure 1725 kPa.

Manual emergency stations, Viking Models C-1, C-2, C-3. An emergency station connected to the pilot line of a deluge valve in order to provide a remote means of releasing pressure from the line, thereby tripping the deluge valve.

Trimpac for special system water control valves, deluge type, Models A-1, A-1B, A-2, A-2B, A-3, A-3B, A-4, A-4B, A-8, A-8B, A-9, A-9B, A-10, A-10B, D-1 and D-1B for use only with Viking's special system water control valves, deluge type Models E-1 and E-2 sizes 2, 3, 4, and 6 inches, E-3 and E-4 size 1 ½ in. and F-1 and F-2 sizes 1 ½, 2, 2 ½, 3, 4, 6 and 8 inches rated for 250 psi.

Models B-1, B-1B, B-2, B-2B, B-3, B-3B, B-4, B-4B, B-8, B-8B, B-9, B-9B, B-10 and B-10B for use only with Viking's special system water control valves, deluge type Models E-1, E-2, H-1 and H-2 sizes 2, 3, 4 and 6 inches, E-3, E-4, H-3 and H-4 size 1 ½ in. and J-1 and J-2 sizes 1 ½, 2, 2 ½, 3, 4, 6 and 8 inches rated 250 psi.

Models C-1 and C-1B for use only with Viking's special system water control valves, deluge type Models H-1 and H-2 sizes 2, 3, 4 and 6 inches, H-3 and H-4 size 1 ½ in. and J-1 and J-2 sizes 1 ½, 2, 2 ½, 3, 4, 6 and 8 rated for 250 psi.

Trimpac for special system water control valves, double interlock type, Models A-6, A-6B, D-2 and D-2B for use only with Viking's special system water control valves, deluge type Models E-1 and E-2 sizes 2, 3, 4 and 6 inches, E-3 and E-4 size 1 ½ in., F-1 and F-2 sizes 1 ½, 2, 2 ½, 3, 4, 6, and 8 inches rated for 250 psi.

Models B-5, B-5B, B-6, B-6B, B-7 and B-7B for use only with Viking's special system water control valves, deluge type Models E-1, E-2, H-1 and H-2 sizes 2, 3, 4 and 6 inches, E-3, E-4, H-3 and H-4 size 1 ½ in. and F-1, F-2, J-1 and J-2 sizes 1 ½, 2, 2 ½, 3, 4, 6 and 8 inches rated for 250 psi.

Trimpac for special system water control valves, flow cycling assemblies, Models E-1, E-1B, E-2, E-2B, E-3 and E-3B for use with Viking's special system water control valves, deluge type Model H-1 and H-2 sizes 2, 3, 4 and 6 inches, H-3 and H-4 size 1 ½ in., J-1 and J-2 sizes 1 ½, 2, 2 ½, 3, 4 and 6, H-3 and H-4 size 1 ½ in., J-1 and J-2 sizes 1 ½, 2, 2 ½, 3, 4, 6 and 8 rated for 250 psi.

Last Updated on 2007-08-13

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2008 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

