

## SWIVEL X-PRESS™ - Swivel Application



Application	Product Features
<p>for <b>extreme</b> or <b>variant</b> roof pitches</p>	<ul style="list-style-type: none"> <li>The <b>Swivel X-Press</b> allows you to hang plumb in extreme roof pitches:                             <ul style="list-style-type: none"> <li>- 89° in z-purlin</li> <li>- 45° in metal deck for 12/12 pitch</li> </ul> </li> <li>Installs in seconds with Sammy X-Press It® Tool, saving time &amp; installation costs.</li> <li>Use in applications where access to the back of the installed fastener is prohibited. ie. metal roof deck, tubular steel, or vapor barrier fabric.</li> <li>Less jobsite material needed.</li> <li>No retaining nut required.</li> <li>Provides design flexibility.</li> <li>Made in the U.S.A.</li> </ul>



Approvals	Rod Size	Part Number	Model	Description	Ultimate Pullout (lbs)	UL Test Load (lbs)	UL Min Thick	FM Test Load (lbs)	FM Min Thick	Max Thick	Box Qty	Case Qty	Application
<b>SWIVEL MOUNT</b>													
	3/8"	8294922	SXP 20	Swivel X-Press 20	1061 (22 ga Vert) 829 (45° Off Vert)	750 (2" Pipe) 170 Vertical (Luminaire) 80 @ 45° (Luminaire) 283 Vertical (Conduit & Cable) 233 @ 45° (Conduit & Cable)	.029"	635 (2" Pipe)	.029"	.125"	25	125	Metal Deck
	3/8"	8295922	SXP 35	Swivel X-Press 35	1675 (16 ga Vert) 1558 (89° Off Vert)	1250 (3-1/2" Pipe) 250 Vertical (Luminaire) 80 @ 90° (Luminaire) 500 Vertical (Conduit & Cable) 333 @ 89° (Conduit & Cable)	.059"	635 (2" Pipe)	.029"	.125"	25	125	Purlin
	1/2"	8272957	SXP 2.0	Swivel X-Press 2.0	1061 (22 ga Vert) 829 (45° Off Vert)		.027"	.125"			25	125	Metal Deck
	1/2"	8271957	SXP 3.5	Swivel X-Press 3.5	1675 (16 ga Vert) 1558 (89° Off Vert)		.060"	.125"			25	125	Purlin

## SAMMY X-PRESS IT® Installation Tool



Application	Product Features
	<ul style="list-style-type: none"> <li>The <b>Sammy X-Press</b> expands to provide direct vertical attachment in:                             <ul style="list-style-type: none"> <li>- metal deck (22-16 gauge)</li> <li>- z-purlin (18-16 gauge)</li> </ul> </li> <li>Made in the U.S.A.</li> </ul>



Part Number	Model	Description	Qty
8194910	UXPIT*	Universal X-Press It Tool	1
8152910	XPDB	25/64" Drill Bit	1

\*Tool Includes: Sleeve, Bit Receiver, Hex Wrench, and 25/64" Drill Bit.