

# QUICK SLIP PIPE JOINT LUBRICANT QS-SPEC

## PRODUCT DESCRIPTION

### PRODUCT

**QUICK SLIP** Pipe Joint Lubricant

### TYPE

**QUICK SLIP** is a vegetable oil-based pipe joint lubricant derived from oleic acid.

### RECOMMENDED USES

**QUICK SLIP** is a non-drying paste lubricant for assembly of pipe joints using rubber or synthetic gaskets. Great for all types of metal or plastic gasketed pipe including Victaulic\* type fittings. Works on Wet or Dry Surfaces. Safe for Potable Water Systems. Nontoxic, Non-corrosive, Nonflammable. Adheres to wet or dry pipe.

### COLOR

Golden Brown

### CONSISTENCY

Smooth, grit-free paste. **QUICK SLIP** has an indefinite shelf life.

### ENVIRONMENTAL STATEMENT

**QUICK SLIP** is formulated to inhibit growth of all germs and infectious organisms within the oil. Will not promote bacterial growth. **QUICK SLIP** is free of toxic ingredients.

### TEMPERATURE RANGE USE

0°F (-17°C) to 110°F (-43°C)

### WEIGHT PER U.S. GALLON

7.93 lbs. (3.62 kg)

### PACKAGING

#### U.S. Measure:

Stock Code	Size
<b>Screw Top Plastic Container</b>	
QS32	1 quart (.95 L)
<b>Plastic Pail w/Handle</b>	
QS1	1 gal. (3.785 L)
<b>55 Gallon Drum</b>	
QS55	55 gal. (208 L)

### SHIPPING WEIGHT PER CASE

Stock#	Case Weight	#/Case
QS32	30 lbs. (13.6 kg)	12/case
QS1	34 lbs. (15.4 kg)	4/case
QS5	45 lbs. (20.4 kg)	1 each
QS55	480 lbs. (217.7 kg)	1 each

### PRECAUTIONS

**QUICK SLIP** is a pipe lubricant which has the consistency of soap. Prolonged contact with skin could cause irritation. Keep lubricant from coming into contact with eyes. In case of contact flush with water for 5 minutes. Contact a physician for medical attention.

### DIRECTIONS FOR USE

1. If **QUICK SLIP** is separated, mix before using. This product is ready for use. Do not alter or dilute with water or any other additives.
2. Pre-clean pipe and gasket of any foreign matter.
3. Check gasket to insure that it is properly seated.
4. Apply **QUICK SLIP** using a sponge, glove, cotton swab applicator, bristle brush, or similar type applicator. Be sure enough lubricant is applied to coat surfaces uniformly.
5. Do not place lubricant in the ringed groove.
6. Pipe should easily push into the female end of the gasketed pipe.

### QS-SPEC

© 2005 J.C. Whitlam Manufacturing Company  
This product is manufactured in the U.S.A.



Division of  
J.C. Whitlam Manufacturing Company  
P.O. Box 380  
Wadsworth, Ohio 44282  
Phone: 330-334-2524  
Fax: 330-334-3005  
email: [Info@jcwhitlam.com](mailto:Info@jcwhitlam.com)  
Website: [www.jcwhitlam.com](http://www.jcwhitlam.com)

The information contained in this bulletin is correct to the best of our knowledge. The recommendations or suggestions herein are made without guarantee or representation as to result, since the conditions of use are beyond our control. We suggest that you evaluate the recommendations contained in this bulletin. No statement is to be construed as violating any copyright or patent. They are intended only as a source of information.

\*Victaulic is a registered trademark of Victaulic Co.