


	TECHNICAL DATA	2-1/2" MODEL J SERIES FLOW CONTROL VALVES FRICTION LOSS CHART
---	-----------------------	--

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

FOR USE WITH ENGLISH PRACTICAL SYSTEM
 Where Flow is Measured in GPM and Pressure is Measured in PSI

Graph is for reference purposes.



Friction Loss for the 2-1/2" Viking J Series Flow Control Valves is equivalent to 12 feet of 2-1/2" Schedule 40 (id = 2.469") Pipe (C = 120).

To calculate friction loss for the 2-1/2" (id = 2.469") Viking Model J Series Flow Control Valves at a specific flow, use the following formula:

$$P_{\text{PSI}} = \left(\frac{4.52 \times Q^{1.85}}{C^{1.85} \times 2.469^{4.87}} \right) \times 12$$

Where P = Friction Loss (PSI)
 Q = Flow in GPM
 C = Constant (=120)