




Pipe Clamp

SSG

Technical Features

- **Sizes:** Nominal sizes in Hot Dipped Galvanized finish from 1" to 8" to accommodate pipe diameters from 35 mm to 222 mm. In Black Steel from 1/2" to 12" to accommodate pipe diameters from 22 mm to 327 mm.
- **Finish:** Hot Dipped Galvanized & Black Steel



Pipe Clamp - SSG

Physical Data

Reference	Finish / Material	Nominal Pipe Size		Pipe Diameter Ø (mm)	A	B x S (mm)	Box Qty.	Weight (x1) (kg / lbs)
		Metric	inch					
574500	HDG	DN25	1"	35			10	
574510	HDG	DN32	1 1/4"	43			10	
574520	HDG	DN40	1 1/2"	49			10	
574530	HDG	DN50	2"	61			10	
574540	HDG	DN65	2 1/2"	77			10	
574550	HDG	DN80	3"	90			10	
574560	HDG	DN100	4"	115			10	
574565	HDG	DN125	5"	141			10	
574570	HDG	DN150	6"	170			10	
574580	HDG	207 mm	-	207			10	
574590	HDG	DN200	8"	222			10	
574600	Black Steel	DN15	1/2"	22			10	
574610	Black Steel	DN20	3/4"	28			10	
574620	Black Steel	DN25	1"	35			10	
574630	Black Steel	DN32	1 1/4"	43			10	
574640	Black Steel	DN40	1 1/2"	49			10	
574650	Black Steel	DN50	2"	61			10	
574660	Black Steel	DN65	2 1/2"	77			10	
574670	Black Steel	DN80	3"	90			10	
574680	Black Steel	DN100	4"	115			10	
574685	Black Steel	DN125	5"	141			10	
574690	Black Steel	DN150	6"	170			10	
574700	Black Steel	DN200	8"	222			10	
574710	Black Steel	DN250	10"	276			10	
574720	Black Steel	DN300	12"	327			10	