


Class 125 (Standard)

FIG. 3351R

Reducing 90° Elbow



For Listings/Approval Details and Limitations, visit our website at www.anvilintl.com or contact an Anvil® Sales Representative.

FIGURE 3351R - REDUCING 90° ELBOW

Nominal Size	Max. Working Pressure [▲]	Dimensions		Approx. Wt. Each
		A	B	
<i>In. (mm)</i>	<i>PSI (kPa)</i>	<i>In. (mm)</i>	<i>In. (mm)</i>	<i>Lbs. (kg)</i>
1 x 1/2 25 x 15	300 2065	1.26 32.00	1.36 34.54	0.64 0.29
1 x 3/4 25 x 20	300 2065	1.37 34.79	1.45 36.83	0.87 0.39
1 1/4 x 1/2 32 x 15	300 2065	1.34 34.03	1.53 38.86	0.96 0.44
1 1/4 x 3/4 32 x 20	300 2065	1.45 36.83	1.62 41.14	1.13 0.51
1 1/4 x 1 32 x 25	300 2065	1.58 40.13	1.67 42.41	1.16 0.53
1 1/2 x 1/2 40 x 15	300 2065	1.41 35.81	1.66 42.16	1.17 0.53
1 1/2 x 3/4 40 x 20	300 2065	1.52 38.60	1.75 44.45	1.28 0.58
1 1/2 x 1 40 x 25	300 2065	1.65 41.91	1.80 45.72	1.51 0.68
1 1/2 x 1 1/4 40 x 32	300 2065	1.82 46.22	1.88 47.75	1.62 0.73
2 x 1/2 50 x 40	300 2065	1.49 37.84	1.88 47.75	2.00 0.91
2 x 3/4 50 x 20	300 2065	1.60 40.64	1.97 50.03	2.05 0.93
2 x 1 50 x 25	300 2065	1.73 43.94	2.02 51.30	2.10 0.95
2 x 1 1/4 50 x 32	300 2065	1.90 48.26	2.10 53.34	2.30 1.04
2 x 1 1/2 50 x 40	300 2065	2.02 51.30	2.16 54.86	2.60 1.18

▲ – Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit anvilintl.com or contact your local Anvil Representative.

MATERIAL SPECIFICATIONS

Dimensions: ASME B16.4 Class 125

Material: ASTM A126

Finish: Black or Hot Dip Galvanized per ASTM A153 Class A

Threads: NPT per ASME B1.20.1

Agency Approvals: All cast iron threaded fittings are UL/ULC Listed and FM Approved.

PROJECT INFORMATION

APPROVAL STAMP

Project:	<input type="checkbox"/> Approved
Address:	<input type="checkbox"/> Approved as noted
Contractor:	<input type="checkbox"/> Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	