



For Listings/Approval Details and Limitations, visit our website at www.anvilint.com or contact an Anvil® Sales Representative.

X-1 CROSS			
Nominal Size	O.D.	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./Kg
1¼ 32	1.660 42.2	3¾ 95	2.0 0.9
1½ 40	1.900 48.3	3¾ 95	2.2 1.0
2 50	2.375 60.3	3¾ 95	2.2 1.0
2½ 65	2.875 73.0	3¾ 95	3.3 1.5
3 80	3.500 88.9	3¾ 95	5.0 3.2
4 100	4.500 114.3	5 127	6.6 3.0
5 125	5.563 141.3	5¼ 133	9.3 4.2
6 150	6.625 168.3	6½ 165	14.5 6.6
8 200	8.625 219.1	7¾ 197	28.5 12.9
10 250	10.750 273.1	9 229	40.5 18.4
12 300	12.750 323.9	10 254	57.0 25.9

MATERIAL SPECIFICATIONS

FABRICATED FITTINGS:

- 1"- 10" Carbon Steel, Schedule 40, conforming to ASTM A-53, Grade B
- 12" Carbon Steel, Standard Wall, conforming to ASTM A-53, Grade B

COATINGS:

- Rust inhibiting paint Color: ORANGE (standard) or
- Hot Dipped Zinc Galvanized conforming to ASTM A-153 (optional)
- Other available options: Example: RAL3000 or RAL9000 Series

PROJECT INFORMATION		APPROVAL STAMP	
Project:		<input type="checkbox"/> Approved	
Address:		<input type="checkbox"/> Approved as noted	
Contractor:		<input type="checkbox"/> Not approved	
Engineer:		Remarks:	
Submittal Date:			
Notes 1:			
Notes 2:			