



**Section E**  
**Special Sprinklers**

**TABLE OF CONTENTS**

Institutional - VK410/VK412, 5.6 (81) K factor, flush pendent / flush horizontal sidewall.....E-1  
 Combustible Interstitial Space - VK900, VK950, COIN<sup>®</sup>, upright .....E-1  
 Model V-BB specific application attic sprinkler - VK684, VK685, VK686, VK681, VK682, VK683 .....E-2  
 Model V-SD specific application attic sprinkler - VK693, VK694, VK695 .....E-2  
 Model V-HIP specific application attic sprinkler – VK660 .....E-2  
 Attic upright specific application sprinkler – VK696, VK697.....E-2


**Notes**


1. Unless otherwise indicated, all cover plates and escutcheons are sold separately.
2. Cover plates, escutcheons, and sprinklers are available in custom colors at an additional charge. See pages F-8 and F-9 for details.
3. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting [www.vikinggroupinc.com](http://www.vikinggroupinc.com).
4. List prices effective June 4, 2016. Supersedes May 2015 list price book.
5. All sales by Viking are subject to the Terms & Conditions found on the last page of this book.


*COIN<sup>®</sup> is a registered trademark of The Viking Corporation*  
*Micromatic<sup>®</sup> is a registered trademark of The Viking Corporation*


	<b>COIN<sup>®</sup></b> <b>Quick Response</b> <b>COmbustible INterstitial</b> <b>Glass Bulb</b> <b>Upright</b>			
	<b>SIN:</b>	VK900		
	<b>K Factor:</b>	4.2 (60)		
	<b>Thread Size:</b>	1/2 inch NPT		
	<b>Base Part #:</b>	12493		
<b>Finish</b>	<b>Temp</b>	<b>Part #</b>	<b>IPG</b>	<b>List Price</b>
Standard Brass	175°F	12493AD	V14.3	\$60.46
<b>FUSIBLE LINK - VK901 (4.2 (60) K Factor)</b>				
Standard Brass	205°F	12676AE	V14.3	\$66.67
Std Sprinkler Wrench		10896W/B	V20	\$67.72

	<b>COIN<sup>®</sup></b> <b>Quick Response</b> <b>COmbustible INterstitial</b> <b>Glass Bulb</b> <b>Upright (Specific Application)</b>			
	<b>SIN:</b>	VK950		
	<b>K Factor:</b>	5.6 (80)		
	<b>Thread Size:</b>	1/2 inch NPT		
	<b>Base Part #:</b>	20757		
<b>Finish</b>	<b>Temp</b>	<b>Part #</b>	<b>IPG</b>	<b>List Price</b>
Standard Brass	200°F	20757AE	V14.3	\$74.06
Std Sprinkler Wrench		10896W/B	V20	\$67.72

	<b>Institutional<sup>2,3</sup></b> <b>Quick Response</b> <b>Extended Coverage</b> <b>Fusible Link</b> <b>Flush Pendent</b>			
	<b>SIN:</b>	VK410		
	<b>K Factor:</b>	5.6 (81)		
	<b>Thread Size:</b>	1/2 inch NPT		
	<b>Base Part #:</b>	10554		
<b>Finish</b>	<b>Temp</b>	<b>Part #</b>	<b>IPG</b>	<b>List Price</b>
Polished Chrome	165°F	10554FC	V17.1	\$62.50
Polished Chrome	220°F	10554FF	V17.1	\$62.50
Heavy Duty Spk Wrench		08336W/B	V20	\$130.44
Light Duty Spk Wrench		10366W/B	V20	\$30.88


	<b>Institutional<sup>2,3</sup></b> <b>Quick Response</b> <b>Standard Coverage</b> <b>Fusible Link</b> <b>Flush Horizontal Sidewall</b>			
	<b>SIN:</b>	VK412		
	<b>K Factor:</b>	5.6 (81)		
	<b>Thread Size:</b>	1/2 inch NPT		
	<b>Base Part #:</b>	10579		
<b>Finish</b>	<b>Temp</b>	<b>Part #</b>	<b>IPG</b>	<b>List Price</b>
Polished Chrome	165°F	10579FC	V17.1	\$73.57
Polished Chrome	220°F <sup>1</sup>	10579FF	V17.1	\$73.57
Heavy Duty Spk Wrench		08336W/B	V20	\$130.44
Light Duty Spk Wrench		10366W/B	V20	\$30.88


	<b>Institutional</b> <b>Escutcheon / Lock Ring Pkg<sup>3</sup></b> <i>(3-1/4 inch diameter)</i>			
	<b>Finish</b>	<b>Part #</b>	<b>IPG</b>	<b>List Price</b>
Polished Chrome	10627F	V17.1	\$25.94	
Esc Installation Wrench	10551W/B	V20	\$44.57	
Spanner Wrench-Removal	10729	V20	\$148.61	


	<b>Institutional</b> <b>Optional Retaining Flange</b> <b>and Screw Assembly<sup>3</sup></b>			
	<b>Finish</b>	<b>Part #</b>	<b>IPG</b>	<b>List Price</b>
Polished Chrome	10599	V17.1	\$37.89	


- (1) 220°F institutional flush sidewall is not listed or approved.
- (2) For institutional sprinklers, once lock ring is installed and escutcheon is threaded, the escutcheon cannot be removed without damage to the sprinkler or escutcheon.
- (3) Institutional sprinklers and escutcheon/lock ring packages are sold separately.
- (4) Electroless Nickel PTFE (ENT) plating is UL Listed for corrosion resistance.

**Specific Application Attic Sprinklers**

	Back-to-Back (Model V-BB) Attic Sprinkler, Specific Application, Glass Bulb, ½ and ¾ inch NPT							
	K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
	5.6 (81)	4:12 < 7:12	VK684	19627AE	200°F	Standard Brass	V14.5	\$ 329.60
	5.6 (81)	7:12 < 10:12	VK685	19801AE	200°F	Standard Brass	V14.5	\$ 329.60
	5.6 (81)	10:12 ≤ 12:12	VK686	19754AE	200°F	Standard Brass	V14.5	\$ 329.60
	8.0 (115)	4:12 < 7:12	VK681	19626AE	200°F	Standard Brass	V14.5	\$ 384.53
	8.0 (115)	7:12 < 10:12	VK682	19798AE	200°F	Standard Brass	V14.5	\$ 384.53
8.0 (115)	10:12 ≤ 12:12	VK683	19751AE	200°F	Standard Brass	V14.5	\$ 384.53	

	Single Directional (Model V-SD) Attic Sprinkler, Specific Application, Glass Bulb, ½ inch NPT							
	K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
	5.6 (81)	4:12 < 7:12	VK693	19578AE	200°F	Standard Brass	V14.5	\$ 329.60
	5.6 (81)	7:12 < 10:12	VK694	19799AE	200°F	Standard Brass	V14.5	\$ 329.60
5.6 (81)	10:12 ≤ 12:12	VK695	19759AE	200°F	Standard Brass	V14.5	\$ 329.60	

	Attic Upright Sprinkler, Specific Application, Glass Bulb, ½ inch NPT							
	K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
	4.2 (57)	4:12 to 12:12	VK696	19538AE	200°F	Standard Brass	V14.4	\$ 48.22
5.6 (81)	4:12 to 12:12	VK697	21716AE	200°F	Standard Brass	V14.4	\$ 55.08	

	Attic HIP (Model V-HIP), Specific Application, Glass Bulb, ½ inch NPT							
	K Factor	Roof Pitch	SIN	Part #	Temp	Finish <sup>1</sup>	IPG	List Price
5.6 (81)	4:12 to 12:12	VK660	20952AE	200°F	Standard Brass	V14.5	\$ 329.60	

Installation Wrench	Part #	IPG	List Price
Standard Wrench	10896W/B	V20	\$ 67.72

(1) Also available with Electroless Nickel PTFE (ENT) plating for corrosion resistance (special order with extended lead time).  
Please contact customer service for price and availability.

