


FIG. E-3 22¹/₂° Elbow



For Listings/Approval Details and Limitations, visit our website at www.anvilint.com or contact an Anvil® Sales Representative.

LPS 1219: Issue 3.1
Cert/LPCB ref. 519a/25

E-3 22¹/₂° ELBOW

Nominal Size	O.D.	Max. Working Pressure	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm	Lbs./Kg
1¼ 32	1.660 42.2	300 20.7	1¾ 44	0.8 0.4
1½ 40	1.900 48.3	300 20.7	1¾ 44	0.7 0.3
2 50	2.375 60.3	300 20.7	2 51	1.6 0.7
2½ 65	2.875 73.0	300 20.7	2 51	2.1 1.0
3 80	3.500 88.9	300 20.7	2¼ 57	3.1 1.4
4 100	4.500 114.3	300 20.7	2½ 73	5.4 2.4
5 125	5.563 141.3	300 20.7	2½ 73	7.8 3.5
6 150	6.625 168.3	300 20.7	3½ 79	8.3 3.8
8 200	8.625 219.1	300 20.7	3½ 98	17.9 8.1
10 250	10.750 273.1	300 20.7	4¾ 121	30.0 13.6
12 300	12.750 323.9	300 20.7	4¾ 124	40.4 18.3

MATERIAL SPECIFICATIONS

CAST FITTINGS:

Ductile Iron conforming to ASTM A-536, Grade 65-45-12

COATINGS:

- Rust inhibiting paint Color: ORANGE (standard) or
- Hot Dipped Zinc Galvanized conforming to ASTM A-153 (optional)
- Other available options: Example: RAL3000 or RAL9000 Series

PROJECT INFORMATION

APPROVAL STAMP

Project:	<input type="checkbox"/> Approved
Address:	<input type="checkbox"/> Approved as noted
Contractor:	<input type="checkbox"/> Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	