



Viking Special Systems | Firecycle® III Wet, Deluge, and Preaction

Automatically stop water flow when the fire is extinguished.

Viking's Firecycle® III cycling fire protection systems are ideal for conserving water, limiting water discharge damage, and automatically shutting off water flow when no one is present. This unique technology turns off water discharge and resets once the heat from a fire has dissipated and the fire is extinguished, and will also reactivate automatically if a fire condition should reignite.

Firecycle® III Wet, Deluge, and Preaction systems are provided in TRIMPAC® trim packages that are preassembled and factory leak-tested in a single metal enclosure. They feature access doors for manual operation of emergency release and alarm test valves, and priming water pressure gauge view-ports for easy water pressure monitoring.

- System cycles on and off, monitoring fire conditions and providing water as needed.
- Factory assembled trim package in a single cabinet.
- As easy to install as standard wet, deluge, and preaction systems.
- Galvanization and other special coatings available on request.
- Firecycle® Systems also available in Viking TotalPac® Integrated Systems.

Contact your local Viking SupplyNet team to place an order today!

The Viking Corporation

210 N Industrial Park Drive, Hastings, MI 49058

Telephone: (269) 945-9501

Email: products@vikingcorp.com

www.vikinggroupinc.com

Trusted above all.™

Standard TRIMPAC® includes:

Conventional Trim
NO Solenoid Valve
NC Solenoid Valve
Releasing Trim
Flexible Hose Kit
Drain Package (must be ordered separately)

TRIMPAC® Multi-Cycle Systems

Model E-3 Wet
Model E-2/E-2B Deluge
Model E-1/E-1B Preaction



Firecycle® III Detectors

Rate Compensating,
Automatic Recycling

OH Detectors available
in Flush Mount and
Surface Mount, with
temperatures from
140°F to 225°F



FPL Detectors for use
with conduit available
in temperatures from
140°F to 190°F



VIKING®