


FIG. T-2 Reducing Tee



For Listings/Approval Details and Limitations, visit our website at www.anvilint.com or contact an Anvil® Sales Representative.

MATERIAL SPECIFICATIONS

CAST FITTINGS:

Ductile Iron conforming to ASTM-A536, Grade 65-45-12


FABRICATED FITTINGS:

1"- 10" Carbon Steel, Schedule 40, conforming to ASTM A-53, Grade B

12" Carbon Steel, Standard Wall, conforming to ASTM A-53, Grade B

COATINGS:

- Rust inhibiting paint Color: ORANGE (standard) or
- Hot Dipped Zinc Galvanized conforming to ASTM A-153 (optional)
- Other available options: Example: RAL3000 or RAL9000 Series



T-2 REDUCING TEE

Nominal Size	Center to End	Approx. Wt. Ea.	Nominal Size	Center to End	Approx. Wt. Ea.	Nominal Size	Center to End	Approx. Wt. Ea.	Nominal Size	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	Lbs./Kg	In./DN(mm)	In./mm	Lbs./Kg	In./DN(mm)	In./mm	Lbs./Kg	In./DN(mm)	In./mm	Lbs./Kg
2 x 2 x 1 (d)	3/4	2.6	4 x 4 x 1 1/2	5	11.0	6 x 6 x 2 (d)	6 1/2	26.4	10 x 10 x 3	9	69.3
50 x 50 x 25	83	1.2	100 x 100 x 40	127	5.0	150 x 150 x 50	165	12.0	250 x 250 x 80	229	31.4
2 x 2 x 1 1/4	3/4	3.0	4 x 4 x 2	5	11.0	6 x 6 x 2 1/2 (d)	6 1/2	22.8	10 x 10 x 4	9	69.3
50 x 50 x 32	83	1.4	100 x 100 x 50	127	5.0	150 x 150 x 65	165	10.3	250 x 250 x 100	229	31.4
2 x 2 x 1 1/2	3/4	3.0	4 x 4 x 2 1/2 (d)	5	12.3	6 x 6 x 3 (d)	6 1/2	25.0	10 x 10 x 5	9	69.3
50 x 50 x 40	83	1.4	100 x 100 x 65	127	5.6	150 x 150 x 80	165	11.3	250 x 250 x 125	229	31.4
2 1/2 x 2 1/2 x 1	3/4	4.4	4 x 4 x 3 (d)	5	12.0	6 x 6 x 4 (d)	6 1/2	24.2	10 x 10 x 6	9	69.3
65 x 65 x 25	95	2.0	100 x 100 x 80	127	5.4	150 x 150 x 100	165	11.0	250 x 250 x 150	229	31.4
2 1/2 x 2 1/2 x 1 1/4	3/4	4.4	5 x 5 x 1	5 1/2	14.0	6 x 6 x 5 (d)	6 1/2	25.4	10 x 10 x 8	9	69.3
65 x 65 x 32	95	2.0	125 x 125 x 25	140	6.3	150 x 150 x 125	165	11.5	250 x 250 x 200	229	31.4
2 1/2 x 2 1/2 x 1 1/2	3/4	4.4	5 x 5 x 1 1/4	5 1/2	14.0	8 x 8 x 1 1/2	-	42.2	12 x 12 x 3	10	100.0
65 x 65 x 40	95	2.0	125 x 125 x 32	140	6.3	200 x 200 x 40	-	19.1	300 x 300 x 80	254	45.4
2 1/2 x 2 1/2 x 2 (d)	3/4	4.6	5 x 5 x 1 1/2	5 1/2	14.0	8 x 8 x 2	7 3/4	42.2	12 x 12 x 4	10	101.6
65 x 65 x 50	95	2.1	125 x 125 x 40	140	6.3	200 x 200 x 50	197	19.1	300 x 300 x 100	254	46.1
3 x 3 x 1	4/4	6.1	5 x 5 x 2	5 1/2	14.0	8 x 8 x 2 1/2	7 3/4	42.2	12 x 12 x 5	10	100.0
80 x 80 x 25	108	2.7	125 x 125 x 50	140	6.3	200 x 200 x 65	197	19.1	300 x 300 x 125	254	45.4
3 x 3 x 1 1/4	4/4	6.1	5 x 5 x 2 1/2	5 1/2	14.0	8 x 8 x 3	7 3/4	42.2	12 x 12 x 6	10	100.0
80 x 80 x 32	108	2.7	125 x 125 x 65	140	6.3	200 x 200 x 80	197	19.1	300 x 300 x 150	254	45.4
3 x 3 x 1 1/2	4/4	6.1	5 x 5 x 3	5 1/2	14.0	8 x 8 x 4 (d)	7 3/4	41.5	12 x 12 x 8	10	100.0
80 x 80 x 40	108	2.7	125 x 125 x 80	140	6.3	200 x 200 x 100	197	18.8	300 x 300 x 200	254	45.4
3 x 3 x 2	4/4	6.1	5 x 5 x 4	5 1/2	14.0	8 x 8 x 5	7 3/4	24.8	12 x 12 x 10 (d)	10	101.6
80 x 80 x 50	108	2.7	125 x 125 x 100	140	6.3	200 x 200 x 125	197	11.2	300 x 300 x 250	254	46.1
3 x 3 x 2 1/2 (d)	4/4	6.1	6 x 6 x 1	-	25.3	8 x 8 x 6 (d)	7 3/4	39.5			
80 x 80 x 65	108	2.7	150 x 150 x 25	-	11.5	200 x 200 x 150	197	17.9			
4 x 4 x 1	3/4	11.0	6 x 6 x 1 1/4	6 1/2	25.3	10 x 10 x 2	9	69.3			
100 x 100 x 25	95	5.0	150 x 150 x 32	165	11.5	250 x 250 x 50	229	31.4			
4 x 4 x 1 1/4	5	11.0	6 x 6 x 1 1/2	6 1/2	25.3	10 x 10 x 2 1/2	9	69.3			
100 x 100 x 32	127	5.0	150 x 150 x 40	165	11.5	250 x 250 x 65	229	31.4			

(d)=Ductile Iron all others are fabricated.

O.D. CHART

Nominal Size	O.D.
In./DN(mm)	In./mm
1	1.315
25	33.4
1 1/4	1.660
32	42.2
1 1/2	1.900
40	48.3
2	2.375
50	60.3
2 1/2	2.875
65	73.0
3	3.500
80	88.9
3 1/2	4.000
90	101.6
4	4.500
100	114.3
5	5.563
125	141.3
6	6.625
150	168.3
8	8.625
200	219.1
10	10.750
250	273.1
12	12.750
300	323.9

PROJECT INFORMATION

APPROVAL STAMP

Project:	<input type="checkbox"/> Approved <input type="checkbox"/> Approved as noted <input type="checkbox"/> Not approved Remarks:
Address:	
Contractor:	
Engineer:	
Submittal Date:	
Notes 1:	
Notes 2:	