

# Angle Hose Valves

# INSIST<sup>ON</sup> FPPI<sup>®</sup>

## UL, ULC and FM Approved

### Description

Angle hose valves feature all brass\* construction with forged or cast bodies for rigidity and light weight. Typical uses are in rack assemblies or any other application which requires a listed fire hose valve. Available in rough brass or polished chrome finish with a red hand wheel. **UL, ULC and FM Approved. Rated 300psi**



### Installation

Install in accordance with customary installation practices. Use an approved thread sealant such as PipeFit Thread Sealing Paste with PTFE on the male threads to which the valve is being installed.

**DO NOT OVER TIGHTEN. Over tightening of the valve during installation to the male pipe threads may crack or deform the valve body. Only use tools suitable for the installation of this product. Do not use pipe wrench extenders to increase leverage on pipe wrenches. This may result in valve damage as well as personal injury.**

### Specifications


**Material:**  
Cast or Forged Brass\* Body

**Finish:**  
Rough Brass  
Polished Chrome\*

**Threads:**  
2½" FNPT x FNPT  
FNPT x MNST\*  
MBCT  
MQST  
MONT  
MPHX  
MTEM  
MCLV  
2½" GRV x FNPT  
GRV x MNST  
1½" FNPT x FNPT  
FNPT x MNST

Friction loss is less than 3 psi thru an equivalent length of pipe per UL Standards.

\*Contains lead. Not for use in water systems intended for human consumption.



3198 LIONSHEAD AVE  
CARLSBAD, CA 92010  
TEL + 1 760 599-1168  
+ 1 800 344-1822  
FAX + 1 800 344-3775

© 2012 Fire Protection Products, Inc.

[WWW.FPPI.COM](http://WWW.FPPI.COM)

