

TABLE OF CONTENTS

TotalPac[®]3 – Introduction K-1
TotalPac[®]3 – Preaction Systems..... K-2
TotalPac[®]3 – Deluge, Wet, and Dry Systems K-3
TotalPac[®]3 – Firecycle[®] III and SureFire[®] Systems..... K-4
TotalPac[®]3 – System Options / Release Control Panel Options..... K-5
TotalPac[®]3 – Air Supply Options K-6
TotalPac[®]3 – Terms and ConditionsK-7

Notes

1. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting www.vikinggroupinc.com.
2. List prices effective January 12, 2019. Supersedes June 2018 list price book.
3. All sales by Viking are subject to the terms & conditions found on the last page of this book.

SureFire[®] and Firecycle[®] are registered trademarks of The Viking Corporation.



NEW - TOTALPAC®3 Integrated Fire Protection Systems

Introduction:

Pricing of the TotalPac3 Product Line are priced by adding various options together until a complete unit is obtained.

A basic system now includes the system valve, its releasing trim and its supporting assembly, whether it is a skid, a remote controlled cabinet without control panel or a self-contained unit with control panel. These are all included under a single part number.

The price list now resembles a matrix which facilitates its use. It is divided into 10 sections and is consistent with the User Manuals:

1. Preaction Systems (Non, Single & Double Interlock);
2. Deluge Systems;
3. Wet Pipe Systems;
4. Dry Pipe Systems (both normal & HP);
5. Cycling Systems (Firecycle III);
6. Surefire Systems.

Followed by:

7. System Options (Shut-off Valve, FD Connection, etc.);
8. VFR-400 Control Panel Options (zones, relays, batteries, etc.);
9. Air Supplies (the usual 4 styles – A,B,C & D), and then,
10. Air Supply Options (Dehydrator, Accelerator, etc.).

To order a TotalPac3:

First, select the type of system required (preaction, deluge, dry, etc...). Then, choose the style of system required (skid mounted, remote controlled or self-contained) and its release system (electric, pneumatic, etc.). Finally, follow this line to the proper part number under the column of the system size (TotalPac3 units are available in 6 sizes: 1½", 2", 3", 4", 6" and 8" diam.). This is the part number that should be ordered. Add the required system options to complete your order.

The Configuration/order Form (doc. # FM-08CD-0-17) uses the same format as the price list.

Provided are additional details on the three styles of TotalPac3 units available:

- **Skid Mounted Units:** Skid Units include only the basic Valve Trim and its required Releasing Trim. Electrical components have to be wired on-site by the contractor. Grooved or flanged connections are provided for water supply, drain and system riser. Remote releasing control panel and air compressor (if required) have to be purchased separately (*they are not provided by FireFlex Systems Inc.*) and installed by the contractor on-site. Every Skid Unit is supplied with its own User Manual and is also serialized for after sales support. Serial Number format is TOTSxxxx.

- **Remote Controlled Units:** These units are composed of the basic Valve, Trim and Releasing Trim, enclosed in a sturdy 14 gauge steel cabinet with one or two front doors and a contractor field wiring junction box on top of the cabinet. All electrical components are factory wired to the field wiring terminal strip. Wiring schematics are included on the inside of the front doors. Grooved or flanged connections are provided for water supply, drain and system riser. Four different air supply options are available and factory assembled. Remote releasing control panel, if required, has to be purchased separately (*they are not provided by FireFlex Systems Inc.*) and installed by the contractor on-site. Every Remote Controlled Unit is supplied with a User Manual and is serialized for after sales support. Serial Number format is TOT3xxxx.

- **Self-Contained Units:** These units are composed of a Remote Controlled Unit as described above, plus a Release Control Panel Enclosure mounted on top of the cabinet. All electrical components are factory wired to the Viking VFR-400 Control Panel, with wiring schematics included on the inside of the front doors. Grooved or flanged connections are provided for water supply, drain and system riser. Four different air supply options are available and factory assembled.

Every self-contained unit is supplied with a User Manual and is serialized for after sales support. Serial Number format is TOT3xxxx.

Refer to the Price List for various options available with each style & system type.

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Preaction Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION NON INTERLOCK	Skid Mounted	Electric	T3PNELSK15 \$23,312	T3PNELSK20 \$26,540	T3PNELSK30 \$29,503	T3PNELSK40 \$32,807	T3PNELSK60 \$38,418	N/A
		Pneumatic	T3PNPNSK15 \$20,562	T3PNPNSK20 \$23,789	T3PNPNSK30 \$26,752	T3PNPNSK40 \$30,057	T3PNPNSK60 \$35,700	N/A
	Without Panel (Remote)	Electric	T3PNELNP15 \$31,500	T3PNELNP20 \$34,727	T3PNELNP30 \$37,684	T3PNELNP40 \$42,045	T3PNELNP60 \$47,629	T3PNELNP80 \$69,708
		Pneumatic	T3PNPNNP15 \$28,743	T3PNPNNP20 \$31,976	T3PNPNNP30 \$34,933	T3PNPNNP40 \$39,294	T3PNPNNP60 \$44,898	T3PNPNNP80 \$67,798
	With VFR-400 – 120V/60Hz	Electric	T3PNELWP15 \$37,458	T3PNELWP20 \$40,685	T3PNELWP30 \$43,636	T3PNELWP40 \$48,125	T3PNELWP60 \$53,620	T3PNELWP80 \$76,553
	PREACTION SINGLE INTERLOCK	Skid Mounted	Electric	T3PSELSK15 \$20,446	T3PSELSK20 \$23,673	T3PSELSK30 \$26,623	T3PSELSK40 \$29,941	T3PSELSK60 \$35,571
Pneumatic			T3PSPNSK15 \$19,171	T3PSPNSK20 \$22,239	T3PSPNSK30 \$25,055	T3PSPNSK40 \$28,209	T3PSPNSK60 \$34,527	N/A
Without Panel (Remote)		Electric	T3PSELNP15 \$28,607	T3PSELNP20 \$31,802	T3PSELNP30 \$34,836	T3PSELNP40 \$39,184	T3PSELNP60 \$44,802	T3PSELNP80 \$65,997
		Pneumatic	T3PSPNNP15 \$28,305	T3PSPNNP20 \$31,532	T3PSPNNP30 \$34,495	T3PSPNNP40 \$38,856	T3PSPNNP60 \$45,459	T3PSPNNP80 \$66,745
With VFR-400 – 120V/60Hz		Electric	T3PSELWP15 \$34,559	T3PSELWP20 \$37,761	T3PSELWP30 \$40,788	T3PSELWP40 \$44,434	T3PSELWP60 \$50,580	T3PSELWP80 \$73,331
PREACTION DOUBLE INTERLOCK Note: NYFD Accepted & FM Approved for use in refrigerated areas only.		Skid Mounted	Elect-Pnelect.	T3PDEPSK15 \$20,517	T3PDEPSK20 \$23,744	T3PDEPSK30 \$26,701	T3PDEPSK40 \$30,005	T3PDEPSK60 \$35,648
	Elect-Pneum.		T3PDPASK15 \$21,824	T3PDPASK20 \$24,852	T3PDPASK30 \$27,641	T3PDPASK40 \$30,739	T3PDPASK60 \$36,067	N/A
	Pneum-Pneum.		T3PDPPSK15 \$20,465	T3PDPPSK20 \$23,493	T3PDPPSK30 \$26,282	T3PDPPSK40 \$29,380	T3PDPPSK60 \$34,675	N/A
	Without Panel (Remote)	Elect-Pnelect.	T3PDEPNP15 \$28,685	T3PDEPNP20 \$31,880	T3PDEPNP30 \$34,901	T3PDEPNP40 \$39,262	T3PDEPNP60 \$44,879	T3PDEPNP80 \$65,999
		Elect-Pneum.	T3PDPANP15 \$29,490	T3PDPANP20 \$32,504	T3PDPANP30 \$35,300	T3PDPANP40 \$39,423	T3PDPANP60 \$44,628	T3PDPANP80 \$67,560
		Pneum-Pneum.	T3PDPPNP15 \$28,156	T3PDPPNP20 \$31,190	T3PDPPNP30 \$33,973	T3PDPPNP40 \$69,870	T3PDPPNP60 \$43,281	T3PDPPNP80 \$67,885
	With VFR-400 – 120V/60Hz	Elect-Pnelect.	T3PDEPWP15 \$34,643	T3PDEPWP20 \$37,838	T3PDEPWP30 \$40,859	T3PDEPWP40 \$45,336	T3PDEPWP60 \$50,947	T3PDEPWP80 \$73,333
		Elect-Pneum.	T3PDPAWP15 \$35,088	T3PDPAWP20 \$38,102	T3PDPAWP30 \$40,891	T3PDPAWP40 \$45,130	T3PDPAWP60 \$50,341	T3PDPAWP80 \$74,479

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Deluge Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
DELUGE	Skid Mounted	Electric	T3DELSK15 \$19,911	T3DELSK20 \$23,602	T3DELSK30 \$26,520	T3DELSK40 \$28,852	T3DELSK60 \$33,439	N/A
		Pneumatic	T3DEPNK15 \$19,660	T3DEPNK20 \$22,320	T3DEPNK30 \$25,238	T3DEPNK40 \$28,530	T3DEPNK60 \$34,108	N/A
		Hydraulic	T3DEHYSK15 \$18,107	T3DEHYSK20 \$20,839	T3DEHYSK30 \$23,750	T3DEHYSK40 \$27,042	T3DEHYSK60 \$31,603	N/A

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
DELUGE	Without Panel (Remote)	Electric	T3DEELNP15 \$28,343	T3DEELNP20 \$30,991	T3DEELNP30 \$33,786	T3DEELNP40 \$38,263	T3DEELNP60 \$42,818	T3DEELNP80 \$62,666
		Pneumatic	T3DEPNNP15 \$27,937	T3DEPNNP20 \$30,669	T3DEPNNP30 \$33,580	T3DEPNNP40 \$37,684	T3DEPNNP60 \$43,481	T3DEPNNP80 \$63,104
		Hydraulic	T3DEHYNP15 \$26,449	T3DEHYNP20 \$29,181	T3DEHYNP30 \$32,092	T3DEHYNP40 \$36,447	T3DEHYNP60 \$40,995	T3DEHYNP80 \$61,992
	With VFR-400 – 120V/60Hz	Electric	T3DEELWP15 \$34,302	T3DEELWP20 \$37,026	T3DEELWP30 \$39,829	T3DEELWP40 \$44,434	T3DEELWP60 \$48,976	T3DEELWP80 \$70,012

Wet Pipe Systems:

WET PIPE	Skid Mounted	N/A	N/A	N/A	T3WETESK30 \$11,743	T3WETESK40 \$12,529	T3WETESK60 \$14,056	N/A
	In Cabinet	N/A	N/A	N/A	T3WETENP30 \$20,691	T3WETENP40 \$22,700	T3WETENP60 \$24,549	T3WETENP80 \$29,714
System Options:	Constant Pressure Trim	T3CONPRESS \$667		Excess Pressure Pump 1/3 HP (120V/60Hz)		T3WETEPP03 POA		
	Retard Chamber	T3WETRET00 \$1,984		Excess Pressure Pump 1/2 HP (120V/60Hz)		T3WETEPP05 POA		

Dry Pipe Systems:

DRY PIPE 175 psi	Skid Mounted	N/A	N/A	N/A	N/A	T3DRYESK40 \$18,906	T3DRYESK60 \$22,069	N/A
	In Cabinet (Remote)	N/A	N/A	N/A	N/A	T3DRYENP40 \$30,347	T3DRYENP60 \$33,522	N/A
HP DRY PIPE 250 psi	Skid Mounted	N/A	T3DHPESK15 POA	T3DHPESK20 POA	T3DHPESK30 POA	T3DHPESK40 POA	T3DHPESK60 POA	N/A
	In Cabinet (Remote)	N/A	T3DHPENP15 \$24,987	T3DHPENP20 \$28,208	T3DHPENP30 \$31,171	T3DHPENP40 \$35,532	T3DHPENP60 \$41,130	T3DHPENP80 \$59,387

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Firecycle® III Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION SINGLE INTERLOCK	Skid Mounted	Firecycle III	T3FSINSK15 \$29,239	T3FSINSK20 \$34,154	T3FSINSK30 \$37,735	T3FSINSK40 \$41,742	T3FSINSK60 \$48,589	N/A
	Without Panel (Remote)		T3FSINNP15 \$36,969	T3FSINNP20 \$41,883	T3FSINNP30 \$45,800	T3FSINNP40 \$50,960	T3FSINNP60 \$57,434	T3FSINNP80 \$72,572
	With VFR-400 – 120V/60Hz		T3FSINWP15 \$43,977	T3FSINWP20 \$48,886	T3FSINWP30 \$52,796	T3FSINWP40 \$58,091	T3FSINWP60 \$64,242	T3FSINWP80 \$79,835
PREACTION DOUBLE INTERLOCK	Skid Mounted	Firecycle III	T3FDOUSK15 \$29,239	T3FDOUSK20 \$34,154	T3FDOUSK30 \$37,735	T3FDOUSK40 \$41,742	T3FDOUSK60 \$48,589	N/A
	Without Panel (Remote)		T3FDOUNP15 \$36,969	T3FDOUNP20 \$41,883	T3FDOUNP30 \$45,800	T3FDOUNP40 \$50,960	T3FDOUNP60 \$57,434	T3FDOUNP80 \$72,832
	With VFR-400 – 120V/60Hz		T3FDOWP15 \$43,977	T3FDOWP20 \$48,886	T3FDOWP30 \$52,796	T3FDOWP40 \$58,091	T3FDOWP60 \$64,242	T3FDOWP80 \$79,887

SureFire® Fail Safe Preaction Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION SINGLE INTERLOCK	Skid Mounted	Surefire	T3SFSISK15 \$27,229	T3SFSISK20 \$30,701	T3SFSISK30 \$33,883	T3SFSISK40 \$37,452	T3SFSISK60 \$43,520	N/A
	Without Panel (Remote)		T3SFSINP15 \$35,377	T3SFSINP20 \$38,856	T3SFSINP30 \$42,045	T3SFSINP40 \$46,740	T3SFSINP60 \$52,776	T3SFSINP80 \$70,242
	With VFR-400 - 120V/60Hz		T3SFSIWP15 \$41,690	T3SFSIWP20 \$45,162	T3SFSIWP30 \$48,351	T3SFSIWP40 \$53,176	T3SFSIWP60 \$59,211	T3SFSIWP80 \$77,520
PREACTION DOUBLE INTERLOCK <small>Note: NYFD & FM Approved for use in refrigerated areas only.</small>	Skid Mounted	Surefire	T3SFDOSK15 \$27,796	T3SFDOSK20 \$31,268	T3SFDOSK30 \$34,456	T3SFDOSK40 \$38,025	T3SFDOSK60 \$44,093	N/A
	Without Panel (Remote)		T3SFDONP15 \$35,957	T3SFDONP20 \$36,292	T3SFDONP30 \$42,611	T3SFDONP40 \$47,294	T3SFDONP60 \$52,190	T3SFDONP80 \$70,000
	With VFR-400 - 120V/60Hz		T3SFDOWP15 \$42,264	T3SFDOWP20 \$45,736	T3SFDOWP30 \$48,918	T3SFDOWP40 \$53,749	T3SFDOWP60 \$59,785	T3SFDOWP80 \$77,527

NEW - TOTALPAC®3 Integrated Fire Protection Systems

System Options:

Shut-off Valve & Sight Glass (Not available for Wet & Dry Pipe systems)	T3SHUTV015 \$1,472	T3SHUTV020 \$1,553	T3SHUTV030 \$1,867	T3SHUTV040 \$2,007	T3SHUTV060 \$2,468	N/A
Fire Department Connection (Always on right hand side)	T3FIRDPT15 \$476	T3FIRDPT20 \$476	T3FIRDPT30 \$528	T3FIRDPT40 \$557	T3FIRDPT60 \$718	N/A
Semi-Flanged Inlets & Outlet:	T3SEMFLG15 \$1,194	T3SEMFLG20 \$1,062	T3SEMFLG30 \$1,245	T3SEMFLG40 \$1,413	T3SEMFLG60 \$1,714	T3SEMFLG80 \$2,244
Full-Flanged Inlets & Outlet:	PRICE ON REQUEST ONLY					
Elevator Option	T3ELEVATOR			PRICE ON REQUEST ONLY SPECIAL CONDITIONS APPLY		
Anti Column device	T3ANTCOLD1			\$389		
Galvanized Main Inlet & Riser	T3GALVOPTI			\$1,147		

VFR-400 Releasing Panel Options:

Available with 120V / 60Hz or 220V / 50Hz

Emergency Batteries:	Standard Systems:	7 AH (Included with unit, use for replacement only) T3BAT02407 \$198	12 AH (FM's 90 Hrs Stand-by) T3BAT02412 \$513
	Surefire & Firecycle III Systems:	12 AH (Included with unit, use for replacement only) T3BAT02412 \$513	17 AH (FM's 90 Hrs Stand-by) T3BAT02417 POA
VFR-400 Panel Options:	L.A. Auxiliary Contacts – T3LAOPTION \$73	Chicago Auxiliary Contacts – T3CHOPTION \$73	NYFD Kit – T3VFRPNYOP \$392 (Class A Modules included do not duplicate)
	Rem. Annunciator – T3VFRP4410 \$1,194		
	Class "A" Initiating Ccts – T3VFRPCA2Z \$485	Class "A" Indicating Ccts – T3VFRPCAM2 \$373	Relay Module – T3OPTARM44 \$1,428

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Air Supplies:

Air Supplies for Skids (Trim only – NO compressor)	For Preaction – Surefire Firecycle III & HP Dry Pipe	Deluge Pneum. Release	Single Pneum. & Double Int'l'k Pneum-Pneum. Release
	T3ARTITSK1 \$762	T3ARTITSK2 \$732	T3ARTITSK3 \$1,494

Air Supplies for Cabinets	Style "A" (Tankless Air Compressor)						Style "B"	Style "C"	Style "D"
	1/6 HP	1/3 HP	1/2 HP	1 HP	1 1/2 HP (8" unit only)	2 HP (8" unit only)	Air Pressure Maintenance Device for Sprinkler Piping	Air Pressure Maintenance Device for Pilot Line	Air Shut-off Valve, Pressure Gauge, & Pressure Switch Only
120 V / 60 Hz:	T3AIRK0A02 \$4,394	T3AIRK0A03 \$5,280	T3AIRK0A05 \$5,991	T3AIRK0A10 \$7,214	T3AIRK0A15 POA	T3AIRK0A20 POA	T3AIRK0B00 \$2,087	T3AIRK0C00 \$2,021	T3AIRK0D00 \$469
220V / 50 Hz	T3AIRK2A02 \$5,331	T3AIRK2A03 \$6,349	T3AIRK2A05 \$7,801	T3AIRK2A10 \$8,986	T3AIRK2A15 POA	N/A			

Notes:

1. Style "A" Air Supply cannot be mixed with Style "B".
2. In the case of a Preaction System with Pilot Line, order either one Style "A" with one Style "C" if you need a tankless air compressor in the cabinet for the sprinklers piping, OR, one Style "B" and one Style "C" if you want both air supplies to be located outside the system cabinet.
3. Pilot Line Air Supply will always be provided by a source located outside the TP3 Cabinet, supplied by others (not FireFlex).
4. Air Supply Style "D" is used when air supply and regulation is provided by others, as is the case with plant air, or with refrigerated areas when a dry air supply as described in NFPA-13 is required.
5. 1 HP Air compressor available on 4" & 6" systems only.
6. 1 ½ HP & 2 HP Air compressors available on 8" systems only.

Air Supply Options:

Accelerator E-1	Without Anti-flood Device (For Preaction, Pneum. Rel. Pilot Line & HP Dry only)	With Anti-flood Device (For Standard Dry Pipe only)
		T3ACCELE1P \$2,944
Dehydrator	T3DEHYDRAT \$3,252	

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Terms and Conditions

This price list should be used in conjunction with the VIKING TotalPac3 Configuration/Order Form (FM-08CD-0-17 latest revision).

All prices are NET and are indicated in US dollars, FOB our plant in Boisbriand, Quebec (Canada). For special discounts or configurations, please contact FireFlex Systems Customer Service.

Listings and Approvals: Most TotalPac3 Configurations in our product range are cULus Listed & FM Approved as factory-built complete units. Any system modification, to meet project specs or local AHJ requirements, ordered as a custom built system will void the Listing on the TotalPac3 as an assembly but individual components Listings/Approvals will remain.

Special Order Item: Every TotalPac3 Unit is a Special Order Item which is built to order. It can therefore not be cancelled nor returned without FireFlex Systems explicit consent or authorization.

Returns & Credits: The following conditions shall apply to all TotalPac3 units returned for credit:

- Unit(s) shall be of current design, three months old maximum after shipping date from the factory;
- Unit(s) shall still be in its (their) original packing (never unpacked), unused and not installed. Any unit not in this condition is subject to additional charges to cover inspection, handling, repackaging, refurbishment, or any other expenses incurred by FireFlex Systems in accepting the unit(s).
- The customer is responsible for freight charges to return overstocked unit(s), unit(s) no longer required, or ordered by mistake. Any damage incurred in transit will be deducted from the credit value.

NOTE: An RMA Number shall be obtained from FireFlex' Customer Service PRIOR to returning any unit. Please provide unit(s) serial number(s) as indicated on the shipping label of the unit(s) (format: TOTSxxxx or TOT3xxxx) as well as the address for us to make arrangements for pick-up.

Please note that a minimum restocking charge of \$ 1,500.00 is applicable on all TotalPac3 returns. Systems older than 3 months after date of shipment will NOT be accepted for credit.

Upon receiving returned unit(s), FireFlex Systems will inspect each unit. If any damage is found, the credit amount will be adjusted accordingly.

Contractor must ascertain the unit is returned in its original packing, including the internal plastic liner. This liner protects the unit finish against abrasion damage during transport.

Warranty: FireFlex Systems provides warranty on all TotalPac3 Units for a period of 1 (one) year from time of shipping. Warranty does not cover labor. We will replace any component found defective at no charge during this period but will NOT reimburse labor charges incurred by the contractor. In the case of unauthorized modification of, or tampering with the unit, the warranty is void.

The warranty on batteries warranty is limited to 3 (three) months. Refer to the terms of our Standard Warranty for all details (provided with every TotalPac3 User's Manual).