

Residential Sprinkler Quick Reference Guide

This guide is intended for general reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and always consult with the AHJ. Viking makes no representation or warranty as to whether following this guide will satisfy any rule or requirement. Please visit www.vikinggroupinc.com for the most current technical data and product specifications. All products must be installed in accordance with the manufacturer's current installation instructions. Viking reserves the right to change product specifications at any time without notice and without incurring obligation.



Pendent and Recessed Pendent Sprinklers

Recessed adjustment up to 5/8" (16 mm)

3.0 (43) K-factor



VK470, Part No. 17147
Technical datasheet F_061011

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Enables two-head design with flows less than 20 gpm (75,7 lpm)
- Can optimize NFPA 13 residential designs when combined with larger K-factor residential sprinklers
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	8 (30)	7.1 (49)
14 x 14 (4,3x4,3)	10 (38)	11.1 (77)
15 x 15 (4,6x4,6)	12 (45)	16 (110)
16 x 16 (4,9x4,9)	13 (49)	18.8 (129)

4.3 (62) K-factor



VK430, Part No. 09530
Technical datasheet F_082095

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Continually listed by UL since 1995
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	12 (45)	7.8 (54)
14 x 14 (4,3x4,3)	13 (49)	9.1 (63)
16 x 16 (4,9x4,9)	13 (49)	9.1 (63)
18 x 18 (5,5x5,5)	17 (64)	15.6 (108)
20 x 20 (6,1x6,1)	21 (80)	23.9 (164)

4.9 (71) K-factor



VK468, Part No. 13637
Technical datasheet F_012706

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	20 (76)	16.7 (115)

5.2 (75) K-factor



VK466, Part No. 13781
Technical datasheet F_019406

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	14 (53)	7.2 (50)
14 x 14 (4,3x4,3)	14 (53)	7.2 (50)
16 x 16 (4,9x4,9)	14 (53)	7.2 (50)
18 x 18 (5,5x5,5)	17 (64)	10.7 (74)
20 x 20 (6,1x6,1)	20 (76)	14.8 (1.02)

5.8 (84) K-factor



VK472, Part No. 16130
Technical datasheet F_121409

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	16 (61)	7.6 (52)
14 x 14 (4,3x4,3)	16 (61)	7.6 (52)
16 x 16 (4,9x4,9)	16 (61)	7.6 (52)
18 x 18 (5,5x5,5)	17 (64)	8.6 (59)
20 x 20 (6,1x6,1)	21 (80)	13.1 (90)

7.4 (107) K-factor



VK458, Part No. 13230
Technical datasheet F_042005

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	20 (76)	7.3 (50)
14 x 14 (4,3x4,3)	20 (76)	7.3 (50)
16 x 16 (4,9x4,9)	20 (76)	7.3 (50)
18 x 18 (5,5x5,5)	22 (83)	8.8 (61)
20 x 20 (6,1x6,1)	24 (91)	10.5 (73)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

All application data is for smooth, flat, horizontal ceilings unless otherwise noted, and is per each sprinkler's cULus Listing for systems designed to NFPA 13D or NFPA 13R requiring a 0.05 gpm/ft² density.

Trusted above all.™



Flat Plate Concealed Pendent Sprinklers

Cover Plate Temp = 135°F/57°C; Adjustment up to 1/2" (13 mm)

3.0 (43) K-factor



VK488, Part No. 18325AC
Technical datasheet F_073012

- Sprinkler temp = 165°F/74°C and 205°F/96°C*
- Enables two-head design with flows less than 20 gpm (76 lpm)
- Can optimize NFPA 13 residential designs when combined with larger K-factor residential sprinklers

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	8 (30)	7.1 (49)
14 x 14 (4,3x4,3)	11 (42)	13.4 (92)
16 x 16 (6,1x6,1)	13 (49)	18.8 (130)

*UL Listed flow rates are identical for both temperature ratings.

4.9 (71) K-factor



VK494, Part No. 20759
Technical datasheet F_012116

- Sprinkler temp = 155°F/68°C and 200°F/93°C*
- Intermediate temperature models provide greater installation flexibility
- Available with either standard, large, or square cover plate
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	20 (76)	16.7 (115)

*UL Listed flow rates are identical for both temperature ratings.

5.8 (84) K-factor



VK498, Part No. 22037
Technical datasheet F_112817

- Sprinkler temp = 155°F/68°C and 200°F/93°C*
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	16 (61)	7.6 (52)
14 x 14 (4,3x4,3)	16 (61)	7.6 (52)
16 x 16 (4,9x4,9)	16 (61)	7.6 (52)
18 x 18 (5,5x5,5)	17 (64)	8.6 (59)
20 x 20 (6,1x6,1)	20 (76)	11.9 (82)

*UL Listed flow rates are identical for both temperature ratings.

Flat Plate Concealed Sidewall Sprinklers

Cover plate temp = 135°F/57°C

4.0 (58) K-factor



VK480, Part No. 16116AC
Technical datasheet F_121609

- Sprinkler temp = 165°F/74°C and 205°F/96°C
- Use cover plate 16207MA/W
- White cover plate is standard; can be custom painted to match any decor
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	4-6" (102mm-152mm) From Ceiling		6-12" (152mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	11 (42)*	7.6 (52)	12 (46)**	9.0 (62)
14 x 14 (4,3x4,3)	13 (49)*	10.6 (73)	14 (53)**	12.3 (84)
16 x 16 (4,9x4,9)	16 (61)*	16.0 (110)	16 (61)**	16.0 (110)
16 x 18 (4,9x5,5)	17 (64)*	18.1 (125)	18 (68)**	20.3 (140)

*Centerline of the sprinkler located 4-3/8" (111mm) to 6-3/8" (162mm) below the ceiling.

**Centerline of the sprinkler located 6-3/8" (162mm) to 12-3/8" (314mm) below the ceiling.

5.8 (84) K-factor



VK490, Part No. 20409
Technical datasheet F_032116

- Sprinkler temp = 165°F/74°C and 205°F/96°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft²)

Coverage Area ft (m)	4-6" (102mm-152mm) From Ceiling		6-12" (152mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3.7 x 3.7)	16 (70)*	7.6 (52)	17 (64)**	8.6 (59)
14 x 14 (4.3 x 4.3)	17 (64)*	8.6 (59)	17 (64)**	8.6 (59)
16 x 16 (4.9 x 4.9)	18 (68)*	9.6 (66)	19 (72)**	10.7 (74)
16 x 18 (4.9 x 5.5)	21 (80)*	13.1 (90)	21 (80)**	13.1 (90)
16 x 20 (4.9 x 6.1)	23 (87)*	15.7 (108)	26 (98)**	20.1 (139)
16 x 22 (4.9 x 6.7)	31 (117)*	28.6 (197)	31 (117)**	28.6 (197)
18 x 20 (5.5 x 6.1)	28 (106)*	23.3 (161)	28 (106)**	23.3 (161)

*Centerline of the sprinkler located 4-3/8" (111mm) to 6-3/8" (162mm) below the ceiling.

**Centerline of the sprinkler located 6-3/8" (162mm) to 12-3/8" (314mm) below the ceiling.

Domed Concealed Pendent Sprinklers

Cover Plate Temp = 135°F / 57°C; Adjustment up to 1/2" (13 mm)

4.9 (71) K-factor



VK468-D, Part No. 13637A-X
Technical datasheet F_020206

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	20 (76)	16.7 (115)

5.2 (75) K-factor



VK466-D, Part No. 13781A-X
Technical datasheet F_091606

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	14 (53)	7.2 (50)
14 x 14 (4,3x4,3)	14 (53)	7.2 (50)
16 x 16 (4,9x4,9)	14 (53)	7.2 (50)
18 x 18 (5,5x5,5)	17 (64)	10.7 (74)
20 x 20 (6,1x6,1)	20 (76)	14.8 (102)

7.4 (107) K-factor



VK458-D, Part No. 13230ABX
Technical datasheet F_092305

- Sprinkler temp = 155°F/68°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	20 (76)	7.3 (50)
14 x 14 (4,3x4,3)	20 (76)	7.3 (50)
16 x 16 (4,9x4,9)	20 (76)	7.3 (50)
18 x 18 (5,5x5,5)	23 (87)	9.7 (67)
20 x 20 (6,1x6,1)	28 (106)	14.3 (99)

Flush Concealed Pendent Sprinklers

Adjustment up to 5/8" (16mm) with ceiling ring (Part No. 15618)

4.9 (71) K-factor



VK476, Part No. 15630
Technical datasheet F_120608

- Sprinkler temp = 165°F/74°C
- Sprinkler and escutcheon sold together

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	21 (80)	18.4 (127)

Upright Sprinklers

Available in 155°F/68°C and 175°F/79°C

4.9 (71) K-factor



VK467, Part No. 19154
Technical datasheet F_090413

- The industry's first and only residential upright sprinkler
- May provide significant design advantages in loft-type residential structures
- Listed with beam ceilings up to 14" (356 mm); deflector should be installed 1" - 3" below 14" beams
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	Horizontal Ceiling		
	Flow gpm (lpm)	Pressure psi (kPa)	Deflector to Ceiling
12 x 12 (3,7x3,7)	14 (53)	8.2 (56)	3-5" (76mm- 127mm)
14 x 14 (4,3x4,3)	14 (53)	8.2 (56)	
16 x 16 (4,9x4,9)	16 (61)	10.7 (73)	
12 x 12 (3,7x3,7)	15 (57)	9.4 (65)	*5-10" (152mm- 254mm)
12 x 12 (3,7x3,7)	15 (57)	9.4 (65)	
16 x 16 (4,9x4,9)	18 (68)	13.5 (93)	

*Note: Also applies to installations 1-3" below 14" beams at 155°F/68°C temperature rating only.

Viking offers lead-free versions of several Freedom® residential sprinklers. Please refer to Viking's technical datasheets for complete design and installation data. Lead content complies with the definition of 'Lead Free' established in the Reduction of Lead in Drinking Water Act (S.3874) endorsed by AWWA's Water Utility Council, and California Assembly Bill # 1953.

Horizontal Sidewall Sprinklers

Available in 155°F/68°C and 175°F/79°C; Recessed adjustment up to 5/8" (16mm)

3.0 (43) K-factor



VK479, Part No. 19707
Technical datasheet F_012915

- Sprinkler temp = 155°F/68°C
- Patented "flow shaper" design provides the ultimate combination of low flows and starting pressures
- Can optimize NFPA 13 residential designs when combined with larger K-factor residential sprinklers
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	4-12" (102mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	11 (42)	13.4 (92)
14 x 14 (4,3x4,3)	13 (49)	18.8 (129)
16 x 16 (4,9x4,9)	13 (49)	18.8 (129)

4.0 (58) K-factor



VK486, Part No. 17315
Technical datasheet F_082411

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Patented "flow shaper" design provides the ultimate combination of low flows and starting pressures
- Lowest flow rate in the industry
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	4-6" (102mm-152mm) From Ceiling		6-12" (152mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	11 (42)	7.6 (52)	12 (46)	9.0 (62)
14 x 14 (4,3x4,3)	12 (46)	9.0 (62)	12 (46)	9.0 (62)
16 x 16 (4,9x4,9)	13 (49)	10.6 (73)	14 (53)	12.3 (85)
16 x 18 (4,9x5,5)	16 (61)	16.0 (110)	16 (61)	16 (110)
16 x 20 (4,9x6,1)	22 (83)	30.3 (209)	23 (87)	33.1 (228)
16 x 22 (4,9x6,7)	24 (91)	36.0 (248)	26 (98)	42.3 (291)
18 x 18 (5,5x5,5)	18 (68)	20.3 (140)	18 (68)	20.3 (140)
18 x 20 (5,5x6,1)	22 (83)	30.3 (209)	23 (87)	33.1 (228)
20 x 20 (6,1x6,1)	22 (83)	30.3 (209)	24 (91)	36.0 (248)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

4.2 (60) K-factor



VK484, Part No. 16240
Technical datasheet F_050310

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	13 (49)	9.6 (66)	14 (53)	11.1 (77)
14 x 14 (4,3x4,3)	14 (53)	11.1 (77)	16 (61)	14.5 (100)
16 x 16 (4,9x4,9)	16 (61)	14.5 (100)	18 (68)	18.4 (127)
16 x 18 (4,9x5,5)	19 (72)	20.5 (141)	20 (76)	22.7 (156)
16 x 20 (4,9x6,1)	22 (83)	27.4 (189)	25 (95)	35.4 (244)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

5.8 (84) K-factor



VK460, Part No. 13933
Technical datasheet F_110205

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Patented "flow shaper" design provides the ultimate combination of low flows and starting pressures
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	16 (61)	7.6 (52)	16 (61)	7.6 (52)
14 x 14 (4,3x4,3)	16 (61)	7.6 (52)	18 (68)	9.7 (67)
14 x 26 (4,3x7,9)	42 (159)	52.4 (362)	46 (174)	62.9 (434)
16 x 16 (4,9x4,9)	20 (76)	11.9 (82)	24 (91)	17.1 (120)
16 x 18 (4,9x5,5)	22 (83)	14.4 (99)	27 (102)	21.7 (149)
16 x 20 (4,9x6,1)	26 (98)	20.1 (139)	32 (121)	30.4 (210)
16 x 22 (4,9x6,7)	31 (117)	28.6 (197)	37 (140)	40.7(281)
16 x 24 (4,9x7,3)	38 (144)	42.9 (296)	42 (159)	52.4 (362)
18 x 18 (5,5x5,5)	23 (87)	15.7 (110)	29 (110)	25.0 (170)
18 x 20 (5,5x6,1)	29 (110)	25.0 (170)	35 (133)	36.4 (251)
20 x 20 (6,1x6,1)	30 (114)	26.8 (180)	36 (136)	38.5 (266)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

Flat Cover Plate Finishes

Freedom offers the smallest available cover plates and low-profile recessed sprinkler models, providing optimum protection while blending with décor. A choice of nine standard finishes and unlimited custom colors make Freedom almost undetectable once installed.

Viking concealed cover plates are UL Listed to accept any type and manufacturer of paint within the constraints of Viking's quality control requirements. All custom color painted cover plates have a label affixed to the inside of the cover that identifies the color by name, and that also carries a representative paint dot.

To order custom cover plate painting, contact your Viking SupplyNet customer service representative.



Our exclusive Colormatch® service can duplicate any paint sample or color chip, providing endless options for a beautiful, finished look.

Standard Finishes



White



Ivory



Black



Antique
Brass



Brushed
Brass



Brushed
Chrome



Bright
Brass



Polished
Chrome



Brushed
Copper

Cover Plates

Technical datasheet Sprinkler F_040600



Standard, Part No. 13504
2-3/4" (70mm) diameter



Square, Part No. 15394
3-5/16" (84mm) L x W



Domed, Part No. 12207
3-1/8" (80mm) diameter



Large, Part No. 13642
3-5/16" (84mm) diameter
(Part No. 16207 for VK480 and VK490)

Recessed and Sloped Ceiling Escutcheons

Technical datasheet Sprinkler F_122698



- E-1 – Push-on, Part No. 11123-3/8", 06419-1/2", 20369-3/4"
- E-2 – Threaded, Part No. 11038-1/2", 20130-3/4"
- E-3 – Threaded, Part No. 18347-1/2", 18348-3/4"
- F-1 – Adjustable, Part No. 06911A-1/2", 20371-3/4"



- G-1 – Sloped, Part No. 14315-1/2"
Part No. 20133-3/4"
Push-on

Tools

Technical datasheet Sprinkler F_122598



Cabinet Wrench & Sprinkler Cap Removal Tool, Part No. 13619
(See Part No. 16267 for Models VK480 and VK490 and Part No. 14047 for Model VK494)




Concealed Cover Installer Tool, Standard Diameter, Part No. 14412
Concealed Cover Installer Tool, Large Diameter, Part No. 14867



Escutcheon Installer Tool, Part No. 15915 (Technical datasheet F_051808)



Individual tools and length of pipe all sold separately.



Viking SupplyNet Regional Headquarters

Viking SupplyNet - U.S. East

48 Cranberry Rd
Parsippany, NJ 07054
Phone: 973-541-2580

Viking SupplyNet - Canada

325 Vaughan Valley Blvd.
Woodbridge, Ontario L4H 3B5
Phone: 866-670-3550

Viking SupplyNet - Mexico

Irving TX Office
972-466-0933

Viking SupplyNet - Latin America

Ft. Lauderdale FL Office
954-791-2901

Viking SupplyNet - U.S. East


100 Piedmont Court, Suite A
Doraville, GA 30340
Phone: 770-446-3068

Viking SupplyNet - U.S. Central

2353 International St
Columbus, OH 43228
Phone: 614-527-5800

Viking SupplyNet - U.S. West

9101 Sorensen Ave.
Santa Fe Springs, CA 90670
Phone: 562-903-7274



U.S. and Canada Locations

- Distribution Center
- ◐ Distribution + Fabrication

Viking SupplyNet has thirty-two distribution centers in North America - fourteen with turn-key fabrication services.

Visit www.vikinggroupinc.com for a Viking SupplyNet location near you.