



Viking Foam-Water Sprinklers | FM Approved and UL Listed

It takes a lot to be a proven “Foam Sprinkler”

Sprinkler applications are especially challenging for any foam due to the very low operating pressure and expansion reached. Applying foam through a sprinkler head is a very forceful application method and requires foam that can handle direct application and partial submersion into the fuel without losing its fire performance and burn back resistance.

Features and advantages of Viking's foam-water sprinklers:

- Comprehensive range of foam-water sprinklers.
- Approved with AFFF 1% S, AFFF 3% S, AFFF 3% Mil Spec and ARC 3X3 S foam concentrates.
- Extensive testing with Viking foam concentrates.
- All foams are C6 compliant with the EPA 2010/15 Stewardship Program.
- Approved for various fuel groups.
- FM Approved to heights up to 33 ft (10.1 m).
- Meeting the requirements of FM Global Data Sheet 4-12 and UL 162.
- Part of a complete foam system package from one trusted source.

Contact your local Viking SupplyNet team to place an order today!

The Viking Corporation

210 N Industrial Park Drive, Hastings, Michigan 49058

Telephone: (800) 968-9501

Email: products@vikingcorp.com

www.vikinggroupinc.com

Trusted above all.™

Models: Pendent (SSP)
Upright (SSU)

Listings/Approvals*: FM Approved (FM5130)
UL Listed (UL162)

K-factor: K5.6 (K80)
K8.0 (K115)
K11.2 (K161)
K16.8 (K242)

Connection: 1/2" (15mm)
3/4" (20mm)

Material: Brass

Finish: Various
(refer to the technical documentation)

Density: Refer to the technical documentaton

Expansion: Typically 2:1 to 4:1

Configuration: Closed and open head

*For all applicable approvals, please refer to the technical documentation or contact your local Viking sales office.

VIKING®