


# The Eddy Pipe Family

Bull Moose Tube Company's "Eddy Pipe" brand sprinkler pipe is produced to meet sprinkler pipe standards & applications. Here are just a few advantages of Eddy Pipe:

- All pipe products are UL Listed (for U.S. and Canada), and have been Approved by Factory Mutual.
- Excellent Production & coating capabilities, tighter tolerances, and our unique steel properties make our pipe excellent for roll grooving, welding, threading, and plain end fittings.
- All products are dual certified to ASTM A-135 and A-795.
- Available in specific cut to order lengths from regular mill rollings.
- More popular sizes roll every two weeks.
- Floor stock available in various lengths.
- Available with coating or bare.
- Ultra Eddy, Eddy Flow, Eddylite, and Eddythread 40 offer cost savings along with superior hydraulics without compromising service life.



- ◆ **Schedule 10 and Schedule 40:** FM Approved and UL Listed sprinkler pipe
- ◆ **Eddy Flow:** Cost effective replacement for Schedule 10
- ◆ **Eddylite:** Lightwall threadable with standard outside diameter
- ◆ **Eddythread 40:** Lightwall threadable Schedule 40 replacement with Corrosion Resistance Ratio of 1.0
- ◆ **Ultra Eddy:** Lightwall roll groovable pipe



A CAPARO company

1819 Clarkson Road  
Chesterfield, MO 63017  
(800) 325-4467  
FAX: (636) 537-2645  
[www.bullmoosetube.com](http://www.bullmoosetube.com)  
e-mail: [sales@bullmoosetube.com](mailto:sales@bullmoosetube.com)

For additional information,  
contact your salesperson today at  
(800) 325-4467 or (636) 537-2600  
in the USA, or from Canada  
call (800) 882-4666



## “BMT - Eddy Pipe” Sizes Available

	NPS (in)	1	1 1/4	1 1/2	2	2 1/2	3	4
Ultra Eddy	O.D. (in)	1.315	1.660	1.900	2.375			
	I.D. (in)	1.201	1.546	1.786	2.261			
	Empty Weight (lbs/ft)	0.868	1.107	1.274	1.604			
	Water-Filled Weight (lbs/ft)	1.359	1.920	2.360	3.344			
	C.R.R.	2.17	1.40	1.11	1.00			
Eddy Flow	O.D. (in)		1.660	1.900	2.375	2.875	3.500	4.500
	I.D. (in)		1.530	1.728	2.203	2.705	3.334	4.310
	Empty Weight (lbs/ft)		1.222	1.844	2.330	2.809	3.361	4.968
	Water-Filled Weight (lbs/ft)		2.019	2.860	3.982	5.299	7.144	11.290
	C.R.R.		1.98	3.44	2.78	1.66	1.00	1.00
Schedule 10	O.D. (in)	1.315	1.660	1.900	2.375	2.875	3.500	4.500
	I.D. (in)	1.097	1.442	1.682	2.157	2.635	3.260	4.260
	Empty Weight (lbs/ft)	1.410	1.810	2.090	2.640	3.530	4.340	5.620
	Water-Filled Weight (lbs/ft)	1.820	2.518	3.053	4.223	5.893	7.957	11.796
	C.R.R.	15.27	9.91	7.76	6.27	4.92	3.54	2.50
Eddylite	O.D. (in)	1.315	1.660	1.900	2.375			
	I.D. (in)	1.137	1.482	1.712	2.177			
	Empty Weight (lbs/ft)	1.260	1.617	1.967	2.617			
	Water-Filled Weight (lbs/ft)	1.700	2.364	2.965	4.230			
	C.R.R.	0.13	0.08	0.12	0.16			
Eddythread 40	O.D. (in)	1.295	1.650	1.900	2.375			
	I.D. (in)	1.083	1.418	1.654	2.123			
	Empty Weight (lbs/ft)	1.461	2.070	2.547	3.308			
	Water-Filled Weight (lbs/ft)	1.860	2.754	3.478	4.842			
	C.R.R.	1.00	1.00	1.00	1.00			
Schedule 40	O.D. (in)	1.315	1.660	1.900	2.375	2.875	3.500	4.500
	I.D. (in)	1.049	1.380	1.610	2.067	2.469	3.068	4.026
	Empty Weight (lbs/ft)	1.680	2.270	2.720	3.660	5.800	7.580	10.800
	Water-Filled Weight (lbs/ft)	2.055	2.918	3.602	5.114	7.875	10.783	16.316
	C.R.R.	1.00	1.00	1.00	1.00	1.00	1.00	1.00

**Metric conversions table is also available**

\* All Weights are Nominal  
N/A: Not Applicable

#### PIPE PREPARATION

For proper operation, all pipe surfaces should be cleaned prior to installation. In order to provide a leak-tight seat for the gasket, pipe surfaces should be free from indentations and projections from the end of the pipe to the groove. All loose paint, scale, dirt, chips, grease, and rust must be removed prior to installation. Failure to take these important steps may result in improper coupling assembly, causing leakage. Also, check the manufacturer's instructions for the specific fitting used.