


May 18, 2009

	<b>TECHNICAL DATA</b>	<b>1-1/2" GROOVED MODEL L-1 SPRING LOADED IN-LINE CHECK VALVE FRICTION LOSS CHART</b>
---	-----------------------	---

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058  
 Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

FOR USE WITH ENGLISH PRACTICAL SYSTEM  
 Where Flow is Measured in GPM and Pressure is Measured in PSI

Graph is for reference purposes.



**Friction Loss for the 1-1/2" Viking Grooved Model L-1 Spring Loaded In-Line Check Valve is equivalent to 5 feet of 1-1/2" Schedule 40 (id = 1.61") Pipe (C = 120).**

**To calculate friction loss for the 1-1/2" (id = 1.61") Viking Grooved Model L-1 Spring Loaded In-Line Check Valve at a specific flow, use the following formula:**

$$P_{\text{PSI}} = \left( \frac{4.52 \times Q^{1.85}}{C^{1.85} \times 1.61^{4.87}} \right) \times 5$$

Where P = Friction Loss (PSI)  
 Q = Flow in GPM  
 C = Constant (=120)