


TECHNICAL DATA

2" MODEL E AND F SERIES DELUGE VALVES FRICTION LOSS CHART

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

FOR USE WITH ENGLISH PRACTICAL SYSTEM Where Flow is Measured in GPM and Pressure is Measured in PSI

Graph is for reference purposes.



Flow in GPM (C = 120)

Friction Loss for the 2" Viking Model E and F Series Deluge Valves is equivalent to 13 feet of 2" Schedule 40 (id = 2.067") Pipe (C = 120).

To calculate friction loss for the 2" (id = 2.067") Viking Model E and F Series Deluge Valves at a specific flow, use the following formula:

$$P = \left(\frac{4.52 \times Q^{1.85}}{C^{1.85} \times 2.067^{4.87}}\right) \times 13$$

Where P = Friction Loss (PSI)Q = Flow in GPM

C = Constant (=120)