

File Ex643
Project 78NK8884
Project 91NK1369
Project 91NK8921
Project 91NK6712
Project 91NK20429
Project 97NK23564
Project 97NK23619
Project 97NK32051
Project 98NK5103
Project 98NK17623
Project 98NK11873
Project 99NK21033
Project 99NK25817
Project 99NK36385
Project 99NK40795
Project 00NK24313
Project 00NK39796
Project 00NK36004
Project 00NK26085
Project 01NK6252
Project 01NK33
Project 01NK09243
Project 01NK46248
Project 01NK14642
Project 03NK09286

Issued: September 4, 1981
Revised: October 3, 2003

REPORT

on

SPRINKLERS, AUTOMATIC AND OPEN

Viking Corp.
Hastings, MI

Copyright © 1981 Underwriters Laboratories Inc.

Underwriters Laboratories Inc. authorizes the above named company to reproduce this Report provided it is reproduced in its entirety.



The following tests were conducted on the VK102, VK202, VK302 and VK352 Concealed Pendent sprinklers. These sprinklers are identical to the currently Listed Pendent and Recessed Pendent sprinklers except for the addition of the concealed cup assembly. The results for the following tests are recorded in Test Record No. 25.

1. Examination of Samples
2. Operation - Lodgment
3. Response for Ceiling Sprinklers
4. Operation Cold - Soldering
5. 10-Pan Distribution
6. 16-Pan Distribution
7. Fire Test

TEST RECORD INDEX

Description	Test Record
Model M (intermediate, pendent) using Model C-1 sprinkler guard	2
Model A-1 (concealed, 1/2 in. orifice), 135 and 155°F using 8 mm glass bulbs	3
Model A-1 (concealed, 1/2 in. orifice), 155°F utilizing 8 mm glass bulbs, with alternate mounting base for rigid ceilings	4
Model M (8 mm), 286°F coated with intermediate temperature rated wax	5
Model M (pendent, 1/2 in. orifice) with white and Poly 99- polyester painted surfaces designated M/W and M/B	6
Model M, 8 mm glass bulb, 1/2 in. orifice corrosion resistant and 17/32 in. orifice brass sprinkler	7
Model M (upright, 1/2 in. orifice)	8
Model M, 1/2 and 17/32 in. orifice recessed pendent and upright sprinklers with modified pip cap and G5, 5 mm glass bulbs.	9
Model M (17/32 in. orifice, pendent) rated at 500°F	10
Model M, 1/2 and 17/32 in. orifice, utilizing 5 mm glass bulbs and stainless steel pip cap insert	11
Model M, horizontal side wall, 3/8 and 1/2 in. orifice, utilizing modified pip cap and 5 mm glass bulb	12
Model M, 1/2 and 17/32 in. orifice	13
Loctite 675	14
Model M (1/2 in. orifice) upright and pendent with die cast frame designed with UNS C87400 brass	15
Model M utilizing white E-coating on frame and deflector	16
Model M (upright, 1/2 in. orifice) die cast frame	17
Model M (pendent, 1/2 in. orifice) die cast frame	18
SIN VK202 and VK352 sand cast frame, 8.0K, pendent	19
SIN 100 and VK102, sand cast frame, 5.6K, upright and pendent	20
SIN VK100, VK102, VK200, VK300, VK302, VK350, VK352	21
SIN VK333, 2.8K, horizontal side wall, 3 mm glass bulb and VK202, 8.0K, pendent 5 mm glass bulb	22
Viking sprinklers incorporating Component Recognized Norbulb glass bulbs (3 and 5 mm)	23
VK102, VK124, VK202, VK302 and VK352 pendent sprinklers with a new deflector	24
<u>VK102, VK202, VK302 and VK352 concealed pendent sprinklers</u>	<u>25</u>

Test Record Summary:

The results of this investigation indicate that the product(s) evaluated comply with applicable requirements, and therefore, such products are judged eligible to bear UL's Mark as described on the Conclusion Page of this Report.

Test Record by:
STEVE WISNIEWSKI
Lead Engineering Associate

Reviewed by:
MICHAEL McCORMICK
Engineering Group Leader