


## **TECHNICAL DATA**

## 3" MODEL F SERIES DRY VALVES FRICTION LOSS CHART

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

## FOR USE WITH ENGLISH PRACTICAL SYSTEM Where Flow is Measured in GPM and Pressure is Measured in PSI

Graph is for reference purposes.



Flow in GPM (C = 120)

Friction Loss for the 3" Viking Model F Series Dry Valves is equivalent to 3 feet of 3" Schedule 40 (id = 3.068") Pipe (C = 120).

To calculate friction loss for the 3" (id = 3.068") Viking Model F Series Dry Valves at a specific flow, use the following formula:

$$P_{PSI} = \left(\frac{4.52 \times Q^{1.85}}{C^{1.85} \times 3.068^{4.87}}\right) \times 3$$

Where P = Friction Loss (PSI)Q = Flow in GPM

C = Constant (=120)

## THIS PAGE INTENTIONALLY LEFT BLANK