

CERTIFICATE OF COMPLIANCE

Certificate Number 20131227-EX3836
Report Reference EX3836-20131221
Issue Date 2013-DECEMBER-27

Issued to: VIKING CORP
210 N INDUSTRIAL PARK RD, HASTINGS MI 49058


This is to certify that RESIDENTIAL AUTOMATIC SPRINKLERS
representative samples of See next page for Models

Have been investigated by UL in accordance with the Standard(s) indicated on this Certificate.

Standard(s) for Safety: Standard for Residential Sprinklers for Fire-Protection Service, UL1626
Other Recognized Document for Residential Sprinklers for Fire-Protection Service, ULC/ORD C-1626-03

Additional Information: See the UL Online Certifications Directory at www.ul.com/database for additional information

Only those products bearing the UL Listing Mark for the US and Canada should be considered as being covered by UL's Listing and Follow-Up Service meeting the appropriate requirements for US and Canada.

The UL Listing Mark for the US and Canada generally includes: the UL in a circle symbol with "C" and "US" identifiers:  the word "LISTED"; a control number (may be alphanumeric) assigned by UL; and the product category name (product identifier) as indicated in the appropriate UL Directory.

Look for the UL Listing Mark on the product.



William R. Carney, Director, North American Certification Programs

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at www.ul.com/contactus



CERTIFICATE OF COMPLIANCE

Certificate Number 20131227-EX3836
Report Reference EX3836-20131221
Issue Date 2013-DECEMBER-27

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

VK467 upright style sprinkler, discharge coefficient "K" = 4.9, (3 mm glass bulb type) heat responsive element, 155 and 175 °F temperature rated residential type sprinklers.


These sprinklers have a maximum pressure of 175 psig for wet systems only for spacing and flow rates as indicated below:

	SIN	Style	Temperature Rating, °F	Nominal K-Factor	Maximum Sprinkler Spacing, ft.	Minimum Flow, gpm/Sprinkler	Flowing Pressure, psig
USL, CNL	VK467#	Upright	155, 175	4.9	12 by 12	14	8.2
USL, CNL	VK467+	Upright	155, 175	4.9	12 by 12	15	9.4
USL, CNL	VK467#	Upright	155, 175	4.9	14 by 14	14	8.2
USL, CNL	VK467+	Upright	155, 175	4.9	14 by 14	15	9.4
USL, CNL	VK467#	Upright	155, 175	4.9	16 by 16	16	10.7
USL, CNL	VK467+	Upright	155, 175	4.9	16 by 16	18	13.5
USL, CNL	VK467*	Upright	155	4.9	12 by 12	15	9.4
USL, CNL	VK467*	Upright	155	4.9	14 by 14	15	9.4
USL, CNL	VK467*	Upright	155	4.9	16 by 16	18	13.5

- For installation 3 to 5 in. below the ceiling

+ - For installation 5 to 10 in. below the ceiling

* - May be installed in ceilings with beams up to 14 in. deep when installed in accordance with the manufacturer's Installation Instructions.



William R. Carney, Director, North American Certification Programs

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at www.ul.com/contactus

