

IAPMO R&T OCEANA

7-11 Fullard Road, Narre Warren, Victoria 3805, Australia



IAPMO R&T Oceana is a product certification body which inspects and arranges for the independent laboratory testing of samples taken from the manufacturer's stock or from the market or a combination of both, to verify compliance of the requirements of applicable Standards and Specifications. This activity is coupled with periodic surveillance of the manufacturer's factory and any major subcontractor's site/s as well as the assessment of the manufacturer's Quality Assurance System. This certification is subject to the conditions set forth in the characteristics below and is not to be construed as any recommendation, assurance or guarantee by IAPMO R&T Oceana of the product acceptance by Authorities Having Jurisdiction.

CERTIFICATE OF CONFORMITY

IAPMO R&T Oceana hereby grants to:

The Viking Corporation

210 N. Industrial Park Drive, Hastings, Michigan 49058 United States

the right to use the WaterMark in accordance with the ABCB Manual for the WaterMark Certification Scheme;— Australian Standards; WaterMark Technical Specifications; and the Plumbing Code of Australia; only in respect of the certified product as described in the WaterMark Certificate of Conformity – Schedule of Certified Product (Refer also IAPMO Product Listing Directory). The Certificate is granted subject to the rules governing the WaterMark Certification Scheme and the Terms and Conditions of the Approved User Agreement and IAPMO Oceana's WaterMark Governance Rules. the right to use the WaterMark in accordance with the Procedures for Certification of Plumbing and Drainage Products - WaterMark Technical Specification and the Plumbing Code of Australia only in respect of the certified product as described in the attached WaterMark Schedule. The Licence is granted subject to the rules governing the Watermark Certification Scheme and the Terms and Conditions for WaterMark Certification

Evaluated to:

WMTS486:2016

Fire sprinkler heads for domestic applications

Manufacturer:

Refer to Licence Holder

Licence No.: WM-022899

First Certified: 30 October 2019

Certification Date: 27 July 2020

Expiry Date: 29 October 2024

Chief Executive Officer of The IAPMO Group

This WaterMark certification is for the period indicated herein and is void after the date shown above. Any change in material, manufacturing process, marking or design without having first obtained the approval of IAPMO R&T Oceana, or any evidence of non-compliance with applicable Standards, Specifications or of inferior workmanship, may be deemed sufficient cause for revocation of this certification. Reproduction of or reference to this certificate for advertising purposes may be made only by specific written permission of IAPMO R&T Oceana. Any alteration of this certificate could be grounds for revocation of this certification.

"This certificate is issued by a JAS-ANZ accredited Conformity Assessment Body. The ABCB and JAS-ANZ do not in any way warrant, guarantee or represent that the product the subject of this Certificate conforms to the WaterMark Certification Scheme Rules, nor accepts any liability arising out of the use of the product. The ABCB disclaims to the extent permitted by law, all liability (including negligence) for claims of losses, expenses, damages and costs arising as a result of the use of the product(s) referred to in this Certificate."



WATERMARK CERTIFICATE OF CONFORMITY

SCHEDULE OF CERTIFIED PRODUCT



Certificate Holder: The Viking Corporation
Address: 210 N. Industrial Park Drive, Hastings,
 Michigan 49058 United States
A.B.N.:
Manufacturer: Refer to Licence Holder

Licence No: WM-022899
Certification Date: 27 July 2020
Expiry Date: 29 October 2024
First Certified: 30 October 2019
Standards: WMTS486:2016
Title: Fire sprinkler heads for domestic applications

Brand Name	Model Name	Model ID	Product Type	Product Description	Nominal Size	Inlet	Max Working Pressure	Max Operating Temperature	Material	Additional Product Information
VIKING	23021	VK470	Fire Protection	K3.0 Pendent and Recessed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23022	VK430	Fire Protection	K4.3 Pendent and Recessed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23023	VK468	Fire Protection	K4.9 Pendent, Recessed and Domed Concealed domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23024	VK466	Fire Protection	K5.2 Pendent and Recessed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23025	VK472	Fire Protection	K5.8 Pendent and Recessed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23026	VK486	Fire Protection	K4.0 Horizontal Sidewall and Recessed Horizontal Sidewall domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23027	VK484	Fire Protection	K4.2 Horizontal Sidewall and Recessed Horizontal Sidewall domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23028	VK460	Fire Protection	K5.8 Horizontal Sidewall and Recessed Horizontal Sidewall domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23029	VK467	Fire Protection	K4.9 Upright domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/79°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23031	VK480	Fire Protection	K4.0 Flat Plate Concealed Horizontal Sidewall domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	74°C/96°C	DR Brass	Product finishes: Plain Brass, Electroless Nickel Teflon
VIKING	23032	VK490	Fire Protection	K5.8 Flat Plate Concealed Horizontal Sidewall domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	74°C/96°C	DR Brass	Product finishes: Plain Brass, Electroless Nickel Teflon
VIKING	23033	VK496	Fire Protection	K3.0 Flat Plate Concealed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/93°C	DR Brass	Product finishes: Plain Brass, Electroless Nickel Teflon
VIKING	23034	VK494	Fire Protection	K4.9 Flat Plate Concealed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/93°C	DR Brass	Product finishes: Plain Brass, Electroless Nickel Teflon

Brand Name	Model Name	Model ID	Product Type	Product Description	Nominal Size	Inlet	Max Working Pressure	Max Operating Temperature	Material	Additional Product Information
VIKING	23035	VK498	Fire Protection	K5.8 Flat Plate Concealed Pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	68°C/93°C	DR Brass	Product finishes: Plain Brass, Electroless Nickel Teflon
VIKING	23343	VK305	Fire Protection	K5.6 Microfast quick response horizontal sidewall domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	57°C/68°C/79°C/93°C/141°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23344	VK3001	Fire Protection	K5.6 Quick response upright domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	57°C/68°C/79°C/93°C/141°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23345	VK3021	Fire Protection	K5.6 Quick response pendent domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	57°C/68°C/79°C/93°C/141°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon
VIKING	23346	VK3101	Fire Protection	K5.6 Quick response conventional domestic fire sprinkler head.	DN15	1/2" NPT	1200kPa	57°C/68°C/79°C/93°C/141°C	DR Brass	Product finishes: Plain Brass, Chrome, Painted, Electroless Nickel Teflon

END RECORD

END RECORD


 Chief Executive Officer of The IAPMO Group